

# UNISONIC TECHNOLOGIES CO., LTD

7N70-M **Preliminary Power MOSFET** 

# **7A, 700V N-CHANNEL POWER MOSFET**


#### DESCRIPTION

The UTC 7N70-M is a high voltage power MOSFET and is designed to have better characteristics, such as fast switching time, low gate charge, low on-state resistance and have a high rugged avalanche characteristics. This power MOSFET is usually used at high speed switching applications in power supplies, PWM motor controls, high efficient DC to DC converters and bridge circuits.



- \*  $R_{DS(ON)}$  < 1.4 $\Omega$  @  $V_{GS}$  = 10V,  $I_{D}$  = 3.5A
- \* Fast switching capability
- \* Avalanche energy specified
- \* Improved dv/dt capability, high ruggedness

#### **SYMBOL**



#### ORDERING INFORMATION

Pin Assignment: G: Gate

Order Number		Doolsons	Pin Assignment			Doolsing	
Lead Free	Halogen Free	Package	1	2	3	Packing	
7N70L-TF1-T	7N70G-TF1-T	TO-220F1	G	D	S	Tube	


S: Source

D: Drain

7N70L-TF1-T (1) T: Tube (1)Packing Type (2)Package Type (2) TF1: TO-220F1 (3) L. Lead Free, G. Halogen Free and Lead Free (3)Green Package

#### **MARKING**

Note:



TO-220F1

www.unisonic.com.tw 1 of 6

## ■ ABSOLUTE MAXIMUM RATINGS (T<sub>C</sub> = 25°C, unless otherwise specified)

PARAMETER	SYMBOL	RATINGS	UNIT	
Drain-Source Voltage	$V_{DSS}$	700	V	
Gate-Source Voltage	$V_{GSS}$	±30	٧	
Continuous Drain Current		7.0	Α	
$T_C = 100^{\circ}C$	I <sub>D</sub>	4.7	Α	
Drain Current Pulsed (Note 2)	I <sub>DM</sub>	28	Α	
Avalanche Energy, Single Pulsed (Note 3)	E <sub>AS</sub>	380	mJ	
Avalanche Energy, Repetitive, Limited by T <sub>JMAX</sub>	E <sub>AR</sub>	14.2	mJ	
Peak Diode Recovery dv/dt (Note 4)	dv/dt	4.5	V/ns	
Power Dissipation (T <sub>C</sub> = 25°C)	$P_{D}$	48	W	
Junction Temperature	TJ	+150	°C	
Storage Temperature	T <sub>STG</sub>	-55 ~ +150	°C	

Notes: 1. Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.

- 2. Repetitive Rating : Pulse width limited by  $T_{\mathsf{J}}$
- 3. L=15.5mH,  $I_{AS}$ =7.0A,  $V_{DD}$ =50V,  $R_{G}$ =0  $\Omega$ , Starting  $T_{J}$ =25°C
- 4.  $I_{SD} \le 7.0A$ , di/dt  $\le 100A/\mu s$ ,  $V_{DD} \le BV_{DSS}$ , Starting  $T_J = 25^{\circ}C$

## **■ THERMAL DATA**

PARAMETER	SYMBOL	RATINGS	UNIT
Junction to Ambient	$\theta_{JA}$	62.5	°C/W
Junction to Case	$\theta_{JC}$	2.6	°C/W


# ■ **ELECTRICAL CHARACTERISTICS** (T<sub>C</sub> =25°C, unless otherwise specified)

PARAMETER		SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
OFF CHARACTERISTICS							
Drain-Source Breakdown Voltage		BV <sub>DSS</sub>	$V_{GS} = 0V, I_D = 250\mu A$	700			V
Drain-Source Leakage Current			$V_{DS} = 700V, V_{GS} = 0V$			1	μA
			V <sub>DS</sub> = 560V, T <sub>C</sub> = 125°C			1	μA
Gate-Source Leakage Current	Forward	I <sub>GSS</sub>	$V_{GS} = 30V, V_{DS} = 0V$			100	nA
	Reverse		$V_{GS} = -30V, V_{DS} = 0V$			-100	nA
Drookdown Voltago Tomporaturo	Coefficient	^ D\/ _ / ^ T	I <sub>D</sub> = 250mA	0.07			V/°C
Breakdown Voltage Temperature Coefficient		$\triangle BV_{DSS}/\triangle T_{J}$	Referenced to 25°C		0.67		V/ C
ON CHARACTERISTICS							
Gate Threshold Voltage		$V_{GS(TH)}$	$V_{DS} = V_{GS}, I_{D} = 250 \mu A$	2.0		4.0	V
Drain-Source ON-State Resistance	Drain-Source ON-State Resistance		$V_{GS} = 10V, I_D = 3.5A$			1.4	Ω
DYNAMIC CHARACTERISTICS							
Input Capacitance	nput Capacitance		V - 25V V - 0V		1000		pF
Output Capacitance		C <sub>ISS</sub>	$V_{DS} = 25V, V_{GS} = 0V,$ f = 1MHz		97		pF
Reverse Transfer Capacitance		$C_{RSS}$			19		pF
SWITCHING CHARACTERISTIC	S						
Total Gate Charge		$Q_G$	V <sub>DS</sub> = 50V, I <sub>D</sub> = 1.3A,		120		nC
Gate-Source Charge		$Q_GS$	$V_{GS}$ = 10V, $I_{G}$ = 100 $\mu$ A		7		nC
Gate-Drain Charge		$Q_{DD}$	(Note 1, 2)		18		nC
Turn-on Delay Time		t <sub>D(ON)</sub>	V 20V V 40V		50		ns
Turn-on Rise Time		t <sub>R</sub>	$V_{DD} = 30V, V_{GS} = 10V,$		80		ns
Turn-off Delay Time		t <sub>D(OFF)</sub>	$I_D$ = 0.5A, R <sub>G</sub> =25Ω (Note 1, 2)		295		ns
Turn-off Fall Time		$t_{F}$	(Note 1, 2)		75		ns
SOURCE- DRAIN DIODE RATIN	GS AND CH	IARACTERIST	TICS			ā.	
Drain-Source Diode Forward Voltage		$V_{SD}$	$V_{GS} = 0V, I_S = 7.0A$			1.4	V
Maximum Continuous Drain-Source Diode Forward Current		Is				7.0	Α
						7.0	A
Maximum Pulsed Drain-Source Diode		I <sub>SM</sub>				28	Α
Forward Current						20	A
Reverse Recovery Time		t <sub>rr</sub>	$V_{GS} = 0V, I_{S} = 7.0A,$		320		ns
Reverse Recovery Charge		$Q_{RR}$	$dI_F/dt = 100 A/\mu s (Note 1)$		2.4		μC


Notes: 1. Pulse Test: Pulse width ≤ 300µs, Duty cycle ≤ 2%

<sup>2.</sup> Essentially independent of operating temperature

#### **■ TEST CIRCUITS AND WAVEFORMS**




Peak Diode Recovery dv/dt Test Circuit




Peak Diode Recovery dv/dt Waveforms


# ■ TEST CIRCUITS AND WAVEFORMS (Cont.)




**Switching Test Circuit** 




**Switching Waveforms** 




**Gate Charge Test Circuit** 



**Gate Charge Waveform** 



**Unclamped Inductive Switching Test Circuit** 



**Unclamped Inductive Switching Waveforms** 

UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice.

