
# SS5817D THRU SS5819D

#### SURFACE MOUNT SCHOTTKY BARRIER RECTIFIERS Reverse Voltage - 20 to 40 V Forward Current - 1 A

### Features

- Plastic package has Underwriters Laboratory Classification 94V-0
- Metal silicon junction, majority carrier conduction
- For surface mount applications
- Guard ring for overvoltage protection
- Low power loss, high efficiency
- High current capability, Low forward voltage drop
- High surge capability



## **Mechanical Data**

- Case: SMA (DO-214AC) molded plastic case
- Terminals: Solder plate, solderable per MIL-STD -750, method 2026
- Polarity: Color band denotes cathode end
- Mounting Position: Any

## Maximum Ratings and Electrical Characteristics

Ratings at 25 °C ambient temperature unless otherwise specified. Single phase, half wave, resistive or inductive load, for capacitive load, derate by 20 %

Parameter	Symbols	SS5817D	SS5818D	SS5819D	Units
Maximum Repetitive Peak Reverse Voltage	V <sub>RRM</sub>	20	30	40	V
Maximum RMS Voltage	V <sub>RMS</sub>	14	21	28	V
Maximum DC Blocking Voltage	V <sub>DC</sub>	20	30	40	V
Maximum Average Forward Rectified Current 0.375" (9.5 mm) Load Length at $T_L$ = 90 $^{\circ}\mathrm{C}$	I <sub>F(AV)</sub>	1			А
Peak Forward Surge Current 8.3 mS Single Half Sine-wave Superimposed on Rated Load (JEDEC Method) at $T_L = 70$ °C	I <sub>FSM</sub>	25			А
Maximum Instantaneous Forward Voltage at 1 A	VF	0.45	0.55	0.6	V
$ \begin{array}{ll} \mbox{Maximum Instantaneous Reverse Current} & \mbox{at } T_a = 25 \ ^{\circ}\mbox{C} \\ \mbox{at Rated DC Blocking Voltage} & \mbox{at } T_a = 100 \ ^{\circ}\mbox{C} \\ \end{array} $	I <sub>R</sub>	0.5 10			mA
Typical Junction Capacitance <sup>1)</sup>	Cj	110			pF
Typical Thermal Resistance <sup>2)</sup>	$R_{ ext{ heta}JA}$	88			°C/W
Operating and Storage Temperature Range	Tj, T <sub>stg</sub>	- 65 to + 125			°C

<sup>1)</sup> Measured at 1 MHz and reverse voltage of 4 V.


SEMTECH ELECTRONICS LTD.

Subsidiary of Sino-Tech International (BVI) Limited


<sup>2)</sup> Thermal Resistance (from Junction to Ambient) Vertical P.C.B Mounted, with 1.5 X 1.5" (38 X 38 mm) copper pads.







R





Subsidiary of Sino-Tech International (BVI) Limited



Dated: 27/02/2012 J Rev: 01