


**ES1A-W THRU ES1J-W****Formosa MS****1.0A Surface Mount Super Fast Rectifiers-50-600V****Features**

- ◆ The plastic package carries Underwriters Laboratory Flammability Classification 94V-0
- ◆ For surface mounted applications
- ◆ Super fast switching for high efficiency
- ◆ Low reverse leakage
- ◆ Built-in strain relief, ideal for automated placement
- ◆ High forward surge current capability
- ◆ High temperature soldering guaranteed: 250°C/10 seconds at terminals
- ◆ Compliant to RoHS Directive 2011/65/EU
- ◆ Suffix "-H" indicates Halogen-free part, ex. ES1J-W-H

**Mechanical data**

- ◆ **Case:** JEDEC DO-214AC molded plastic body
- ◆ **Terminals:** Solder plated, solderable per MIL-STD-750, Method 2026
- ◆ **Polarity:** Color band denotes cathode end
- ◆ **Mounting Position:** Any
- ◆ **Weight:** 0.002 ounce, 0.07 grams

**Package outline****Maximum ratings and Electrical Characteristics (AT  $T_A=25^\circ\text{C}$  unless otherwise noted)**

PARAMETER	CONDITIONS			Symbol	MIN.	TYP.	MAX.	UNIT
Forward rectified current	See Fig.2			$I_o$			1.0	A
Forward surge current	8.3ms single half sine-wave (JEDEC method)			$I_{FSM}$			30	A
Reverse current	$V_R = V_{RRM} T_A = 25^\circ\text{C}$			$I_R$			5.0	$\mu\text{A}$
	$V_R = V_{RRM} T_A = 100^\circ\text{C}$						50	
Thermal resistance	Junction to ambient NOTE 1			$R_{\theta JA}$		60		$^\circ\text{C}/\text{W}$
Diode junction capacitance	$f=1\text{MHz}$ and applied 4V DC reverse voltage			$C_J$		15		pF
Storage temperature				$T_{STG}$	-65		+125	$^\circ\text{C}$

SYMBOLS	$V_{RRM}$ *1 (V)	$V_{RMS}$ *2 (V)	$V_R$ *3 (V)	$V_F$ *4 (V)	$t_{rr}$ *5 (ns)	Operating temperature $T_J$ , ( $^\circ\text{C}$ )
ES1A-W	50	35	50			
ES1B-W	100	70	100			
ES1C-W	150	105	150			
ES1D-W	200	140	200			
ES1E-W	300	210	300			
ES1G-W	400	280	400			
ES1J-W	600	420	600	1.70		

\*1 Repetitive peak reverse voltage

\*2 RMS voltage







\*3 Continuous reverse voltage

\*4 Maximum forward voltage@ $I_F=1.0\text{A}$ 

\*5 Maximum Reverse recovery time, note 2

Note: 1.P.C.B. mounted with 0.2x0.2"(5.0x5.0mm) copper pad areas



2. Reverse recovery time test condition,  $I_F=0.5\text{A}$ ,  $I_R=1.0\text{A}$ ,  $I_{RR}=0.25\text{A}$ 


**ES1A-W THRU ES1J-W****Formosa MS****Rating and characteristic curves**

**ES1A-W THRU ES1J-W****Formosa MS****Pinning information**

Pin	Simplified outline	Symbol
Pin1 cathode Pin2 anode		

**Marking**

Type number	Marking code	Example	
ES1A-W	ES1A	For Halogen Device	
ES1B-W	ES1B	For Halogen-free Device	
ES1C-W	ES1C		
ES1D-W	ES1D		
ES1E-W	ES1E		
ES1G-W	ES1G		
ES1J-W	ES1J		

**Suggested solder pad layout**

Dimensions in inches and (millimeters)

PACKAGE	A	B	C
SMA-W	0.110 (2.80)	0.063 (1.60)	0.087 (2.20)