

(2) D

(3) s

Schematic diagram

NCE85H21C XXXXX

Marking and pin assignment

GD

TO-220-3L top view

NCE

(1) GO



NCE N-Channel Enhancement Mode Power MOSFET



The NCE85H21C uses advanced trench technology and design to provide excellent $R_{DS(ON)}$ with low gate charge. It can be used in automotive applications and a wide variety of other applications.

General Features

V_{DSS} =85V,I_D =210A
R_{DS(ON)} < 4.95mΩ @ V_{GS}=10V

- Good stability and uniformity with high E_{AS}
- Special process technology for high ESD capability
- High density cell design for ultra low Rdson
- Fully characterized avalanche voltage and current
- Excellent package for good heat dissipation

Application

- Automotive applications
- Hard switched and high frequency circuits
- Uninterruptible power supply

100% UIS TESTED!

100% ΔVds TESTED!

Package Marking and Ordering Information

Device Marking	Device	Device Package	Reel Size	Tape width	Quantity
NCE85H21C	NCE85H21C	TO-220	-	-	-

Absolute Maximum Ratings (T_c=25℃ unless otherwise noted)

Parameter	Symbol	Limit	Unit	
Drain-Source Voltage	VDSS	85	V	
Gate-Source Voltage	Vgs	±20	V	
Drain Current-Continuous	Ι _D	210 (Note5)	А	
Drain Current-Continuous(Tc=100℃)	I _D (100℃)	148	А	
Pulsed Drain Current	I _{DM}	850	А	
Maximum Power Dissipation	PD	300	W	
Derating factor		2.0	W/℃	
Single pulse avalanche energy (Note 3)	E _{AS}	1800	mJ	
Peak Diode Recovery dv/dt (Note 4)	dv/dt	5	V/ns	
Operating Junction and Storage Temperature Range	T _J ,T _{STG}	-55 To 175	°C	





Thermal Characteristic

Thermal Resistance, Junction-to-Case (Note 1)	$R_{ extsf{ heta}JC}$	0.5	°C/W
---	-----------------------	-----	------

Electrical Characteristics (T_C=25[°]C unless otherwise noted)

Parameter	Symbol	Condition	Min	Тур	Max	Unit
Off Characteristics			•			
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V I _D =250µA	85	-	-	V
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =85V,V _{GS} =0V	-	-	1	μA
Gate-Body Leakage Current	I _{GSS}	V_{GS} =±20V, V_{DS} =0V	-	-	±200	nA
On Characteristics						
Gate Threshold Voltage	V _{GS(th)}	$V_{DS}=V_{GS}$, $I_{D}=250\mu A$	2	3.2	4	V
Drain-Source On-State Resistance	R _{DS(ON)}	V_{GS} =10V, I _D =40A	-	4.1	4.95	mΩ
Forward Transconductance	g fs	V _{DS} =10V,I _D =20A	35	-	-	S
Dynamic Characteristics						
Input Capacitance	C _{lss}		-	7600	-	PF
Output Capacitance	C _{oss}	V _{DS} =25V,V _{GS} =0V, F=1.0MHz	-	720	-	PF
Reverse Transfer Capacitance	C _{rss}		-	346	-	PF
Switching Characteristics						
Turn-on Delay Time	t _{d(on)})/ _40)// _404	-	23	-	nS
Turn-on Rise Time	tr	$V_{DD}=40V, I_D=40A$	-	124	-	nS
Turn-Off Delay Time	t _{d(off)}	V _{GS} =10V,R _{GEN} =1.2Ω _(Note2)	-	84	-	nS
Turn-Off Fall Time	t _f		-	78	-	nS
Total Gate Charge	Qg	V =40V/L =40A	-	140	-	nC
Gate-Source Charge	Q _{gs}	V_{DS} =40V,I _D =40A, V_{GS} =10V ^(Note2)	-	40	-	nC
Gate-Drain Charge	Q _{gd}	VGS-10V	-	57	-	nC
Drain-Source Diode Characteristics						
Diode Forward Voltage	V _{SD}	V _{GS} =0V,I _S =40A	-	-	1.2	V
Reverse Recovery Time	t _{rr}	TJ = 25°C, IF = 40A	-	110	-	nS
Reverse Recovery Charge	Qrr	di/dt = 100A/µs ^(Note2)	-	300	-	nC
Forward Turn-On Time	t _{on}	Intrinsic turn-on time is negligible (turn-on is dominated by LS+			LS+LD)	

Notes:


- 1. Surface Mounted on FR4 Board, t ≤ 10 sec.
- 2. Pulse Test: Pulse Width ≤ 400µs, Duty Cycle ≤ 2%.
- 3. EAS condition: Tj=25 $^\circ\!\!\mathrm{C}$,V_{DD}=42.5V,V_G=10V,L=0.5mH,Rg=25\Omega
- 4. ISD≤125A, di/dt≤260A/µs, VDD≤V(BR)DSS, TJ ≤175°C




Pb Free Product




Test Circuit 1) E_{AS} test circuit



2) Gate charge test circuit



3) Switch time test circuit












Typical Electrical and Thermal Characteristics





T_J-Junction Temperature ($^{\circ}C$)

Figure 4 Rdson-JunctionTemperature



Qg Gate Charge (nC)

Figure 5 Gate Charge





Figure 6 Source- Drain Diode Forward





NCE85H21C










Figure 10 BV_{DSS} vs Junction Temperature



T_J-Junction Temperature(°C)

Figure 11 V_{GS(th)} vs Junction Temperature








Figure 11 Normalized Maximum Transient Thermal Impedance


TO-220-3L Package Information

Pb Free Product

NCE85H21C



NCE85H21C



Symbol	Dimensions	In Millimeters	Dimensions In Inches			
	Min.	Max.	Min.	Max.		
А	4.400	4.600	0.173	0.181		
A1	2.250	2.550	0.089	0.100		
b	0.710	0.910	0.028	0.036		
b1	1.170	1.370	0.046	0.054		
С	0.330	0.650	0.013	0.026		
c1	1.200	1.400	0.047	0.055		
D	9.910	10.250	0.390	0.404		
E	8.9500	9.750	0.352	0.384		
E1	12.650	12.950	0.498	0.510		
е	2.540	2.540 TYP.		0.100 TYP.		
e1	4.980	5.180	0.196	0.204		
F	2.650	2.950	0.104	0.116		
Н	7.900	8.100	0.311	0.319		
h	0.000	0.300	0.000	0.012		
L	12.900	13.400	0.508	0.528		
L1	2.850	3.250	0.112	0.128		
V	7.500 REF.		0.295 REF.			
Φ	3.400	3.800	0.134	0.150		

Attention





- Any and all NCE power products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your NCE power representative nearest you before using any NCE power products described or contained herein in such applications.
- NCE power assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all NCE power products described or contained herein.
- Specifications of any and all NCE power products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- NCE power Semiconductor CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all NCE power products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of NCE power Semiconductor CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. NCE power believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the NCE power product that you intend to use.
- This catalog provides information as of Sep.2010. Specifications and information herein are subject to change without notice.