

# APPROVAL SHEET

MODEL NO.: SMD0805-020-16V
----------------------------

CUSTOMER:

CUSTOMER'S APPROVAL:


AUTHORIZED SIGNATURE/STAMP:

DATE

MANUFACTURER	:
HEAD OFFICE:	
	13F.,No.120-10,Sec.3,Zhongshan Rd.,Zhonghe Dist.,New Taipei City 23544,Taiwan
	Tel: 886-2-8221-2567
	Fax:882-2-2225-7268
	E-mail:service@chipfast.com.tw
China Branch:	
	Factory Building B)Shuangpeng,Weibu Village, Qiuchang Town,
	Huiyang District, Huizhou City, Guangdong Province, P.R.C.)
	Tel: 86-752-3562001
	Fax:86-752-3558696
	E-mail:service@atpptc.com

Submitted by:Chung ChengApproved by:YC LinDATE:2-Mar-22

SEA & LAND ELECTRONIC CORP.



# SMD0805-020-16V

# Features

Surface Mount Devices

- Lead free device
- Size 2.0\*1.2 mm / 0.08\*0.05 inch
- Surface Mount packaging for automated assembly

#### Applications

- Almost anywhere there is a low voltage power supply, up to 15V and a load to be protected, including: Computer mother board, Modem. USB hub
- PDAs & Charger, Analog & digital line card
  Digital cameras, Disk drivers, CD-ROMs,

Alpha-Top (Sea & Land Alliance)

# Performance Specification

<b>M</b> edal	Model Marking V <sub>max</sub>		I <sub>max</sub> I <sub>hold</sub>		I <sub>trip</sub>	P <sub>d</sub>	Maximum Time To Trip		Resistance		Agency Approval	
woder	Marking			@25°C	@25°C	Тур.	Current	Time	<b>Ri</b> <sub>min</sub>	R1max	UL	TUV
		(Vdc)	(A)	(A)	(A)	(W)	(A)	(Sec)	(Ω)	(Ω)	UL	104
SMD0805-020-16V	2	16.0	100	0.20	0.50	0.5	8.0	0.02	0.650	3.500		
Ihold = Hold Current.	Ihold = Hold Current. Maximum current device will not trip in 25°C still air.											
Itrip = Trip Current. M	Itrip = Trip Current. Minimum current at which the device will always trip in 25°C still air.											
Vmax = Maximum oper	Vmax = Maximum operating voltage device can withstand without damage at rated current (Imax).											
Imax = Maximum fault current device can withstand without damage at rated voltage (Vmax).												
Pd = Power dissipation when device is in the tripped state in 25°C still air environment at rated voltage.												
<b>Rimin/max</b> = Minimum/Maximum device resistance prior to tripping at 25°C.												
R1 <sub>max</sub> = Maximum device resistance is measured one hour post reflow.												
CAUTION : Operation beyond the specified ratings may result in damage and possible arcing and flame.												

#### **Environmental Specifications**

Test	Conditions	Resistance change		
Passive aging	+85°C, 1000 hrs.	±5% typical		
Humidity aging	+85°C, 85% R.H. , 168 hours	±5% typical		
Thermal shock	+85°C to -40°C, 20 times	±33% typical		
Resistance to solvent	MIL-STD-202, Method 215	No change		
Vibration	MIL-STD-202, Method 201	No change		
Ambient operating conditions : - 40 °C to +85 °C				
Maximum surface temperature of the device in the trip	oped state is 125 °C			

#### Agency Approvals :

Regulation/Standard:

RoHS 2015/863/EU

## Ihold Versus Temperature

Model		Max	kimum ambie	ent operating	temperature	e (T <sub>mao</sub> ) vs. h	old current (	I <sub>hold</sub> )	
Model	-40°C	-20°C	0°C	25°C	40°C	50°C	60°C	70°C	85°C
SMD0805-020-13.2V	0.280	0.250	0.230	0.20	0.170	0.140	0.120	0.100	0.070


# SMD0805-020-16V


## Alpha-Top (Sea & Land Alliance)


#### Construction And Dimension (Unit:mm)

Model	Α		В		С		D	E
Woder	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Min.
SMD0805-020-16V	1.90	2.20	1.20	1.50	0.50	1.20	0.20	0.10

# Dimensions & Marking








#### **Termination Pad Characteristics**

Terminal pad materials : Terminal pad solderability : Tin-plated Nickel-Copper


Meets EIA specification RS186-9E and ANSI/J-STD-002 Category 3.

#### Rework

Use standard industry practices, the removal device must be replaced with a fresh one. Thermal Derating Curve



#### Typical Time-To-Trip At 25°C



# \Lambda WARNING:


· Use PPTC beyond the maximum ratings or improper use may result in device damage and possible electrical arcing and flame.

PPTC are intended for protection against occasional over current or over temperature fault conditions and should not be used when repeated fault conditions or prolonged trip events are anticipated.
 Device performance can be impacted negatively if devices are handled in a manner inconsistent with recommended electronic, thermal, and mechanical procedures for electronic components.
 Use PPTC with a large inductance in circuit will generate a circuit voltage (L di/dt) above the rated voltage of the PPTC.

· Avoid impact PPTC device its thermal expansion like placed under pressure or installed in limited space.

Contamination of the PPTC material with certain silicon based oils or some aggressive solvents can adversely impact the performance of the devices. PPTC SMD can be cleaned by standard methods.
 Requests that customers comply with our recommended solder pad layouts and recommended reflow profile. Improper board layouts or reflow profile could negatively impact solderability performance of our devices.


# SMD0805-020-16V




## Tape And Reel Specifications (mm)

## **EIA Tape Component Dimensions**

Governing Specifications	EIA 481-1
W	8.0 ± 0.3
P0	4.0 ± 0.10
P1	4.0 ± 0.10
P2	2.0 ± 0.05
A0	1.45 ± 0.10
В0	2.30 ± 0.10
B1max.	4.35
D0	1.55 + 0.1, -0
F	3.5 ± 0.05
E1	1.75 ± 0.10
E2min.	6.25
Т	0.25
T1max.	0.1
K0	0.74 ± 0.1
Leader min.	390
Trailer min.	160
Reel Dimensions	
A max.	178
N min.	60
W1	9.0 ± 0.5
W2	12.0 ± 0.05



#### **EIA Reel Dimensions**



# Storage And Handling

- Storage conditions : 40°C max, 70% R.H.
- · Devices may not meet specified performance
- if storage conditions are exceeded.

#### Order Information

Order Information		Packaging
SMD0805	020-16V	Tape & Reel Quantity
Product name	Hold	
Size 2012 mm / 0805 inch	Current	5,000 pcs/reel
SMD: surface mount device	0.20A	

Tape & reel packaging per EIA481-1 Labeling Information

