

Surface Mount Schottky Rectifier Reverse Voltage 40~60V Forward Current 1A

Features

- Low VF Schottky barrier diodes
- Very low profile typical height of 1.0 mm
- Low forward voltage drop
- Low leakage current
- Moisture sensitivity: level 1, per J-STD-020
- High temperature soldering guaranteed: 260°C/10 seconds
- Halogen-free according to IEC 61249-2-21 definition





eSGP(SOD-323F)

Typical Applications

For use of fast swiching in RF module, lighting, cellular phone, portable device, power supplies and other consumer applications.

Maximum Ratings (TA = 25 °C unless otherwise noted)							
Parameter	Symbol	SGP0140SL	SGP0160SL	Unit			
Maximum repetitive peak reverse voltage	VRRM	40	60	V			
Maximum RMS voltage	VRMS	28	42	V			
Maximum DC blocking voltage	VDC	40	60	V			
Maximum average forward rectified current	IF(AV)	1.0		Α			
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	IFSM	30		А			
Operating junction and storage temperature range	TJ, TSTG	- 55 to + 150		°C			

Electrical Characteristics (TA = 25 °C unless otherwise noted)									
Parameter	Test Conditions	Symbol	SGP0140SL	SGP0160SL	Unit				
Maximum instantaneous forward voltage	1 A	V _F	0.50	0.70	Volts				
Maximum DC reverse current at rated DC blocking voltage	TA=25℃ TA=125℃	I _R	0	2	mA				
Typical junction capacitance	4.0 V, 1 MHz	CJ	4	5	pF				
Typical thermal resistance	juntion to mount	$R_{\theta JM}$	5	5	°C/W				

Note:1), The thermal resistance from junction to mount, mounted on P.C.B with 5x5mm copper pads, 2 OZ, FR4 PCB

www.goodark.com 1/4 2015.04-Rev.A



Surface Mount Schottky Rectifier Reverse Voltage 40~60V Forward Current 1A

Ratings and Characteristics Curves

(TA = 25°C unless otherwise noted)




Figure 1. Forward Current Derating Curve




Figure 3. Typical Reverse Characteristics




Figure 5.Maximum Non-Repetitive Peak Forward Surge Current




Figure 2. Typical Instantaneous Forward Characteristics





Figure 4. Typical Junction Capacitance





Surface Mount Schottky Rectifier Reverse Voltage 40~60V Forward Current 1A


Package Outline Dimensions




Package	Unit:mm		Unit:inch		
eSGP	MIN	MAX	MIN	MAX	
Α	0.9	1.08	0.035	0.043	
В	0.5	0.7	0.020	0.028	
С	0.1	0.25	0.004	0.010	
D	1.4	1.6	0.055	0.063	
E	2.0	2.2	0.079	0.087	
L	0.35	0.65	0.014	0.026	
HE	2.4	2.8	0.094	0.110	







Soldering footprint




Packing Information

Packing quantities:

- 1),3000 pcs/Reel, 40 Reels/Box; 8mm Tape, 7" Reel
- 2),10000 pcs/Reel, 16 Reels/Box; 8mm Tape, 13" Reel

Tape & Reel Specification





Surface Mount Schottky Rectifier Reverse Voltage 40~60V Forward Current 1A

Disclaimers

These materials are intended as a reference to assist our customers in the selection of the Suzhou Good-Ark product best suited to the customer's application; they do not convey any license under any intellectual property rights, or any other rights, belonging to Suzhou Good-Ark Electronics Co., Ltd.or a third party.

Suzhou Good-Ark Electronics Co., Ltd. assumes no responsibility for any damage, or infringement of any third-party's rights, originating in the use of any product data, diagrams, charts, programs, algorithms, or circuit application examples contained in these materials.

All information contained in these materials, including product data, diagrams, charts, programs and algorithms represents information on products at the time of publication of these materials, and are subject to change by Suzhou Good-Ark Electronics Co., Ltd. without notice due to product improvements or other reasons. It is therefore recommended that customers contact Suzhou Good-Ark Electronics Co., Ltd. or an authorized Suzhou Good-Ark Electronics Co., Ltd. for the latest product information before purchasing a product listed herein. The information described here may contain technical inaccuracies or typographical errors. Suzhou Good-Ark Electronics Co., Ltd. assumes no responsibility for any damage, liability, or other loss rising from these inaccuracies or errors. Please also pay attention to information published by Suzhou Good-Ark Electronics Co., Ltd. by various means, including our website home page. (http://www.goodark.com)

When using any or all of the information contained in these materials, including product data, diagrams, charts, programs, and algorithms, Please be sure to evaluate all information as a total system before making a final decision on the applicability of the information and products. Suzhou Good-Ark Electronics Co., Ltd. assumes no responsibility for any damage, liability or other loss resulting from the information contained herein.

The prior written approval of Suzhou Good-Ark Electronics Co., Ltd. is necessary to reprint or reproduce in whole or in part these materials.

Please contact Suzhou Good-Ark Electronics Co., Ltd. or an authorized distributor for further details on these materials or the products contained herein.