### Features/Benefits

- Subminiature size—capable of switching 1 AMP
- Vertical & right angle terminations
- PC & panel mount models
- Snap-in front panel mounting available
- Epoxy terminal seal-compatible with bottom wash cleaning
- RoHS compliant models available



Models Available

### Typical Applications

- Telecommunications and networking equipment
- Computers and peripherals
- Instrumentation and controls





### **Specifications**

CONTACT RATING: B contact material: 0.4 VA max. @ 20 V AC or DC max. Q contact material: 1 AMP @ 120 V AC or 28 V DC. See page A-19 for additional ratings.

ELECTRICAL LIFE: TP11, TP21 MODELS: 60,000 make-and-break cycles at full load. TP12 MODELS: 30,000 cycles.

CONTACT RESISTANCE: Below 20 m $\Omega$ 15 typ. initial @ 2-4 V DC, 100 mA, for both silver and gold plated contacts.

INSULATION RESISTANCE:  $10^9\Omega$  15min.

DIELECTRIC STRENGTH: 1000 Vrms min. @ sea level. OPERATING TEMPERATURE: -30°15C to 85°15C. SOLDERABILITY: Per MIL-STD-202F method 208D, or

EIA RS-186E method 9 (1 hour steam aging).

NOTE: Any models supplied with Q, B, P, R or G contact material are RoHS compliant.

NOTE: Specifications and materials listed above are for switches with standard options. For information on specific and custom switches, consult Customer Service Center.

### **Materials**

CASE: Glass filled nylon 4/6 or 6/6, flame retardant, heat stabilized or diallyl phthalate (DAP), (UL 94V-0).

PLUNGER: Thermoplastic polyester (UL 94V-0).

CAP & FRAME: Nylon, black standard.

BUSHING: Brass, nickel plated. HOUSING: Stainless steel.

SWITCH SUPPORT: Brass, matte-tin plated.

END CONTACTS: B contact material: Copper alloy, with gold plate over nickel plate. Q contact material: Coin silver, silver plated. See page A-19 for additional contact materials.


CENTER CONTACT & ALL TERMINALS: B contact material: Copper alloy, with gold plate over nickel plate. Q contact material: Copper alloy, silver plated. See page A-19 for additional contact materials.

TERMINAL SEAL: Epoxy. Refer to soldering and cleaning in Technical Data Chapter

HARDWARE: Nut & Locking Ring: Brass nickel plated. Lockwasher: Steel, nickel plated.


### **Build-A-Switch**

To order, simply select desired option from each category and place in the appropriate box. Available options are shown and described on pages A-16 thru A-20. For additional options not shown in catalog, consult Customer Service Center. All models have epoxy terminal seal and are compatible with all "bottom-wash" PCB cleaning methods.






### **SWITCH FUNCTION**



All models with all options when ordered with G, Q or R contact material.

# **ACTUATOR—SNAP-IN FRONT MOUNT**

## J81 SNAP-IN WITH FRAME



OPTION CODE	CAP COLOR	
2	BLACK	
1	WHITE	

OPTION CODE	FRAME COLOR	
2	BLACK	
NONE	No Frame Color (J80 option)	

Cap and Frame Finish: matte. Other colors available, consult Customer Service Center. NOTE: Available with Z, C, or W terminations.

NOTE: Caps & frames available separately, see page A-20.



Dimensions are shown: Inches (mm)








THREADED, FLAT


LT .21517" HIGH PLUNGER. MS9 .130" HIGH .310" HIGH BUSHING, THREADED

LT9 .215"17 HIGH PLUNGER, .310" HIGH BUSHING, UNTHREADED























1/4 IN. BUSHING

Standard with Z, C, W terminations.


Standard with A, AV, V3 terminations.


Not available with 7 terminations

† Subtract .016 (0,41) for models with A, AV or V3 terminations. NOTE: Caps available for plunger options, see page A-20.

### PANEL MOUNTING

### 10-48 BUSHING





Without locking ring


With standard locking ring


Without locking ring

With standard locking ring

NOTE: One mounting nut, locking ring and lockwasher supplied standard with 10-48 threaded bushings (two nuts with 1/4-40 bushings). Optional mounting nut and locking ring styles and finishes available separately, see section "Technical Data and Additional Hardware".

## **TERMINATIONS** PC THRU-HOLE SP DP .020 THK. (0,51) PC MOUNTING .100 TYP. (2,54) (5,08) .043 DIA. (1,090) TYP. .043 DIA. (1,090) TYP. Omit center holes







Dimensions are shown: Inches (mm) Specifications and dimensions subject to change


## **TERMINATIONS**

RIGHT ANGLE, PC THRU-HOLE







RIGHT ANGLE, PC THRU-HOLE



VERTICAL RIGHT ANGLE, PC THRU-HOLE



NOTE: Terminal bend radii and lead-in manufacturing option.



NOTE: Terminal bend radii and lead-in manufacturing option.




Dimensions are shown: Inches (mm) Specifications and dimensions subject to change




### -0-0-TERMINATIONS -


VERTICAL MOUNT, V-BRACKET



TP11 Models: omit terminal 2.









TP11 Models: omit hole 2.




TP12SH9V3BE SPDT

VERTICAL MOUNT, V-BRACKET











TP21SH9V3BE **DPST** 

## CONTACT MATERIAL

OPTION CODE	CONTACT MATERIAL	TERMINAL PLATING	RATINGS	
В	GOLD <sup>1</sup>	GOLD <sup>1</sup>	LOW LEVEL/DRY CIRCUIT	0.4.VA.MAY @ 00.V.A.O.OB.DO.MAY
Р	GOLD	MATTE-TIN <sup>6</sup>	LOW LEVEL/DAY CIRCUIT	0.4 VA MAX. @ 20 V AC OR DC MAX.
Q	SILVER <sup>4,5</sup>	SILVER <sup>5</sup>	POWER	1 AMP @ 120 V AC OR 28 V DC.
G	GOLD OVER SILVER <sup>2,3</sup>	GOLD <sup>3</sup>	LOW LEVEL/DRY CIRCUIT OR POWER	0.4 VA MAX @ 20 V AC OR DC MAX. OR
R		MATTE-TIN <sup>6</sup>	LOW LEVEL BITT OF TOWER	1 AMP @ 120 V AC OR 28 V DC.

<sup>\*</sup> Note: See Technical Data section of this catalog for RoHS compliant and compatible definitions and specifications.

NOTE: Any models supplied with P, R, Q, B or G contact material are RoHS compliant.


All models , with all options when ordered with R, G, or Q contact material. B contact material standard with A, AV, V3 & W terminations.


Q contact material standard with C & Z terminations

P. R contact materials not available with Z terminations

## SEAL ---

EPOXY SEAL





Dimensions are shown: Inches (mm) Specifications and dimensions subject to change



<sup>&</sup>lt;sup>1</sup> CONTACTS & TERMINALS: Copper alloy, with gold plate over nickel plate.


 $<sup>^{2}</sup>$  END CONTACTS: Coin silver, with gold plate over nickel plate.  $^{\rm 3}$  CENTER CONTACTS & ALL TERMINALS: Copper alloy, with gold plate over nickel plate.

<sup>&</sup>lt;sup>4</sup> END CONTACTS: Coin silver, silver plated.

<sup>&</sup>lt;sup>5</sup> CENTER CONTACT & ALL TERMINALS: Copper alloy, silver plated.

<sup>&</sup>lt;sup>6</sup> TERMINALS: Copper alloy, with matte-tin over nickel plate.

## AVAILABLE HARDWARE




508101000 WHITE 508102000 BLACK

Material: Nylon Finish: Gloss

### Cap, .100" DIA. Plungers (Recommended for S9 plunger) .200 DIA. (5,08)(3,94) .081 (2.06)PART NO. 538701000 WHITE 538702000 BLACK Material: Nylon

Cap, .100" DIA. Plungers




PART NO.

465801000 WHITE 465802000 BLACK

Material: Nylon Finish: Gloss

Cap, .120" DIA. Plungers



PART NO. 708901000 WHITE 708902000


Material: Nylon Finish: Gloss

Cap. .120" DIA. Plungers 1 000° MAX B.015 R.012 .065 ±.005 120 🛆 ø.310 CAVITY ID TUNNEL GATE AS CLOSE 6X 45 ° X .010 CHAMFER OR .010 R. LEAD IN AS POSSIBLE TO THIS SURFACE. PART NO. 891D01000 WHITE 891D02000 BLACK Material: Nylon

PART NO. 484601000 484602000

Finish: Gloss

Cap, J81 option only



WHITE BLACK

Material: Nylon

PART NO. 798201000 WHITE 798202263 BLACK

Material: Nvlon Finish: Matte

NOTE: Additional nuts, locking rings and lockwashers available separately, see section "Technical Data and Additional Hardware" Other cap colors available, consult Customer Service Center.

Frames snap into panel opening and are independent from switch mounting. Accurate positioning of the PC mounted switch relative to the panel opening is necessary to provide proper clearance between actuator and frame. Available in two basic styles and four panel thicknesses .047-.125 in. Material: Nylon. Finish: Matte.

Finish: Gloss

Finish: Gloss

## TYPICAL APPLICATION





.090" (2,29) PANEL THK. .125" (3,18) PANEL THK.

PART NO.


PART NO

432702263


432802263 BLACK

## PANEL MOUNTING

For part numbers 432502263, 432602263



For part numbers 432702263, 432802263



Panel Inserts

LE.D. (.200 DIA. (5 SECURELY INTO INSERT HEIGHT DEPENDS ON PANEL P/N 8949 PANEL W/O L.E.D.

Above frames (part nos. 432XXXXXX) are also available with insert which accepts LED for indicator light assembly. Order insert separately from frame. Blank insert panel (without hole for LED) also available. LED not included.

> PANEL INSERT WITH HOLE FOR LED

BLANK PANEL INSERT WITHOUT HOLE FOR LED

PART NO.

PART NO.

894902000

476602000 BLACK



