Technical Data Sheet

0603 Package Chip LED(0.4mm Height)

Features

- Package in 8mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Mono-color type.
- Pb-free.
- The product itself will remain within RoHS complaint version

Descriptions

- The 19-217 SMD Taping is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

Applications

- Backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.

Device Selection Guide


Part No.	Material	Emitted Color	Lens Color	
19-217/BHC-AN1P2/3T	InGaN	Blue	Water Clear	




19-217/BHC-AN1P2/3T



Package Outline Dimensions





Everlight Electronics Co., Ltd. Device No:SZDSE-197-B01 http://www.everlight.com Prepared date:17-10-2006 19-217/BHC-AN1P2/3T

19-217/BHC-AN1P2/3T

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit	
Reverse Voltage	VR	5	V	
Forward Current	\mathbf{I}_{F}	25	mA	
Peak Forward Current (Duty 1/10 @1KHz)	Ifp	100	mA	
Power Dissipation	Pd	110	mW	
Electrostatic Discharge(HBM)	ESD	150	V	
Operating Temperature	Topr	-40 ~ +85	°C	
Storage Temperature	Tstg	-40 ~ +90	°C	
Soldering Temperature	Tsol	Reflow Soldering:260 $^{\circ}$ C for 10 sec Hand Soldering:350 $^{\circ}$ C for 3 sec		

Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	Iv	28.5		72.0	mcd	
Viewing Angle	$2 \theta 1/2$		120		deg	
Peak Wavelength	λp		468		nm	
Dominant Wavelength	λd	464.5		476.5	nm	I _F =20mA
Spectrum Radiation Bandwidth	$\bigtriangleup \lambda$		35		nm	
Forward Voltage	V_{F}	2.7	3.3	3.7	V	
Reverse Current	I _R			50	$\mu \mathbf{A}$	V _R =5V

Notes:

1.Tolerance of Luminous Intensity ±10%

2.Tolerance of Dominant Wavelength ±1nm

EVERLIGHT ELECTRONICS CO.,LTD.

19-217/BHC-AN1P2/3T

Bin Range Of Dom. Wavelength

EVERLIGHT

Group	Bin	Min	Max	Unit	Condition
A	A9	464.5	467.5	nm	IF=20mA
	A10	467.5	470.5		
	A11	470.5	473.5		
	A12	473.5	476.5		

Bin Range Of Luminous Intensity

Bin	Min	Max	Unit	Condition
N1	28.5	36.0		IF=20mA
N2	36.0	45.0	mcd	
P1	45.0	57.0		
P2	57.0	72.0		


Notes:

1.Tolerance of Luminous Intensity ±10%

2.Tolerance of Dominant Wavelength ±1nm

EVERLIGHT ELECTRONICS CO., LTD.

19-217/BHC-AN1P2/3T



Typical Electro-Optical Characteristics Curves

ÆRLIGHT

Everlight Electronics Co., Ltd. Device No:SZDSE-197-B01 http://www.everlight.com Prepared date:17-10-2006 Rev. 2 Page: 5 of 10 Prepared by: Bian Chang You

19-217/BHC-AN1P2/3T


Label explanation

CAT: Luminous Intensity Rank

- HUE: Dom. Wavelength Rank
- **REF: Forward Voltage Rank**



Reel Dimensions




Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

http://www.everlight.com Prepared date:17-10-2006


19-217/BHC-AN1P2/3T

Carrier Tape Dimensions: Loaded quantity 3000 PCS per reel



Note: The tolerances unless mentioned is ± 0.1 mm ,Unit = mm

Moisture Resistant Packaging



Everlight Electronics Co., Ltd. Device No:SZDSE-197-B01 http://www.everlight.com Prepared date:17-10-2006

19-217/BHC-AN1P2/3T

Reliability Test Items And Conditions

The reliability of products shall be satisfied with items listed below. Confidence level : 90%

LTPD: 10%

No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Reflow Soldering	Temp. : 260°C±5°C Min. 5sec.	6 Min.	22 PCS.	0/1
2	Temperature Cycle	H : +100°C 15min ∫ 5 min L : -40°C 15min	300 Cycles	22 PCS.	0/1
3	Thermal Shock	H: +100°C 5min $\int 10 \sec$ L: -10°C 5min	300 Cycles	22 PCS.	0/1
4	High Temperature Storage	Temp. : 100°C	1000 Hrs.	22 PCS.	0/1
5	Low Temperature Storage	Temp. : -40°C	1000 Hrs.	22 PCS.	0/1
6	DC Operating Life	IF = 20 mA	1000 Hrs.	22 PCS.	0/1
7	High Temperature / High Humidity	85℃/ 85%RH	1000 Hrs.	22 PCS.	0/1

19-217/BHC-AN1P2/3T

Precautions For Use


1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
 - 2.1 Do not open moisture proof bag before the products are ready to use.
 - 2.2 Before opening the package: The LEDs should be kept at 30° C or less and 90%RH or less.
 - 2.3 After opening the package: The LED's floor life is 1 year under 30° C or less and 60% RH or less.

If unused LEDs remain, it should be stored in moisture proof packages.

- 2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.
 Baking treatment : 60±5°C for 24 hours.
- 3. Soldering Condition
- 3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.


19-217/BHC-AN1P2/3T

4.Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350° C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



EVERLIGHT ELECTRONICS CO., LTD. Office: No 25, Lane 76, Sec 3, Chung Yang Rd, Tucheng, Taipei 236, Taiwan, R.O.C *Tel:* 886-2-2267-2000, 2267-9936 *Fax:* 886-2267-6244, 2267-6189, 2267-6306 *http://www.everlight.com*

Everlight Electronics Co., Ltd. Device No:SZDSE-197-B01 http://www.everlight.com Prepared date:17-10-2006 Rev. 2 Page: 10 of 10 Prepared by: Bian Chang You