

PRODUCT SPECIFICATION

SPEC. NO: T-0638-002M

DATE: Aug. 15, 2018

CUSTOMER'S PRODUCT NAME:

EMTEK PRODUCT NAME:

LCD0603-470K-T

THIS SPECIFICATION IS:

- FULLY ACCEPTED
 DENIED
 ACCEPTED UNDER THE FOLLOWING CONDITIONS



SIGNATURE: _____

DATE: _____

NAME(PRINT): _____

TITLE: _____

 **EMTEK CO., LTD.**

本文件內容全部或部份,未經兆欣科技股份有限公司同意不得以任何形式複製或其他用途
All rights reserved.This document or parts thereof,may not be reproduced by any means or used in any manner without written permission of EMTEK CO.,LTD.

FACTORY:

39, Chingao Rd., (305)Hsinpu,
Hsinchu Hsien, Taiwan, R. O. C
TEL: 03-5894-433
FAX: 03-5894-523

PRODUCT SPECIFICATION

SPEC. NO.

T-0638-002M



1. Scope

This specification applies Wire Wound Power Inductors LCD0603-Series to be delivered to user.

2. Product Identification

LCD 0603 -470 □ - T

(1) (2) (3) (4) (5)

(1) Product name

(2) Shapes and dimensions

(3) Inductance


470: 47 uH

(4) Tolerance

K=±10% , M=±20%

(5) Taping Type

3. Shapes and Dimensions



A max. : 1.80 mm


B max. : 1.20 mm

C max. : 1.00 mm

D ref. : 0.45 mm

E : 0.33 mm

Equivalent circuit



No Polarity

Drawn by	Checked by	Approved by
Cindy Jan. 18. 2018	Zheng Jan. 18. 2018	Su Jan. 18. 2018

PRODUCT SPECIFICATION

SPEC. NO.

T-0638-002M



4. Electrical Characteristics

Customer Part Number	Our Product Part Number	Inductance (uH)/MHz	Inductance Tolerance	Q/MHz Typ.	SRF Typ. (MHz)	Rdc ±30% (Ω)	Idc Typ. (mA)	Irms Typ. (mA)	Color Coding
	LCD0603-470□-T	47/2.5	K	12/2.5	11	11.20	100	110	Gray
			M						

1. When ordering, please specify tolerance and packaging codes. Ex: LCD0603-470K-T

Tolerance : K = ±10% , M = ±20%

Packaging : Clear tape and reel {standard}.

2. L , Q 、 SRF : Agilent/HP E4991A+ Agilent/HP 16197A

(The electrical specification test by the smallest gap position) or HP16193A


3. Rdc : DIGITAL MILLIOHM METER Chroma 16502, or equivalent.

4. Idc for Inductance drop 10% from its value without current.

5. Irms for a 15°C rise above 25°C ambient.

6. Operating temperature range from -40°C to 105°C.

1st



COLOR CODING

5. Material list

Item	Material
Core	Ferrite core
Wire	Copper wire
Epoxy	UV Epoxy

PRODUCT SPECIFICATION

SPEC. NO.

T-0638-002M



6. Reliability Test


Item	Specifications	Test conditions
Solderability	The metalized area must have 90% minimum solder coverage.	Dip pads in flux and dip in solder pot(96.5 Sn/3.5 Ag solder) at 255°C ±5°C.
Resistance to soldering heat	There must be no case deformation or change in dimensions. Inductance must not change more than the stated tolerance.	Inductors shall be reflowed onto a PC board using 96.5 Sn/3.5 Ag solder paste. Solder process shall be at a maximum temperature of 260°C. For 96.5 Sn/3.5 Ag solder paste:>217°C for 90 seconds
Vibration	There must be no case deformation or change in dimensions. Inductance must not change more than the stated tolerance.	Solder specimen inductor on the test printed circuit board. Apply vibrations in each of the x,y and z directions for 2 hours for a total of 6 hours. Frequency : 10~50 Hz Amplitude : 1.5mm
High temperature resistance	There must be no case deformation or change in dimensions. Inductance must not change more than the stated tolerance.	Inductors shall be subjected to temperature 105±2°C for 50±12 hours. Measure the test items after leaving the inductors at room temperature and humidity for 2 hours.
Static Humidity	Inductors must not have a shorted or openwinding.	Inductors shall be subjected to temperature 85±2°C and 90 to 95%RH. for ten 24-hours. Measure the test items after leaving the inductors at room temperature and humidity for 2 hours.
Component adhesion (push test)	Inductors shall be subjected to 0.45Kg	Inductors shall be reflow soldered (255°C ±5°C for 10 seconds) to a tinned copper substrate. A force gauge shall be applied to the side of the component. The device must withstand the stated force without a failure of the termination.

PRODUCT SPECIFICATION

SPEC. NO.

T-0638-002M



Item	Specifications	Test conditions
Low temperature resistance	There must be no case deformation or change in dimensions. Inductance must not change more than the stated tolerance.	Inductors shall be subjected to temperature $-40\pm 2^{\circ}\text{C}$ for 48 ± 12 hours. Measure the test items after leaving the inductors at room temperature and humidity for 1 to 2 hours.
Resistance to solvent	There must be no case deformation, change in dimensions, or obliteration of marking.	Inductors must withstand 6 minutes of alcohol or water.
Thermal cycle	There must be no case deformation or change in dimensions. Inductance must not change more than the stated tolerance.	Inductors shall be subjected to 5 cycles to the the following temperature cycle: <div style="text-align: center;">  <p>The diagram illustrates a single temperature cycle. It starts at a baseline, drops to -40°C and remains there for 30 minutes. It then ramps up to $+105^{\circ}\text{C}$ in 3 minutes, stays at $+105^{\circ}\text{C}$ for 30 minutes, and then ramps down back to the baseline. The total duration of one cycle is indicated as 1 cycle.</p> </div> Measure the test items after leaving the inductors at room temperature and humidity for 2 hours.



PRODUCT SPECIFICATION


SPEC. NO.

T-0638-002M

7. Packaging

The packaging must be done not to receive any damage during transporting and storing.


7-1 Tape dimensions



(Dimensions in mm; Tolerance : ±0.1)

Symbol	W	P	P ₀	P ₁	A _o	B _o	K _o	t
Dimension	8	4	4	2	1.25	1.9	1.05	0.22


7-2 Reel dimensions



(Dimensions in mm)

Symbol	T
A	180
B	60
C	13
D	14.4
E	8.4

7-3 Tapping figure



PRODUCT SPECIFICATION


SPEC. NO.

T-0638-002M



7-4 Packaging Form

There shall not continuation more than two vacancies of the product.




7-5 Cover Tape Peel Strength

The force for tearing off cover tape is 0.1~0.6(N) in the arrow direction at the following conditions:

Temperature : 5 ~ 35°C

Humidity : 45 ~ 85%

Atmospheric pressure : 860 ~ 1060 hpa



7-6 Packing Quantity

φ180 mm reel type : 4,000 pcs./reel

PRODUCT SPECIFICATION


SPEC. NO.

T-0638-002M



8. Recommended Soldering Conditions (Please use this product by reflow soldering)


8-1 Recommended Footprint



Unit: mm

8-2 Recommended Reflow Pattern

Reflow : until two times



8-3 Iron Soldering

Use a solder iron of less than 30W when soldering, do not allow the soldering iron tip directly touch the Ceramic body outside of terminal electrode.

5 seconds max. at 260°C.

9. Attention in Case of Using

In case of using product, please avoid following matters:

Splashing water or salt water

Dew condenses

Toxic gas (Hydrogen sulfide, Sulfurous acid, Chlorine, Ammonia)

Vibrations or shocks which exceed the specified condition

Please be careful for the stress to this product by board flexure or something after the mounting.

10. Others

10-1 Operating temperature range : Ferrite Series : -40~+105°C

10-2 Storage condition : Temperature 20°~25°C, Relative Humidity 40%~60%

10-3 Recommended wire wound inductors should be used within 6 months from the time of delivery.