Axial Lead & Cartridge Fuses

5×20 mm > Medium-Acting > 232 Series



Rohs 🔞 (E 🎨 🏼

232 Series, 5×20 mm, Medium-Acting Fuse



Agency Approvals

Agency	Agency File Number	Ampere Range
RS L	Cartridge: NBK180509-JP1021 A/C NBK020609-JP1021 A/C Leaded: NBK180509-JP1021 B/D NBK020609-JP1021 B/D	1A – 5A 6.3A – 10A 1A – 5A 6.3A – 10A
Ĩ.	SU05001-2015	1A – 10A
Œ	N/A	1A – 10A

Electrical Characteristics for Series

% of Ampere Rating	OpeningTime		
130%	1 hour, Minimum		
160%	1 hour, Maximum		
200%	2 minutes, Maximum		

Electrical Characteristic Specifications by Item

Description

The 232 Series Fuse is a 5x20mm, medium-acting, glass body cartridge fuse. It is specifically designed to meet the requirements of Appendix 3 of METI/PSE.

Features

- Available in cartridge and axial lead format
- RoHS compliant and lead-free

Applications

Used as supplementary protection in appliance or utilization equipment to provide individual protection for components or internal circuits.

Additional Information







For recommended fuse accessories for this product series, see '<u>Recommended Accessories</u>' section.

				Nominal Cold	Nominal	Agency Approvals		
Amp Code	Amp Rating Voltage Rating Interrupting (A) (V) Rating	Resistance (Ohms)	Melting I ² t (A ² sec)		ß	Œ		
001.	1	125/250		0.0923	1.37300	х	х	х
1.25	1.25	125/250	10 kA @ 125VAC	0.0685	4.11000	х	х	x
01.6	1.6	125/250		0.0537	6.96000	x	х	x
002.	2	125/250		0.0370	8.25000	х	х	x
02.5	2.5	125/250		0.0291	13.87500	х	х	x
003.	3	125/250		0.0226	17.19000	x	х	x
3.15	3.15	125/250		0.0215	21.9500	x	х	x
004.	4	125/250		0.0174	37.73000	х	х	x
005.	5	125/250		0.0134	56.72000	х	х	x
06.3	6.3	125/250		0.0102	151.54000	х	х	x
008.*	8	125/250	300A @ 125VAC	0.0076	182.58000	х	х	x
010.*	10	125/250		0.0059	290.66500	х	х	x

To order 125Vac rated, please add part no. suffix

* Interrupting Rating for 8A & 10A is 100A@250Vac

© 2016 Littelfuse, Inc.


Specifications are subject to change without notice. Application testing is strongly recommended. Revised: 07/26/16



Axial Lead & Cartridge Fuses

5×20 mm > Medium-Acting > 232 Series


Temperature Re-rating Curve




Note:

Rerating depicted in this curve is in addition to the standard derating of 25% for continuous operation.

Average Time Current Curves



Soldering Parameters - Wave Soldering



Recommended Process Parameters:

Wave Parameter	Lead-Free Recommendation		
Preheat:			
(Depends on Flux Activation Temperature)	(Typical Industry Recommendation)		
Temperature Minimum:	100°C		
Temperature Maximum:	150°C		
Preheat Time:	60-180 seconds		
Solder PotTemperature:	260°C Maximum		
Solder Dwell Time:	2-5 seconds		

Recommended Hand-Solder Parameters:

Solder Iron Temperature: 350°C +/- 5°C Heating Time: 5 seconds max.

Note: These devices are not recommended for IR or Convection Reflow process.

Axial Lead & Cartridge Fuses

5×20 mm > Medium-Acting > 232 Series



Product Characteristics

Materials	Body: Glass Cap: Nickel–plated brass Leads: Tin–plated Copper
Terminal Strength	MIL-STD-202, Method 211. Test Condition A
Solderability	MIL-STD-202 Method 208
Product Marking	Cap 1: Brand log, current and voltage ratings, and agency approval Cap 2: Blank
Packaging	Available in Bulk (M=1000 pcs/pkg) or on Tape/Reel (MRET1=1000 pcs/reel)

← 20<u>+</u>0.5 →

5.1<u>+</u>0.6

5.1<u>+</u>0.6

0 65+0 05

40±1.0 ← 21.5±1.0 →

5.2+0.1


-0.2

All dimensions in mm

- 5.5±0.3

Operating Temperature	-55°C to +125°C
Thermal Shock	MIL-STD-202, Method 107, Test Condition B: (5 cycles $-65^{\circ}C + 125^{\circ}C$)
Vibration	MIL-STD-202, Method 201
Humidity	MIL-STD-202, Method 103, Test Condition A high RH (95%) and elevated temperature (40° C) for 240 hours.
Salt Spray	MIL-STD-202, Method 101, Test Condition B

Part Numbering System



Notes:

Dimensions

0232 000P

0232 000 XEP

* Ratings above 6.3A have 0.8±0.05 diameter lead.

Packaging

Packaging Option	ckaging Option Packaging Specification Quantity Quantity & Packaging Code Ta		Taping Width	
232 Series				
Bulk	N/A	1000	MX	N/A
Bulk	N/A	1000	MXE	N/A

Recommended Accessories

Accessory Type	Series	Description	Max Application Voltage	Max Application Amperage
	<u>345_ISF</u>	Panel Mount Shock-Safe Fuseholder		10
Holder	<u>345</u>	Shock-Safe Fuseholder with PC Mount, Solder Mount and Panel Mount options		20
830		PC Mount Shock-Safe Miniature Fuseholder		16
	<u>520</u>	Metric OMNI-BLOK® Fuse Block		10
Block <u>646</u>		PC Mount Miniature Fuse Block	250	6.3
<u>658</u>	<u>658</u>	Surface Mount Miniature Fuse Block		10
<u>520_W</u>		PC Mount Miniature Fuse Clip		6.3
Clip	<u>111</u>	PC Board Mount Fuse Clip		10
-	<u>445</u>	PC Board Mount Fuse Clip		10

Notes: 1. Do not use in applications above rating. 2. Please refer to fuseholder data sheet for specific re-rating information.

3. Please contact factory for applications greater than the max voltage and amperage shown.

© 2016 Littelfuse, Inc. Specifications are subject to change without notice. Revised: 07/26/16