



DUAL-IN-LINE GLASS PASSIVATED SINGLE-PHASE BRIDGE RECTIFIER

VOLTAGE 50 to 1000 Volts CURRENT 1.5 Amperes

R


Recongnized File #E111753

FEATURES

- Plastic material used carries Underwriters Laboratory recognition 94V-O
- · Low leakage
- Surge overload rating-- 50 amperes peak
- · Ideal for printed circuit board
- Exceeds environmental standards of MIL-S-19500/228
- · Lead free in comply with EU RoHS 2011/65/EU directives
- Green molding compound as per IEC61249 Std. . (Halogen Free)

MECHANICAL DATA

- Case: Reliable low cost construction utilizing molded plastic technique results in inexpensive product
- Terminals: Lead solderable per MIL-STD-750, Method 2026
- Polarity: Polarity symbols molded or marking on body
- Mounting Position: Any
- Weight: 0.02 ounce, 0.4 gram



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz, Resistive or inductive load. For capacitive load, derate current by 20%

PARAMETER	SYMBOL	DI150	DI151	DI152	DI154	DI156	DI158	DI1510	UNITS
Maximum Recurrent Peak Reverse Voltage	V _{RRM}	50	100	200	400	600	800	1000	V
Maximum RMS Bridge Input Voltage	V _{RMS}	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V _{DC}	50	100	200	400	600	800	1000	٧
Maximum Average Forward Current T _A =40°C	I _{F(AV)}	1.5							Α
Peak Forward Surge Current : 8.3ms single half sinewave superimposed on rated load (JEDEC method)	I _{FSM}	50							А
I^2 t Rating for fusing (t<8.35ms)	I²t	10						A²t	
Maximum Forward Voltage Drop per Bridge Element at 1.0A	V _F 1.1						V		
Maximum DC Reverse Current T _J =25 °C at Rated DC Blocking VoltageT _J =125 °C	I _R	5.0 500					uA		
Typical Junction capacitance (Note 1)	C¹	25						pF	
Typical thermal resistance per leg ((Note 2)	R _{eJA} R _{eJL}	40 15						°C / W	
Operating and Storage Temperature Range	TJ	-55 to + 125					°C		
Storage Temperature Range	T _{STG}	-55 to + 150					°C		

NOTES:

- 1. Measured at 1.0 MHz and applied reverse voltage of 4.0 Volts
- 2. Thermal resistance from junction to ambient and from junction to lead mounted on P.C.B. with 0.5 X 0.5"(13 X 13mm) copper pads

STAD-APR.19.2007 PAGE . 1





RATING AND CHARACTERISTIC CURVES




FIG.1 DERATING CURVE FOR OUTPUT RECTIFIED CURRENT





FIG.2 TYPICAL FORWARD CHARACTERISTICS








FIG.4 MAX NON-REPETITIVE SURGE CURRENT

STAD-APR.19.2007 PAGE . 2





Part No_packing code_Version

DI150_T0_00001

For example: RB500V-40_R2_00001 **Serial number** Part No.

Version code means HF

Packing size code means 13"

Packing type means T/R

Packing Code XX				Version Code XXXXX			
Packing type	1 st Code	Packing size code	2 nd Code	HF or RoHS	1 st Code	2 nd ~5 th Code	
Tape and Ammunition Box (T/B)	Α	N/A	0	HF	0	serial number	
Tape and Reel (T/R)	R	7"	1	RoHS	1	serial number	
Bulk Packing (B/P)	В	13"	2				
Tube Packing (T/P)	Т	26mm	X				
Tape and Reel (Right Oriented) (TRR)	S	52mm	Y				
Tape and Reel (Left Oriented) (TRL)	L	PANASERT T/B CATHODE UP (PBCU)	U				
FORMING	F	PANASERT T/B CATHODE DOWN (PBCD)	D				

STAD-APR.19.2007 PAGE . 3





Disclaimer

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties
 of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation.
 Customers are responsible in comprehending the suitable use in particular applications.
 Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.

STAD-APR.19.2007 PAGE . 4