
### **Spec Sheet**

# Wire-wound Chip Power Inductors (CB series)

## CBMF1608T4R7M



#### Features

- Item Summary
  4.7uH±20%, 0.145A, 0603/1608 (EIA/JIS)
- Lifecycle Stage

Mass Production

Standard packaging quantity (minimum)
 Taping Embossed 3000pcs

#### ■ Products characteristics table

Inductance	4.7 uH ± 20 %
Case Size (EIA/JIS)	0603/1608
Rated Current (max)	0.145 A
Saturation Current (max)	0.145 A
Temperature Rise Current (max)	0.47 A
DC Resistance (max)	0.312 Ω
DC Resistance (typ)	0.24 Ω
LQ Measuring Frequency	7.96 MHz
Self Resonant Frequency (min)	45 MHz
Operating Temp. Range	-40 to +105 ℃ (Including-self-generated heat)
Temperature characteristic (Inductance change)	± 25 %
RoHS2 Compliance (10 subst.)	Yes
REACH Compliance (168 subst.)	Yes
Soldering	Reflow

#### ■ External Dimensions

Dimension L	1.6 ±0.2 mm
Dimension W	0.8 ±0.2 mm
Dimension T	0.8 ±0.2 mm
Dimension e	0.45 ±0.15 mm

2017.01.02

## Wire-wound Chip Power Inductors (CB series)

#### CBMF1608T4R7M



Dimension unit : mm unit: inch Length: 1.6 + / - 0.2(0.063 + / - 0.008)Width: 0.8 + / - 0.2(0.031 + / - 0.008)0.8 + / - 0.2Height: (0.031 + / - 0.008)

Inductance: 4.7 uH (test freq at 7.96MHz) DC Resistance: 0.312 ohm (typ/max)

Saturation Current: 145 mA ( max ) 470 mA ( max ) Temp. rise Current:

> Saturation current typical: 30% reduction from initial L value. Temp rise Current typical: Temperature will rise by 40 deg C

