MAX6895-MAX6899

Ultra-Small, Adjustable Sequencing/ Supervisory Circuits

General Description

The MAX6895–MAX6899 is a family of small, low-power, voltage-monitoring circuits with sequencing capability. These miniature devices offer tremendous flexibility with an adjustable threshold capable of monitoring down to 0.5V and an external capacitor-adjustable time delay. These devices are ideal for use in power-supply sequencing, reset sequencing, and power-switching applications. Multiple devices can be cascaded for complex sequencing applications.

A high-impedance input with a 0.5V threshold allows an external resistive divider to set the monitored threshold. The output asserts (OUT = high or \overline{OUT} = low) when the input voltage rises above the 0.5V threshold and the enable input is asserted (ENABLE = high or ENABLE = low). When the voltage at the input falls below 0.5V or when the enable input is deasserted (ENABLE = low or \overline{ENABLE} = high), the output deasserts (OUT = low or OUT = high). All devices provide a capacitor-programmable delay time from when the input rises above 0.5V to when the output is asserted. The MAX689 A versions provide the same capacitor-adjustable delay from when enable is asserted to when the output asserts. The MAX689_P devices have a 1µs propagation delay from when enable is asserted to when the output asserts.

The MAX6895A/P offers an active-high enable input and an active-high push-pull output. The MAX6896A/P offers an active-low enable input and an active-low push-pull output. The MAX6897A/P offers an active-high enable input and an active-high open-drain out-put. Finally, the MAX6898A/P offers an active-low enable input and an active-low open-drain output. The MAX6899A/P offers an active-low enable with an active-high push-pull output.

All devices operate from a 1.5V to 5.5V supply voltage and are fully specified over the -40°C to +125°C operating temperature range. These devices are available in ultra-small 6-pin μ DFN (1.0mm x 1.5mm) and thin SOT23 (1.60mm x 2.90mm) packages.

Applications

- Automotive
- Medical Equipment
- Intelligent Instruments
- Portable Equipment
- Computers/Servers
- Critical µP Monitoring
- Set-Top Boxes
- Telecom

Typical Operating Circuit and Selector Guide appear at end of data sheet.

Features

- 1.8% Accurate Adjustable Threshold Over Temperature
- Operate from V_{CC} of 1.5V to 5.5V
- Capacitor-Adjustable Delay
- Active-High/-Low Enable Input Options
- Active-High/-Low Output Options
- Open-Drain (28V Tolerant)/Push-Pull Output Options
- Low Supply Current (10µA, typ)
- Fully Specified from -40°C to +125°C
- Ultra-Small 6-Pin μDFN Package or Thin SOT23 Package


Ordering Information

PART	PIN-PACKAGE	TOP MARK
MAX6895AALT+	6 μDFN	+AW
MAX6895AAZT+	6 Thin SOT23	+AADK
MAX6895PALT+T	6 μDFN	+AX
MAX6895PAZT+	6 Thin SOT23	+AADL
MAX6896AALT+	6 μDFN	+AY
MAX6896AAZT+	6 Thin SOT23	+AADO
MAX6896AAZT/V+T	6 Thin SOT23	+AATA
MAX6896PALT+T	6 μDFN	+AZ
MAX6896PAZT+	6 Thin SOT23	+AADP
MAX6896PAZT/V+T	6 Thin SOT23	_

Note: All devices are specified over the -40°C to +125°C operating temperature range.

Ordering Information continued at end of data sheet.

Pin Configurations





MAX6895-MAX6899

Ultra-Small, Adjustable Sequencing/ Supervisory Circuits

Absolute Maximum Ratings

V _{CC} , ENABLE, ENABLE, IN0.3V to +6V	Operating Temperature Range40°C to +125°C
OUT, OUT (push-pull)0.3V to (V _{CC} + 0.3V)	Storage Temperature Range65°C to +150°C
OUT, OUT (open-drain)0.3V to +30V	Junction Temperature+150°C
CDELAY0.3V to (V _{CC} + 0.3V)	Lead Temperature (soldering, 10s)+300°C
Output Current (all pins)±20mA	Soldering Temperature (reflow)+260°C
Continuous Power Dissipation (T _A = +70°C)	
6-Pin µDFN (derate 2.1mW/°C above +70°C)167.7mW	
6-Pin Thin SOT23 (derate 9.1mW/°C above +70°C)727.3mW	

Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Package Thermal Characteristics (Note 1)

· donage		(
UDEN		

Junction-to-Ambient Thermal Resistance (θ_{JA}).......477°C/W Junction-to-Case Thermal Resistance (θ_{JC})..........122C/W

Thin SOT23

Junction-to-Ambient Thermal Resistance (θ_{JA})......110°C/W Junction-to-Case Thermal Resistance (θ_{JC}).....50°C/W

Note 1: Package thermal resistances were obtained using the method described in JEDEC specification JESD51-7, using a four layer board. For detailed information on package thermal considerations refer to www.maximintegrated.com/thermal-tutorial.

Electrical Characteristics

(V_{CC} = 1.5V to 5.5V, T_A = -40°C to +125°C, unless otherwise specified. Typical values are at V_{CC} = 3.3V and T_A = +25°C, unless otherwise noted.) (Note 2)

PARAMETER	SYMBOL	CONDITIONS	MIN	TYP	MAX	UNITS
SUPPLY						
Operating Voltage Range	V _{CC}		1.5		5.5	V
Undervoltage Lockout (Note 3)	UVLO	V _{CC} falling	1.20		1.35	V
V _{CC} Supply Current	Icc	V _{CC} = 3.3V, no load		10	20	μA
IN						
Threshold Voltage	V _{TH}	V _{IN} rising, 1.5V < V _{CC} < 5.5V	0.491	0.5	0.509	٧
Hysteresis	V _{HYST}	V _{IN} falling		5		mV
Input Current (Note 4)	I _{IN}	V _{IN} = 0V or V _{CC}	-15		+15	nA
CDELAY						
Delay Charge Current	I _{CD}		200	250	300	nA
Delay Threshold	V _{TCD}	CDELAY rising	0.95	1.00	1.05	V
CDELAY Pulldown Resistance	R _{CDELAY}			130	500	Ω
ENABLE/ENABLE						
Input Low Voltage	V _{IL}				0.4	V
Input High Voltage	V _{IH}		1.4			V
Input Leakage Current	I _{LEAK}	ENABLE, ENABLE = V _{CC} or GND	-100		+100	nA

Electrical Characteristics (continued)

 $(V_{CC} = 1.5V \text{ to } 5.5V, T_A = -40^{\circ}\text{C} \text{ to } +125^{\circ}\text{C}, \text{ unless otherwise specified.}$ Typical values are at $V_{CC} = 3.3V$ and $T_A = +25^{\circ}\text{C}, \text{ unless otherwise specified.}$ otherwise noted.) (Note 2)

PARAMETER	SYMBOL		CONDI	TIONS	MIN	TYP	MAX	UNITS
OUT/OUT								
Output Low Voltage (Open-Drain			_{CC} ≥ 1.2V, I _{SINK} = 90μA, AX6895/MAX6897/MAX6899 only				0.3	
or Push-Pull)	V _{OL}	V _{CC} ≥ 2.25V,	I _{SINK} = 0	.5mA			0.3	V
		V _{CC} ≥ 4.5V, I _S	SINK = 1n	nA			0.4	
Output High Voltage (Push Pull)	V	V _{CC} ≥ 2.25V,	I _{SOURCE}	= 500μΑ	0.8 x V _{CC}			\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \
Output High Voltage (Push-Pull)	V _{OH}	V _{CC} ≥ 4.5V, I _S	SOURCE	= 800μΑ	0.8 x V _{CC}			V
Output Open-Drain Leakage Current	I _{LKG}	Output high im	npedance	e, V _{OUT} = 28V			1	μA
TIMING								
	tDELAY	V _{IN} rising	C _{CDELA}	_{.Υ} = 0μF		40		μs
IN to OUT/OUT Propagation Delay		C _{CDELAY} = 0.047µF			190		ms	
,	t _{DL}	V _{IN} falling				16		μs
Startup Delay (Note 5)						2		ms
ENABLE/ENABLE Minimum Input Pulse Width	t _{PW}				1			μs
ENABLE/ENABLE Glitch Rejection						100		ns
ENABLE/ENABLE to OUT/OUT Delay	t _{OFF}	From device enabled to device disabled			150		ns	
	t _{PROPP}	From device disabled to device enabled (P version)			150		ns	
ENABLE/ENABLE to OUT/OUT Delay		From device disabled		C _{CDELAY} = 0μF		20		μs
belay	t _{PROPA} to device enabled (A version)			C _{CDELAY} = 0.047µF		190		ms


Note 2: All devices are production tested at $T_A = +25^{\circ}C$. Limits over temperature are guaranteed by design. Note 3: When V_{CC} falls below the UVLO threshold, the outputs will deassert (OUT goes low, \overline{OUT} goes high). When V_{CC} falls below 1.2V, the out cannot be determined.

Note 4: Guaranteed by design.

Note 5: During the initial power-up, V_{CC} must exceed 1.5V for at least 2ms before the output is guaranteed to be in the correct

Typical Operating Characteristics

(V_{CC} = 3.3V and T_A = +25°C, unless otherwise noted.)



Pin Description

	PIN						
1	6895/ (6897	1	6896/ 6898	MAX	(6899	NAME	FUNCTION
μDFN	THIN SOT23	μDFN	THIN SOT23	μDFN	THIN SOT23		
1	1	_	_	_	_	ENABLE	Active-High Logic-Enable Input. Drive ENABLE low to immediately deassert the output to its false state (OUT = low or $\overline{\text{OUT}}$ = high) independent of V_{IN} . With V_{IN} above V_{TH} , drive ENABLE high to assert the output to its true state (OUT = high or $\overline{\text{OUT}}$ = low) after the adjustable delay period (MAX689_A) or a 150ns propagation delay (MAX689_P).
_	_	1	1	1	1	ENABLE	Active-Low Logic-Enable Input. Drive $\overline{\text{ENABLE}}$ high to immediately deassert the output to its false state (OUT = low or $\overline{\text{OUT}}$ = high) independent of V _{IN} . With V _{IN} above V _{TH} , drive $\overline{\text{ENABLE}}$ low to assert the output to its true state (OUT = high or $\overline{\text{OUT}}$ = low) after the adjustable delay period (MAX689_A) or a 150ns propagation delay (MAX689_P).
2	2	2	2	2	2	GND	Ground
3	3	3	3	3	3	IN	High-Impedance Monitor Input. Connect IN to an external resistive divider to set the desired monitored threshold. The output changes state when $V_{\rm IN}$ rises above 0.5V and when $V_{\rm IN}$ falls below 0.495V.
4	4	_	_	4	4	OUT	Active-High Sequencer/Monitor Output, Push-Pull (MAX6895/MAX6899) or Open-Drain (MAX6897). OUT is asserted to its true state (OUT = high) when V_{IN} is above V_{TH} and the enable input is in its true state (ENABLE = high or ENABLE = low) for the capacitor-adjusted delay period. OUT is deasserted to its false state (OUT = low) immediately after V_{IN} drops below V_{TH} - 5mV or the enable input is in its false state (ENABLE = low or ENABLE = high). The open-drain version requires an external pullup resistor.
_	_	4	4	_	_	OUT	Active-Low Sequencer/Monitor Output, Push-Pull (MAX6896) or Open-Drain (MAX6898). OUT is asserted to its true state (\overline{OUT} = low) when V_{IN} is above V_{TH} and the enable input is in its true state (ENABLE = high or \overline{ENABLE} = low) after the CDELAY adjusted timeout period. OUT is deasserted to its false state (\overline{OUT} = high) immediately after V_{IN} drops below V_{TH} - 5mV or the enable input is in its false state (ENABLE = low or \overline{ENABLE} = high). The open-drain version requires an external pullup resistor.
5	6	5	6	5	6	CDELAY	Capacitor-Adjustable Delay. Connect an external capacitor (C_{CDELAY}) from CDELAY to GND to set the IN to OUT (and ENABLE to OUT or ENABLE to OUT for A version devices) delay period. t_{DELAY} = (C_{CDELAY} x 4.0 x 10 ⁶) + 40µs. There is a fixed short delay (40µs, typ) for the output deasserting when V_{IN} falls below VTH.
6	5	6	5	6	5	V _{CC}	Supply Voltage Input. Connect a 1.5V to 5.5V supply to V_{CC} to power the device. For noisy systems, bypass with a 0.1µF ceramic capacitor to GND.




Figure 1. MAX6895/MAX6899 Functional Diagram

Detailed Description

The MAX6895–MAX6899 is a family of ultra-small, low-power, sequencing/supervisory circuits. These devices provide adjustable voltage monitoring for inputs down to 0.5V. They are ideal for use in power-supply sequencing, reset sequencing, and power-switching applications. Multiple devices can be cascaded for complex sequencing applications.

Voltage monitoring is performed through a high-impedance input (IN) with an internally fixed 0.5V threshold. When the voltage at IN falls below 0.5V or when the enable input is deasserted (ENABLE = low or $\overline{\text{ENABLE}}$ = high), the output deasserts (OUT goes low or $\overline{\text{OUT}}$ goes high). When VIN rises above 0.5V and the enable input is asserted (ENABLE = high or $\overline{\text{ENABLE}}$ = low), the output asserts (OUT goes high or OUT goes low) after a capacitor-programmable time delay.

With VIN above 0.5V, the enable input can be used to turn the output on or off. After the enable input is asserted, the output turns on with a capacitor-programmable delay period (A version) or with a 150ns propagation delay (P version). Tables 1, 2, and 3 detail the output state depending on the various input and enable conditions.

Table 1. MAX6895/MAX6897 Output

IN	ENABLE	OUT
$V_{IN} < V_{TH}$	Low	Low
V _{IN} < V _{TH}	High	Low
$V_{IN} > V_{TH}$	Low	Low
		OUT = V _{CC} (MAX6895)
$V_{IN} > V_{TH}$	High	OUT = high Impedance (MAX6897)

Table 2. MAX6896/MAX6898 Output

IN	ENABLE	OUT
		$\overline{OUT} = V_{CC} (MAX6896)$
$V_{IN} < V_{TH}$	Low	OUT = high impedance (MAX6898)
		$\overline{OUT} = V_{CC} (MAX6896)$
$V_{IN} < V_{TH}$	High	OUT = high impedance (MAX6898)
$V_{IN} > V_{TH}$	Low	Low
V _{IN} > V _{TH}		$\overline{OUT} = V_{CC} (MAX6896)$
	High	OUT = high impedance (MAX6898)

Table 3. MAX6899 Output

IN	ENABLE	OUT
V _{IN} < V _{TH}	Low	Low
V _{IN} < V _{TH}	High	Low
$V_{IN} > V_{TH}$	Low	High
V _{IN} > V _{TH}	High	Low

Supply Input (V_{CC})

The device operates with a V_{CC} supply voltage from 1.5V to 5.5V. To maintain a 1.8% accurate threshold, VCC must be above 1.5V. When V_{CC} falls below the UVLO threshold, the output deasserts. When V_{CC} falls below 1.2V the output state cannot be determined. For noisy systems, connect a 0.1µF ceramic capacitor from V_{CC} to GND as close to the device as possible. For the push-pull active-high output option, a 100k Ω external pulldown resistor to ground ensures the correct logic state for V_{CC} down to 0.

Ultra-Small, Adjustable Sequencing/ Supervisory Circuits

Monitor Input (IN)

Connect the center point of a resistive divider to IN to monitor external voltages (see R1 and R2 of the *Typical Operating Circuit*). IN has a rising threshold of $V_{TH} = 0.5V$ and a falling threshold of 0.495V (5mV hysteresis). When V_{IN} rises above V_{TH} and \overline{ENABLE} is high (or \overline{ENABLE} is low) OUT goes high (OUT goes low) after the programmed t_{DELAY} period. When V_{IN} falls below 0.495V, OUT goes low (OUT goes high) after a 16 μ s delay. IN has a maximum input current of 15nA so large-value resistors are permitted without adding significant error to the resistive divider.

Adjustable Delay (CDELAY)

When V_{IN} rises above V_{TH} with ENABLE high (ENABLE low), the internal 250nA current source begins charging an external capacitor connected from CDELAY to GND. When the voltage at CDELAY reaches 1V, the output

asserts (OUT goes high or $\overline{\text{OUT}}$ goes low). When the output asserts, C_{CDELAY} is immediately discharged. Adjust the delay (t_{DELAY}) from when V_{IN} rises above V_{TH} (with ENABLE high or $\overline{\text{ENABLE}}$ low) to OUT going high ($\overline{\text{OUT}}$ going low) according to the equation:

$$t_{DELAY} = C_{CDELAY} \times 4.0 \times 10^6 + 40 \mu s$$

where $C_{\mbox{\scriptsize CDELAY}}$ is the external capacitor from CDELAY to GND.

For adjustable delay devices (A version), when $V_{\text{IN}} > 0.5 \text{V}$ and ENABLE goes from low to high (ENABLE goes from high to low) the output asserts after a t_{DELAY} period. For nonadjustable delay devices (P version) there is a 1µs propagation delay from when the enable input is asserted to when the output asserts. Figures 2 through 5 show the timing diagrams for the adjustable and fixed delay versions, respectively.




Figure 2. MAX6895A/MAX6897A Timing Diagram




Figure 3. MAX6896A/MAX6898A Timing Diagram




Figure 4. MAX6895P/MAX6897P Timing Diagram




Figure 5. MAX6896P/MAX6898P Timing Diagram




Figure 6. MAX6899A Timing Diagram




Figure 7. MAX6899P Timing Diagram

Enable Input (ENABLE or ENABLE)

The MAX6895/MAX6897 offer an active-high enable input (ENABLE), while the MAX6896/MAX6898/MAX6899 offer an active-low enable input (ENABLE). With V_{IN} above V_{TH} , drive ENABLE high (ENABLE low) to force OUT high (OUT low) after the adjustable delay time (A versions). For P version devices, when $V_{IN} > 0.5 \text{V}$ and enable is asserted, the output asserts after typically 150ns.

The enable input has logic-high and logic-low voltage thresholds of 1.4V and 0.4V, respectively. For both versions, when V_{IN} > 0.5V, drive ENABLE low (ENABLE high) to force OUT low (OUT high) within 150ns typ.

Output (OUT or OUT)

The MAX6895/MAX6899 offer an active-high, push-pull output (OUT), and the MAX6896 offers an active-low push-pull output ($\overline{\text{OUT}}$). The MAX6897 offers an active-high open-drain output (OUT), and the MAX6898 offers an active-low open-drain output ($\overline{\text{OUT}}$).

Push-pull output devices are referenced to V_{CC} . Open-drain outputs can be pulled up to 28V.

Applications Information

Input Threshold

The MAX6895–MAX6899 monitor the voltage on IN with an external resistive divider (see R1 and R2 in the *Typical Operating Circuit*). Connect R1 and R2 as close to IN as possible. R1 and R2 can have very high values to minimize current consumption due to low IN leakage currents (± 15 nA max). Set R2 to some conveniently high value (1M Ω , for example) and calculate R1 based on the desired monitored voltage using the following formula:

$$R1 = R2 \times \left[\frac{V_{MONITOR}}{V_{IN}} - 1 \right] *$$

where $V_{MONITOR}$ is the desired monitored voltage and V_{IN} is the detector input threshold (0.5V).

Ultra-Small, Adjustable Sequencing/ Supervisory Circuits

Pullup Resistor Values (MAX6897/MAX6898)

The exact value of the pullup resistors for the open-drain outputs is not critical, but some consideration should be made to ensure the proper logic levels when the device is sinking current. For example, if $V_{CC}=2.25V$ and the pullup voltage is 28V, you would try to keep the sink current less than 0.5mA as shown in the *Electrical Characteristics* table. As a result, the pullup resistor should be greater than $56k\Omega$. For a 12V pullup, the resistor should be larger than $24k\Omega$. It should be noted that the ability to sink current is dependent on the V_{CC} supply voltage.

Typical Application Circuits

Figures 8, 9, 10 show typical applications for the MAX6895–MAX6899. Figure 8 shows the MAX6895

3.3V ALWAYS ON

O TO 28V

ENABLE

OUT

MAX6897

IN

CDELAY

GND

Figure 8. Overvoltage Protection

used with a p-channel MOSFET in an overvoltage protection circuit. Figure 9 shows the MAX6895 in a low-voltage sequencing application using an n-channel MOSFET. Figure 10 shows the MAX6895 used in a multiple-output sequencing application.

Using an n-Channel Device for Sequencing

In higher power applications, using an n-channel device reduces the loss across the MOSFETs as it offers a lower drain-to-source on-resistance. However, an n-channel MOSFET requires a sufficient VGS voltage to fully enhance it for a low RDS_ON. The application in Figure 9 shows the MAX6895 in a switch sequencing application using an n-channel MOSFET.

Similarly, if a higher voltage is present in the system, the open-drain version can be used in the same manner.




Figure 9. Low-Voltage Sequencing Using an n-Channel MOSFET




Figure 10. Multiple-Output Sequencing

Selector Guide


PART	ENABLE INPUT	OUTPUT	INPUT (IN) DELAY	ENABLE DELAY
MAX6895AALT+T	Active-High	Active-High, Push-Pull	Capacitor Adjustable	Capacitor Adjustable
MAX6895AAZT+T	Active-High	Active-High, Push-Pull	Capacitor Adjustable	Capacitor Adjustable
MAX6895PALT+T	Active-High	Active-High, Push-Pull	Capacitor Adjustable	150ns Delay
MAX6895PAZT+T	Active-High	Active-High, Push-Pull	Capacitor Adjustable	150ns Delay
MAX6896AALT+T	Active-Low	Active-Low, Push-Pull	Capacitor Adjustable	Capacitor Adjustable
MAX6896AAZT+T	Active-Low	Active-Low, Push-Pull	Capacitor Adjustable	Capacitor Adjustable
MAX6896PALT+T	Active-Low	Active-Low, Push-Pull	Capacitor Adjustable	150ns Delay
MAX6896PAZT+T	Active-Low	Active-Low, Push-Pull	Capacitor Adjustable	150ns Delay
MAX6897AALT+T	Active-High	Active-High, Open-Drain	Capacitor Adjustable	Capacitor Adjustable
MAX6897AAZT+T	Active-High	Active-High, Open-Drain	Capacitor Adjustable	Capacitor Adjustable
MAX6897PALT+T	Active-High	Active-High, Open-Drain	Capacitor Adjustable	150ns Delay
MAX6897PAZT+T	Active-High	Active-High, Open-Drain	Capacitor Adjustable	150ns Delay
MAX6898AALT+T	Active-Low	Active-Low, Open-Drain	Capacitor Adjustable	Capacitor Adjustable
MAX6898AAZT+T	Active-Low	Active-Low, Open-Drain	Capacitor Adjustable	Capacitor Adjustable
MAX6898PALT+T	Active-Low	Active-Low, Open-Drain	Capacitor Adjustable	150ns Delay
MAX6898PAZT+T	Active-Low	Active-Low, Open-Drain	Capacitor Adjustable	150ns Delay
MAX6899AALT+T	Active-Low	Active-High, Push-Pull	Capacitor Adjustable	Capacitor Adjustable
MAX6899AAZT+T	Active-Low	Active-High, Push-Pull	Capacitor Adjustable	Capacitor Adjustable
MAX6899PALT+T	Active-Low	Active-High, Push-Pull	Capacitor Adjustable	150ns Delay
MAX6899PAZT+T	Active-Low	Active-High, Push-Pull	Capacitor Adjustable	150ns Delay

Ordering Information (continued)

PART	PIN-PACKAGE	TOP MARK
MAX6897AALT+	6 μDFN	+BA
MAX6897AAZT+	6 Thin SOT23	+AADQ
MAX6897AAZT/V+*	6 Thin SOT23	_
MAX6897AAZT/V+T*	6 Thin SOT23	_
MAX6897PALT+T	6 μDFN	+BB
MAX6897PAZT+	6 Thin SOT23	+AADR
MAX6898AALT+	6 μDFN	+BD
MAX6898AAZT+	6 Thin SOT23	+AADS
MAX6898AAZT/V+*	6 Thin SOT23	_
MAX6898AAZT/V+T*	6 Thin SOT23	_
MAX6898PALT+T	6 μDFN	+BC
MAX6898PAZT+	6 Thin SOT23	+AADT
MAX6899AALT+	6 μDFN	+LO
MAX6899AAZT+	6 Thin SOT23	+AADM
MAX6899PALT+T	6 μDFN	+LP
MAX6899PAZT+	6 Thin SOT23	+AADN

Note: All devices are specified over the -40°C to +125°C operating temperature range.

Typical Operating Circuit




⁺Denotes a lead(Pb)-free/RoHS-compliant package.

[/]V denotes an automotive qualified part; T = Tape and reel.

^{*}Future product—contact factory for availability.

Pin Configurations (continued)



Chip Information

PROCESS: BICMOS

Package Information

For the latest package outline information and land patterns (footprints), go to www.maximintegrated.com/packages. Note that a "+", "#", or "-" in the package code indicates RoHS status only. Package drawings may show a different suffix character, but the drawing pertains to the package regardless of RoHS status.

PACKAGE TYPE	PACKAGE CODE	OUTLINE NO.	LAND PATTERNNO.
6 μDFN	L611+1	<u>21-0147</u>	<u>90-0080</u>
6 Thin SOT23	Z6+1	<u>21-0114</u>	90-0242

MAX6895-MAX6899

Ultra-Small, Adjustable Sequencing/ **Supervisory Circuits**

Revision History

REVISION NUMBER	REVISION DATE	DESCRIPTION	PAGES CHANGED
5	10/07	_	1, 13, 18
6	11/09	Corrected Absolute Maximum Ratings and made style corrections to Electrical Characteristics and TOC8 and TOC9	2–5
7	7/10	Revised Figures 3, 4, and 6	7–9
8	7/11	Added automotive packages for MAX6896A and MAX6896P; added top mark to MAX6896AAZT/V+1 in the <i>Ordering Information</i> table	1
9	12/13	Added automotive packages for MAX6897 in the Ordering Information table	13
10	3/14	Added automotive packages for MAX6898 in the Ordering Information table	13

For pricing, delivery, and ordering information, please contact Maxim Direct at 1-888-629-4642, or visit Maxim Integrated's website at www.maximintegrated.com.

Maxim Integrated cannot assume responsibility for use of any circuitry other than circuitry entirely embodied in a Maxim Integrated product. No circuit patent licenses are implied. Maxim Integrated reserves the right to change the circuitry and specifications without notice at any time. The parametric values (min and max limits) shown in the Electrical Characteristics table are guaranteed. Other parametric values quoted in this data sheet are provided for guidance.