
# **Surface Mount Fuses** Thin Film > 1206 Size > Slo-Blo® > 468 Series

# RoHS M HF 468 Series Fuse







#### **Agency Approvals**

AGENCY	AGENCY FILE NUMBER	AMPERE RANGE
<i>.</i> 8	E10480	500MA - 3A
<b>€</b> P∞	LR29862	500MA - 3A

# **Electrical Characteristics for Series**

% of Ampere Rating	Opening Time at 25°C	
100%	4 hours, Minimum	
200%	1 sec., Min.; 120 sec., Max.	
300%	0.05 sec., Min.; 1.5 sec., Max	
800%	0.0015 sec., Min.; .05 sec., Max.	

## **Description**

The 468 Series Time-Lag (Slo-Blo®) SMF is a small (1206 size) thin-film device designed for secondary protection of circuits used in space constrained applications such as hand-held portable electronic devices.

This series is 100% lead-free and meets the requirements of the RoHS directive. New Halogen-Free 468 Series fuses are available-to order use the "HF" suffix. See Part Numbering section for additional information.

#### **Features**

- Complies with electronic industry environmental standards for lead reduction.
- Product is compatible with lead-free solders and higher temperature profiles.
- Time delay feature withstands high inrush currents and prevents nuisance openings.
- Package is visually distinct from fastacting version for easy identification.
- Top side marking allows visual verification of amperage rating.

# **Applications**

Secondary protection for space constrained applications:

- Cell phones
- DVD players
- Battery packs
- Hard disk drives.
- Digital cameras


# **Electrical Specifications by Item**

Ampere Amp Voltage Rating (A) Code Rating (V)		Voltage	Voltage Interrupting	Nominal Cold Nominal Resistance Melting	Nom Voltage Drop (mV)	Nom Power Dissipation (W)	Agency Approvals		
		Rating	(Ohms)	I <sup>2</sup> t (A <sup>2</sup> sec)			<i>U</i> R <sub>®</sub>	<b>⊕</b> ®	
0.50	.500	63	50 amperes @63 VAC/VDC	0.27000	0.0310	156.77	0.0784	X	X
1.00	001.	63		0.08250	0.1270	94.70	0.0947	X	х
1.50	01.5	63		0.04750	0.2880	82.32	0.1235	X	X
2.00	002.	63	35 amperes @63 VAC 50 amperes @63 VDC	0.03240	0.5060	77.27	0.1545	X	X
2.50	02.5	63		0.02240	1.0110	73.92	0.1848	Х	Х
3.00	003.	32	50 amperes @32 VAC/VDC	0.01950	1.2700	72.95	0.2189	Х	х


- 1. Measured at 10% of rated current, 25°C.
- 2. Measured at rated voltage.



# **Temperature Rerating Curve**




# **Average Time Current Curves**



# **Soldering Parameters**

Reflow Condition		Pb – Free assembly	
	-Temperature Min (T <sub>s(min)</sub> )	150°C	
Pre Heat	-Temperature Max (T <sub>s(max)</sub> )	200°C	
	-Time (Min to Max) (t <sub>s</sub> )	60 – 180 secs	
Average ra	amp up rate (Liquidus Temp k	5°C/second max	
T <sub>S(max)</sub> to T <sub>L</sub> - Ramp-up Rate		5°C/second max	
Reflow	-Temperature (T <sub>L</sub> ) (Liquidus)	217°C	
	-Temperature (t <sub>L</sub> )	60 – 150 seconds	
PeakTemperature (T <sub>P</sub> )		250 <sup>+0/-5</sup> °C	
Time within 5°C of actual peak Temperature (t <sub>p</sub> )		20 – 40 seconds	
Ramp-down Rate		5°C/second max	
Time 25°C to peakTemperature (T <sub>P</sub> )		8 minutes Max.	
Do not exceed		260°C	






# Surface Mount Fuses Thin Film > 1206 Size > Slo-Blo® > 468 Series


### **Product Characteristics**


Materials	Body: Epoxy Substrate Terminations: 100% Tin Element Cover Coat: Conformal Coating		
Operating Temperature	–55°C to 90°C. Consult temperature rerating curve chart. For operation above 90°C please contact Littelfuse		
Thermal Shock	Withstands 5 cycles of – 50°C to 125°C		
Humidity	MIL-STD-202F, Method 103B, Condition D		

Vibration	Withstands 10-55 Hz per MIL-STD-202F, Method 201A and 10-2000 Hz at 20 G's per MIL-STD-202F, Method 204D, Condition D	
Insulation Resistance (After Opening)	Greater than 10,000 ohms.	
Resistance to Soldering Heat	MIL-STD-202G, Method 210F, Condition D	


#### **Dimensions**














# **Part Marking System**

Marking Code	Amp Code
TF	.500
TH	001.
TK	01.5
TN	002.
то	02.5
TP	003.

# **Part Numbering System**

# 0468002.NRHF

# SERIES -

# AMP Code

The dot is poisitioned before the Packaging Suffix with whole ratings and within the numbering sequence for fractional ratings. Refer to Amp Code column in the Electrical Specifications table.

# **PACKAGING Code** -

NR = Tape and Reel, 5000 pcs

'HF' SUFFIX

**HALOGEN FREE ITEM** 

#### Example:

1.5 amp product is 0467<u>1.5</u>NRHF (2 amp product shown above).

# **Packaging**

Packaging Option	Packaging Specification	Quantity	Quantity & Packaging Code
Tape & Reel – 8mm tape	EIA RS-481-1 (IEC 286, part 3)	5000	NR