

August 2017

## **Inductors for Power Circuits**

Thin-film metal

**TFM-GHM series** 

# TFM201610GHM type

TFM201610GHM

### **REMINDERS FOR USING THESE PRODUCTS**

Before using these products, be sure to request the delivery specifications.

### **SAFETY REMINDERS**

Please pay sufficient attention to the warnings for safe designing when using these products.

<ul> <li>The storage period is less than 6 months. Be sure to follow the sto less).</li> <li>If the storage period elapses, the soldering of the terminal electron</li> </ul>					
If the storage period elapses, the soldering of the terminal electrodes may deteriorate.					
O Do not use or store in locations where there are conditions such a	s gas corrosion (salt, acid, alkali, etc.).				
<ul> <li>Before soldering, be sure to preheat components.</li> <li>The preheating temperature should be set so that the temperature does not exceed 150°C.</li> </ul>	difference between the solder temperature and chip temperature				
<ul> <li>Soldering corrections after mounting should be within the range of If overheated, a short circuit, performance deterioration, or lifespare</li> </ul>	-				
When embedding a printed circuit board where a chip is mounted the overall distortion of the printed circuit board and partial distorti					
<ul> <li>Self heating (temperature increase) occurs when the power is turn design.</li> </ul>	ed ON, so the tolerance should be sufficient for the set thermal				
<ul> <li>Carefully lay out the coil for the circuit board design of the non-ma A malfunction may occur due to magnetic interference.</li> </ul>	gnetic shield type.				
$\bigcirc$ Use a wrist band to discharge static electricity in your body throug	h the grounding wire.				
$\bigcirc$ Do not expose the products to magnets or magnetic fields.					
$\bigcirc$ Do not use for a purpose outside of the contents regulated in the c	lelivery specifications.				
<ul> <li>The products listed on this catalog are intended for use in general equipment, home appliances, amusement equipment, computer e equipment, industrial robots) under a normal operation and use contract to meet the requirement equipment are not designed or warranted to meet the requirement equality require a more stringent level of safety or reliability, or who society, person or property.</li> <li>If you intend to use the products in the applications listed below or set forth in the each catalog, please contact us.</li> </ul>	quipment, personal equipment, office equipment, measurement ondition. ents of the applications listed below, whose performance and/or				
<ol> <li>(1) Aerospace/Aviation equipment</li> <li>(2) Transportation equipment (cars, electric trains, ships, etc.)</li> <li>(3) Medical equipment</li> <li>(4) Power-generation control equipment</li> <li>(5) Atomic energy-related equipment</li> <li>(6) Seabed equipment</li> <li>(7) Transportation control equipment</li> </ol>	<ul> <li>(8) Public information-processing equipment</li> <li>(9) Military equipment</li> <li>(10) Electric heating apparatus, burning equipment</li> <li>(11) Disaster prevention/crime prevention equipment</li> <li>(12) Safety equipment</li> <li>(13) Other applications that are not considered general-purpose applications</li> </ul>				
When designing your equipment even for general-purpose application protection circuit/device or providing backup circuits in your equipment					

### **Inductors for Power Circuits**

Thin-film metal

Product compatible with RoHS directive Halogen-free Compatible with lead-free solders

# **Overview of TFM201610GHM type**


#### FEATURES

- O By using metal magnetic material with high Saturation magnetic flux density the excellent DC bias characteristics needed for inductors for power circuits can be achieved.
- O With the same product shape and terminal structure as general chip parts it has excellent mounting stability characteristics and can also be mounted to general-purpose land patterns.
- O By using a closed magnetic circuit structure leakage flux is minimized.

#### APPLICATION

Smart phones, tablet terminals, HDDs, SSDs, DVCs, DSCs, mobile display panels, portable game devices, compact power supply modules, other

#### PART NUMBER CONSTRUCTION



#### OPERATING TEMPERATURE RANGE, PACKAGE QUANTITY, PRODUCT WEIGHT

Temperature range		Package quantity	Individual weight	
Туре	Operating temperature*	Storage temperature**		
	(° <b>C</b> )	(°C)	(pieces/reel)	( <b>mg</b> )
TFM201610GHM	-40 to +125	-40 to +85	3000	18

\* Operating temperature range includes self-temperature rise.

\*\* The Storage temperature range is for after the circuit board is mounted.

RoHS Directive Compliant Product: See the following for more details.https://product.tdk.com/info/en/environment/rohs/index.html


O Halogen-free: Indicates that CI content is less than 900ppm, Br content is less than 900ppm, and that the total CI and Br content is less than 1500ppm.

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading

#### INDUCTORS

### TFM201610GHM type

#### RECOMMENDED REFLOW PROFILE




Preheating Soldering Peak Temp. Temp. Time Time Temp. Time **T1** T2 t1 ТЗ t2 Т4 t3 150°C 180°C 60 to 120s 230°C 30 to 50s 250 to 260°C 10s max.

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.


#### INDUCTORS

#### SHAPE & DIMENSIONS



Dimensions in mm

#### RECOMMENDED LAND PATTERN



Dimensions in mm

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.

#### ELECTRICAL CHARACTERISTICS

#### **CHARACTERISTICS SPECIFICATION TABLE**

L		L measuring frequency	DC resistance Rated current*			Part No.			
					Isat		Itemp		
(µH)	Tolerance	(MHz)	(m $\Omega$ )max.	(m $\Omega$ )typ.	(A)max.	(A)typ.	(A)max.	(A)typ.	
0.47	±20%	1.0	41	32	4.7	5.0	3.9	4.4	TFM201610GHM-R47MTAA
1.0	±20%	1.0	60	50	3.6	3.8	3.1	3.4	TFM201610GHM-1R0MTAA
2.2	±20%	1.0	152	142	2.4	2.6	1.9	2.1	TFM201610GHM-2R2MTAA

\* Rated current: smaller value of either Isat or Itemp.

Isat: When based on the inductance change rate (30% below the nominal L value)

Itemp: When based on the temperature increase (Temperature increase of 40°C by self heating)

#### O Measurement equipment

Measurement item	Product No.	Manufacturer
L	4294A	Keysight Technologies
DC resistance	Digital Milliohm Meter	
Rated current Isat	4285A+42841A+42842C	Keysight Technologies


\* Equivalent measurement equipment may be used.

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.

### TFM201610GHM type

#### ELECTRICAL CHARACTERISTICS

L FREQUENCY CHARACTERISTICS GRAPH



Product No.	Manufacturer
4294A	Keysight Technologies
ate E an alternations and a second second	the second second second second second second

\* Equivalent measurement equipment may be used.


**⊗TDK** 

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.

### TFM201610GHM type

#### ELECTRICAL CHARACTERISTICS

#### □ INDUCTANCE VS. DC BIAS CHARACTERISTICS GRAPH



Product No. Manufacturer

4285A+42841A+42842C Keysight Technologies

\* Equivalent measurement equipment may be used.

&TDK

(8/9)


A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.

#### INDUCTORS

### TFM201610GHM type


#### PACKAGING STYLE


#### **REEL DIMENSIONS**



Dimensions in mm

#### **TAPE DIMENSIONS**





Dimensions in mm

Туре	А	В	K
TFM201610GHM	2.2	1.8	1.0

A Please be sure to request delivery specifications that provide further details on the features and specifications of the products for proper and safe use. Please note that the contents may change without any prior notice due to reasons such as upgrading.

**⊗TDK** 

#### 20170803 / inductor\_commercial\_power\_tfm201610ghm\_en