

ITEM :

# CRYSTAL OSCILLATORS

TYPE :

DSB321SDA

NOMINAL FREQUENCY :

## 26. 000MHz

SPEC No. :

1XTW26000CGA

Please acknowledge receipt of this specificaiton by signing and returning a copy to us.

	RECEIPT
DATE	
RECEIVED	(signature) (name)

General I	Manufacturer of Quartz Devices
DAIS	HINKU CORP.
675–0194 J Phone (81)	79-425-3141 Fax (81)79-425-1134 /.kds.info/index_en.htm
C.ENG.	Mr. Jamoshita
ENG.	H. Jakase.

- 1. Device Name TCXO
- 2. Model Name DSB321SDA

3. Nominal Frequency 26.000 MHz

4. Mass

0.03g max. 5. Absolute Maximum Ratings

	Item	Symbol		Rating				
1	Supply Voltage	V <sub>cc</sub>		-0.3 ~ +6.0				
2	Storage Temperature Range	T <sub>STG</sub>		°C				
6. Recommended Operating Conditions								
	Item	Symbol	min.	typ.	max.	unit		
1	Supply Voltage	V <sub>CC</sub>	+1.7	-	+3.6	V		
2	Load Impedance (resistance part)	$L_{oad}R$	9	10	11	kΩ		
	(parallel capacitance)	L <sub>oad</sub> _C	9	10	11	pF		

 $T_{OPR}$ 

Operating Temperature Range 3 7. Electrical Characteristics

 $(T_A = -30 \sim +85 \circ C, L_{OAD} R//C = 10k\Omega//10pF, V_{CC} = +1.8V, 2.8V, 3.0V, 3.3V)$ 

\_

+85

°C

-30

	Item Conditions			Limits			Notes
	Item	fter 2 times reflow $T_{A} = -30 \sim +85 \text{ °C}$ $T_{CC} = (+1.8V \sim 3.3V) \pm 5\%$	min.	typ	max.	unit	NOLES
1	Current Consumption		-	-	1.5	mA	
2	Output Level		0.8	-	-	$V_{P-P}$	1
3	Symmetry	GND level (DC cut)	40/60	-	60/40	%	
4	Harmonics		-	-	-5	dBc	
5	Frequency Stability						
	1.Tolerance	After 2 times reflow	-	-	±1.5	ppm	2,3
	2.vs Temperature	T <sub>A</sub> =-30 ~ +85 °C	-	-	±0.5	ppm	4
	3.vs Supply Voltage	V <sub>CC</sub> =(+1.8V~3.3V)±5%	-	-	±0.2	ppm	
	4.vs Load Variation	$L_{oad}R//C= (10k\Omega//10pF) \pm 10\%$	-	-	±0.2	ppm	
	5.vs Aging	T <sub>A</sub> = Room ambient	-	-	±1.0	ppm/year	
6	Start Up	@90% of final Vout level	-	-	2.0	ms	
7	SSB Phase Noise	Relative to f0 level Offset 1kHz	-	-	-130	dBc/Hz	

Notes

1. Clipped sine wave (DC-coupled)

2. Ref. to Nominal Frequency.

3. Please leave after reflow in 2h or more at room ambient.


4. Ref. to Frequency. (T<sub>A</sub>=+25°C)


TITLE TCXO SPECIFICATION	Remark		
Date	Spec. No.	Rev.	Page
2008/11/18	1XTW26000CGA	А	1/13

#### 8. Outline, Pin Connections Outline **Pin Connections** Pin No. Connection #1 GND (2)2.50±0.15 (1) #2 GND (3)#3 Output #4 $V_{\text{CC}}$ 0.25 <u>3.20±0.15</u> #1 Index 0.50 Marking (1) Frequency 26.00 (MHz, 4digits) 0.90±0.1 (2) Model code Т (3)EIA Date code Year (1digit) +Week (2digits) e.g. 2008/1/1 → 801 0.50 <sup>4-</sup>R 0<u>.13</u> 2 unit: mm 2.24 Dimensional Tolerance: ±0.15 <sup>2-</sup>0.70 (Unless otherwise noted) #2 □0.20 (INDEX) 0 <sup>2</sup>-<u>0.40</u> 8-R 0.10 8-0.08 9. Measurement Circuit 1000pF О Т.Р. mA #4 #3 + 10000pF Vcc Output Power TCXO Supply V GND GND L<sub>oad</sub> C $L_{oad}R$ #2 #1 $L_{\text{oad}}$ R=10k $\Omega$ Load C=10pF (Include Jig stray capacitance) TITLE Remark TCXO SPECIFICATION Date Spec. No. Rev. Page 2008/11/18 1XTW26000CGA A 2/13

All test is	performed after 3-times reflow (Clause.13) e	except 10.10 (Resistance to soldering heat
Test Item	Test Description	Requirements
1 Drop	Natural drop (on concrete)   Mounting on the set or test fixture.(Total weig   Height : 150cm   Direction : X,Y,Z, 6directions   Test cycle : 3cycles   Reference specification : EIAJ-ED-4702A Medition	
2 Vibration	Sweep range : 10Hz~500Hz Sweep speed : 11min./cycle Amplitude : 1.5mm (10~55Hz) Acceleration : 200m/s <sup>2</sup> (55~500Hz) Direction : X,Y,Z, 3directions Test cycle : 10cycles Reference specification : IEC 60068-2-6	df/f=<±0.5ppm
3 Shock	Acceleration : 100G (1000m/s <sup>2</sup> ) Direction : X,Y,Z, 6directions Duration : 6ms Test cycle : 3times/each directions Reference specification : IEC 60068-2-27	df/f=<±0.5ppm
4 PCB bend strength	PWB : t=1.6mm Pressure speed : 1.0mm/s Bend width : 1->2->3mm Duration : 10±1s Reference specification : IEC 60068-2-21 Ue	df/f=<±0.5ppm No visible damage.
5 Adherence natur	PWB : t=1.6mm Pressure : 10N Duration : 10±1s Direction : X,Y, 2directions Reference specification : IEC 60068-2-21 Ue	df/f=<±0.5ppm No visible damage.
6 Package strengt	Pressure : 10N Duration : 10±1s Reference specification : IEC 60068-2-77	df/f=<±0.5ppm No mechanical damage. No leak damage.
7 Gross leak	It is immersed for 3 min into +125±5°C Chlorofluorocarbon (CFCs) liquid. Reference specification : IEC 60068-2-17	No continuous air bubbles.
8 Fine leak	It shall be measured by the helium leak deter after pressurization for 60 min by the pressur of (3.92±0.49) x10 <sup>5</sup> Pa in a helium gas atmos Reference specification : IEC 60068-2-17	e
9 Solderability	Solder bath method (Flow soldering) Soldering temperature : +245±5°C Duration : 3±0.3s Reference specification : IEC 60068-2-58	A new uniform coating of solder shall cover a minimum of 95% of the surface being immersed.
10 Resistance to soldering heat	Solder iron method Bit temperature : +350±10°C Duration : 3+1/-0s /each terminal Reference specification : IEC 60068-2-20 Reflow	df/f=<±0.5ppm dVout=<±0.2Vp-p No visible damage. df/f=<±1.0ppm
	In refer to temperature profile shown in claus Test cycle : 3cycles It shall be measured after 2h at room temperature, humidity. Reference specification : IEC 60068-2-58	
TITLE TCXO SPECIFICATIO	N Remark	Chao No.
Date 2008/11/18	1X1	Spec. No.   Rev.   Page     W26000CGA   A   3/1

	Test Item	Test Description		Req	uirements			
	Low temperature	Temperature : -40±3°C		df/f=<±1.0ppm				
	storage	Duration : 1000h		dVout=<±0.2	2Vp-p			
	-	It shall be measured after 2h at room						
		temperature, humidity.						
		Reference specification : IEC 60068-2-1	Ab					
	High temperature	Temperature : +85±2°C		df/f=<±1.0pp	m			
	storage	Duration : 1000h		dVout=<±0.2	2Vp-p			
		It shall be measured after 2h at room						
		temperature, humidity.						
		Reference specification : IEC 60068-2-2	Bb					
	Humidity	Temperature : +85±2°C		df/f=<±1.0pp				
		R.H. 85±5% Duration : 1000h		dVout=<±0.2	2Vp-p			
		It shall be measured after 2h at room						
		temperature, humidity.						
		Reference specification : IEC 60068-2-3	<b>,</b>	1616 1 0				
	НТВ	Temperature : +85±2°C		df/f=<±1.0pp				
	Duration : 1000h		dVout=<±0.2	2Vр-р				
	BIAS : Max value of supply voltage							
		It shall be measured after 2h at room						
		temperature, humidity.						
	ТНВ	Reference specification : IEC 60068-2-2		df/f=<±1.0pp	m			
		Temperature : +40±2°C R.H. 90~95%		dVout=<±0.2				
	Duration : 1000h		uvout- <±0.2	•vp-p				
	BIAS : Max value of supply voltage							
		It shall be measured after 2h at room						
		temperature, humidity.						
		Reference specification : IEC 60068-2-3	3					
	Thermal shock	200 cycles of Temperature:		df/f=<±1.0pp	m			
		-40±3°C:0.5h → +85±2°C:0.5 h		dVout=<±0.2	2Vp-p			
		It shall be measured after 2h at room		Any cracks s	shall not appe	ear.		
		temperature, humidity.						
		Reference specification : IEC pub.68-2-	14.Na					
	ESD	SD Model : Machine Model (MM)						
		Vs=±200V (C1=200pF, R2=0Ω)		No visible da	amage.			
		Number of times : 3times						
		Each terminals except common termina	1.					
		(Connect to test terminal)						
		Reference specification : EIA/JESD22-A	\114					
		Model : Human Body Model (HBM)		df/f=<±1.0pp				
		Vs=±1500V (C1=100pF, R2=1500Ω)		No visible da	amage.			
		Number of times : 3times						
		Each terminals except common termina	l.					
		(Connect to test terminal)						
		Reference specification : EIA/JESD22-A	115					
			mark					
)/		•						
ate			Spec. No.		Rev.	P		





### 15. Packing Condition

#### 15.1 Taping package

- (1) Embossed tape format and dimensions See Fig.1.
- (2) Quantity on reel

2000pcs. max. /reel.

- (3) Taping specification See Fig.2. No lack of a product.
- (4) Reel specification See Fig.3.
- (5) Taping material list See right table.

<u>Taping material List</u> Cover Tape : PET + Olefinic Resin (Conductivity) Emboss : PS (Conductivity) Reel : PS (Conductivity)

#### 15.2 Packing

The products packed in the antistatic bag.

\*Moisture sensitivity level : IPC/JEDEC Standard J-STD-033B / Level 1 No dry pack required and baking after re-storage is unnecessary.

#### 15.3 Packing box

Max 10 reels/packing box. However, in the case of less than 10 reels, It is contained by any boxes. The space in a box is fill up with a cushion.

### 15.4 Label detail


A Lot label is put on a reel and a shipping label and Pb-Free label is put on a packing box.


#### Lot label Shipping label ITEM (Model Name) TYPE (Model Name) SPEC No. (Spec. Number) SPEC (Spec. Number) DELIVERY DATE (Delivery Date) Parts No. (User's Parts Number) Q'TY (Quantity) Lot No. (Lot Number) NOTES (User's Parts Number) FREQ. (Nominal Frequency) DAISHINKU CORP. Q'TY (Quantity) DAISHINKU CORP. KDS Formation of a lot number Lot label (Example) e.a. AH8N18041

		0							~~~~~			~ · · ·		
TYPE	DSB321SDA	Manufact	<u>A</u> turina s	site code	e Pro	<u>H</u> duct co	de		8N18 month	_	ę	<u>041</u> Serial N	-	
SPEC	1XTW26000CGA							,						
NO.		The nota	tion me	ethod of	f a mar	nufactu	re year,	month	, and d	lay. (4-d	igits alp	hanume	eric char	acter)
PARTS		<u>Y</u>	M DD	(4-digi	ts) (	e.g.) 2	00 <u>8</u> / <u>1′</u>	<u>1</u> / <u>18</u> —	• <u>8N18</u>	<u>3</u>				
NO.			<u>Y</u>	Year		1	l-digit (	Last d	igit of	Year)				
LOT	AH8N18041		M	Month	า	1	-digit a	alphan	umeri	c symb	ool			
NO. FREQ.	26.000 MHz	Month	Jan.	Feb.	Mar.	Apr.	May.	Jun.	Jly.	Aug.	Sep.	Oct.	Nov.	Dec.
Q'TY		Symbol	1	2	3	4	5	6	7	8	9	0	Ν	D
	2000 pcs.		DD	Day		2	2-digits	nume	rical c	haract	ers of	day		
KDS														
TITLE					Re	mark								
TCXO SI	PECIFICATION													
Date							Spec	. No.			Re	ev.	Pa	ge
2008/11/18	3				· ·	1XT	W26	000	CG	4		A	7	/13


### DAISHINKU CORP.


DM-Z0002: Style-010





DM-Z0002: Style-010





#### 16. Notes on mounting and handling

#### 16.1 Storage environment

- (1) The temperature and humidity of a storage place, Please give +5~+40°C and 40~85% as a standard.
- (2) Please use this product within one year from the packing label date of issue.
- (3) Please avoid the place which generates corrosive gas, and the place with much dirt.
- (4) Please keep it in a place with little temperature change.
  - Dew condensation arises owing to a rapid temperature change and solderability becomes bad.
- 16.2 Be cautions to static electricity and high voltage.
- 16.3 This product has sufficient durability to fall and vibration. However, conditions may change to the fall after mounting to a PWB, and vibration. When you should drop on a floor the PWB which mounted the product or too much shock is added. Please use after a performance check.
- 16.4 Please check that the curvature of the substrate at the time of substrate cutting does not affect a product. Moreover, especially when a product is near the position of a PWB guide pin, and the position of a PWB break, be careful.
- 16.5 The part concerned does not correspond to washing.
- 16.6 Please repair at +260°C in 10s with hot air or +350°C in 5s with solder Iron.

#### 17. Mandatory control

17.1 Ozone-depleting substance

It regulates by the U.S. air purifying method (November, 1990 establishment). ODS of CLASS-1 and CLASS-2 is not contained or used.

17.2 PBDE, PBBs

PBDE, PBBs are not contained into all the material currently used for this product.

#### 17.3 RoHS

Following material restricted by RoHS is not included or used. Lead, mercury, cadmium, hexavalent, chromium ,PBB and PBDE.

17.4 Law Concerning Examination and Regulation of Manufacture, etc. of Chemical Substances All the material currently used for this product is based on "Law Concerning Examination and Regulation of Manufacture, etc. of Chemical Substances". It is a registered material.

#### 17.5 Lead

Leads, such as solder, are not used for this product.(Lead Free)

#### 17.6 About the existence of silver and mercury use

The silver of very small quantity is contained in the conductive adhesives used for adhesion of Blank. Moreover, mercury is used. It does not get down.

#### 18. The country of origin / factory name / address

Country of origin :JapanFactory name :DAISHINKU Corp. Tottori Production Div.Address :7-3-21 Wakabadai minami, Tottori 689-1112

TITLE TCXO SPECIFICATION	Remark		
Date	Spec. No.	Rev.	Page
2008/11/18	1XTW26000CGA	А	12/13

Rev. No.	Date	Reason	Contents	Approved	Checked	Drawn
_	2008/11/18	-	Initial Release	M.Yamashita	H.Takase	J.Kawakami
А	2008/12/03	User Request	7.5.2 Frequency stability (vs. temperature) ±1.0→ ±0.5ppm	M.Yamashita	H.Takase	J.Kawakami

### 2008-1555 REVERSION RECORD