

# UNISONIC TECHNOLOGIES CO., LTD

# MC4580


#### LINEAR INTEGRATED CIRCUIT

# DUAL OPERATIONAL AMPLIFIER

#### DESCRIPTION

The UTC **MC4580** is the dual operational amplifier, specially designed for improving the tone control, which is most suitable for the audio application.

Featuring noiseless, higher gain bandwidth, high output current and low distortion ratio, and it is most suitable not only for acoustic electronic parts of audio pre-amp and active filter, but also for the industrial measurement tools. It is also suitable for the head phone amp at higher output current, and further more, it can be applied for the handy type set operational amplifier of general purpose in application of low voltage single supply type which is properly biased of the input low voltage source.




#### **■ FEATURES**

\*Operating voltage  $(\pm 2V \sim \pm 18V)$ \*Low input noise voltage  $(0.8\mu Vrms \ typ.)$ \*Wide gain bandwidth product  $(15MHz \ typ.)$ \*Low distortion  $(0.0005\% \ typ.)$ \*Slew rate  $(5V/\mu s \ typ.)$ 

\*Bipolar technology

#### ■ ORDERING INFORMATION


Ordering Number		Dackaga	Dooking	
Lead Free	Halogen Free	Package	Packing	
MC4580L-D08-T	MC4580G-D08-T	DIP-8	Tube	
MC4580L-S08-R	MC4580G-S08-R	SOP-8	Tape Reel	
MC4580L-P08-R	MC4580G-P08-R	TSSOP-8	Tape Reel	
MC4580L-SM1-R	MC4580G-SM1-R	MSOP-8	Tape Reel	
MC4580L-K08-2030-R	MC4580G-K08-2030-R	DFN2030-8	Tape Reel	




# ■ MARKING

PACKAGE	MARKING			
DIP-8	Date Code  UTC			
SOP-8	B 7 6 5  UTC COOC L: Lead Free  MC4580 C G: Halogen Free  Lot Code			
MSOP-8	B 7 6 5  UTC COCC  MC4580  C G: Halogen F  Lot Code			
TSSOP-8	Date Code  UTC GOOD 7  MC4580 G  G Halogen Free  Lot Code			
DFN2030-8	MC 4580 ◆ □□□□ → Date Code			

# **■ PIN CONFIGURATION**



# **■ TEST CIRCUIT**



#### ■ ABSOLUTE MAXIMUM RATINGS (T<sub>A</sub>=25°C)


PARAMETER		SYMBOL	RATINGS	UNIT	
Supply Voltage		V <sup>+</sup> /V <sup>-</sup>	±18	V	
Input Voltage		V <sub>IN</sub>	±15	V	
Differential Input Voltage		$V_{I(DIFF)}$	±30	V	
Output Current		I <sub>OUT</sub>	±50	mA	
	DIP-8	P <sub>D</sub>	750	mW	
	SOP-8		440		
Power Dissipation	TSSOP-8		360		
	MSOP-8		300		
	DFN2030-8		1300		
Junction Temperature		TJ	+125	°C	
Operating Temperature		T <sub>OPR</sub>	-40 ~ +85	°C	
Storage Temperature		T <sub>STG</sub>	-40 ~ +125	°C	


Note Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.


# ■ ELECTRICAL CHARACTERISTICS (V+ /V-=±15V, T<sub>A</sub>=25°C)


PARAMETER	SYMBOL	TEST CONDITION	MIN	TYP	MAX	UNIT
Input Offset Voltage	V <sub>I(OFF)</sub>	$R_S \leq 10k\Omega$		0.5	3	mV
Input Offset Current	I <sub>I(OFF)</sub>			5	200	nA
Input Bias Current	I <sub>I(BIAS)</sub>			100	500	nA
Large Signal Voltage Gain	Gv	$V_{OUT}$ =±10V, $R_L \ge 2k\Omega$	90	110		dB
Output Voltage Swing	V <sub>OM</sub>	$R_L \ge 2k\Omega$	±12	±13.5		V
Input Common Mode Voltage	$V_{I(CM)}$		±12	±13.5		V
Common Mode Rejection Ratio	CMRR	$R_S \leq 10k\Omega$	80	110		dB
Supply Voltage Rejection Ratio	SVR	$Rs \le 10k\Omega$	80	110		dB
Operating Current	Icc			6	9	mA
Slew Rate	SR	$R_L \ge 2k\Omega$		5		V/µs
Gain bandwidth Product	GB	f=10KHz		15		MHz
Total Harmonic Distortion	THD	Gv=20dB, $V_{OUT}$ =5 $V$ , $R_L$ =2 $k\Omega$ , f=1 $KHz$		0.0005		%
Input Noise Voltage	eN	RIAA Rs=2.2 kΩ, 30kHzLPF		0.8		μVrms


#### **■ TYPICAL CHARACTERISTICS**



















#### **■ TYPICAL CHARACTERISTICS(Cont.)**














UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice.

