

SR32 Thru SR36

Surface Mount SCHOTTKY BARRIER Schottky Barrier rectifiers RECTIFIERS Using the Schottky Barrier principle with a Molybdenum barrier meta. These **3.0 AMPERES** state-of-the-art geometry features epitaxial construction with oxide passivation 20-60 VOLTS and metal overlay contact. Ideally suited for low voltage, high frequency rectification, or as free wheeling and polarity protection diodes, in surface mount applications where compact size and weight are critical to the system. Features * Low Forward Voltage. * Low Switching noise. * High Current Capacity * Guarantee Reverse Avalanche. * Guard-Ring for Stress Protection. * Low Power Loss & High efficiency. DO-214AA(SMB) * 150 **Operating Junction Temperature** * Low Stored Charge Majority Carrier Conduction. * Plastic Material used Carries Underwriters Laboratory Flammability Classification 94V-O * Moisture Sensitivity Level: MSL-1 * * In compliance with EU RoHs 2002/95/EC directives **MAXIMUM RATINGS** SR Characteristic Symbol Unit 36 32 33 34 35 Peak Repetitive Reverse Voltage VRRM Working Peak Reverse Voltage 20 30 40 50 60 V V_{RWM} **DC Blocking Voltage** V_{R} MILLIMETERS 35 V DIM **RMS Reverse Voltage** VR_(RMS) 14 21 28 42 MIN MAX 3.30 Average Rectifier Forward Current 3.0 A Α 3.90 lo В 4.20 4.60 Non-Repetitive Peak Surge Current IFSM С 1.80 2.20 (Surge applied at rate load conditions 75 A D 5.10 5.60 half-wave, single phase,60Hz) Е 1.90 2.50 Operating and Storage Junction TJ, TSTG -65 to +150 F 1.30 Temperature Range G 0.22 н 0.95 1.35 **ELECTRIAL CHARACTERISTICS** SR Characteristic Symbol Unit 32 33 34 35 36 CASE---Maximum Instantaneous Forward Voltage V_{F} 0.550 0.700 V Transfer molded $(I_{F} = 3.0 \text{ Amp})$ plastic Maximum Instantaneous Reverse Current (Rated DC Voltage, $T_C = 25$) 0.5 I_R mΑ POLARITY---(Rated DC Voltage, $T_c = 125$) 20 Cathode indicated polarity band Maximum Thermal Resistance Junction to °C/W R_{θjc} 40 Case Typical Junction Capacitance CP 210 190 $_{\mathsf{P}}\mathsf{F}$ (Reverse Voltage of 4 volts & f=1 MHz)

FIG-1 FORWARD CURRENT DERATING CURVE






FIG-2 TYPICAL FORWARD CHARACTERISITICS




FORWARD VOLTAGE (Volts)

FIG-3 TYPICAL REVERSE CHARACTERISTICS




PERCENT OF RATED REVERSE VOLTAGE (%)



REVERSE VOLTAGE (Volts)

FIG-5 PEAK FORWARD SURGE CURRENT



NUMBER OF CYCLES AT 60 Hz