
Spec Sheet

Multilayer Chip Inductors for High Frequency Applications (HK series)

HK160868NJ-T



Features

- Item Summary 68nH±5%, 0.3A, 0603/1608 (EIA/JIS)
- Lifecycle Stage
 Mass Production
- Standard packaging quantity (minimum)
 Taping paper 4000pcs

Products characteristics table

Inductance	68 nH ± 5 %
Case Size (EIA/JIS)	0603/1608
Rated Current (max)	0.3 A
DC Resistance (max)	0.85 Ω
DC Resistance (typ)	0.55 Ω
Q (min)	12
Q (typ)	18
LQ Measuring Frequency	100 MHz
Self Resonant Frequency (min)	700 MHz
Self Resonant Frequency (typ)	1200 MHz
Operating Temp. Range	-40 to +85 ℃
Temperature characteristic (Inductance change)	± 10 %
RoHS2 Compliance (10 subst.)	Yes
REACH Compliance (168 subst.)	Yes
Soldering	Reflow/Wave

■ External Dimensions

Dimension L	1.6 ±0.15 mm
Dimension W	0.8 ±0.15 mm
Dimension T	0.8 ±0.15 mm
Dimension e	0.3 ±0.2 mm

The data is reference only. Electrical characteristics vary depending on environment or measurement condition. TAIYO YUDEN reserves the right to make change to the Date at any time without notice. Before making final selection, please check product specification.