

ABS22 THRU ABS210

MOSPEC




SINGLE PHASE 2.0AMP SURFACE MOUNT GLASS PASSIVATED BRIDGE RECTIFIER

Features

- Glass passivated die construction
- Low forward voltage drop
- High current capability
- High surge current capability
- Designed for surface mount application
- Plastic material-UL flammability 94V-0

Mechanical Data

- Case: SOPA-4, molded plastic ABS
- Terminals: plated leads solderable per MIL-STD-202, Method 208
- Polarity: as marked on case
- Mounting position: Any
- Marking: type number



Dimensions in inches and (millimeters)

Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single Phase, half wave, 60Hz, resistive or inductive load.

For capacitive load, derate current by 20%.

TYPE NUMBER	SYMBOL	ABS22	ABS24	ABS26	ABS28	ABS210	UNITS	
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V _{RRM}							
	V _{RWM}	200	400	600	800	1000	V	
	V _{DC}							
RMS Reverse Voltage	V _{RMS}	140	280	420	560	700	V	
Average Rectified Output Current @T _A = 50°C	I _o	2.0						A
Non-Repetitive Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method)	I _{FSM}	60						A
Forward Voltage per element @I _F = 2.0A	V _{FM}	1.1						V
Peak Reverse Current @T _A = 25°C At Rated DC Blocking Voltage @T _A = 125°C	I _R	5.0 500						uA
Typical Thermal Resistance per leg	R _{θJA}	62.5						°C/W
	R _{θJL}	25						
Operating and Storage Temperature Range	T _J , T _{STG}	-55to+150						°C

FIG.1 FORWARD CURRENT DERATING CURVE




FIG.2 TYPICAL FORWARD CHARACTERISTICS




FIG.3 MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG. 4 TYPICAL REVERSE CHARACTERISTICS

