

# **Schottky Barrier Rectifiers**

Using the Schottky Barrier principle with a Refractory metal capable of high temperature operation metal. proprietary barrier technology allows for reliable operation up to 150 junction temperature. Typical application are in switching Mode Power Supplies such as adaptors, DC/DC converters free- wheeling and polarity protection diodes.

#### **Features**

- \* Low Forward Voltage.
- \* Low Switching noise.
- \* High Current Capacity
- \* Guarantee Reverse Avalanche.
- \* Guard-Ring for Stress Protection.
- \*Low Power Loss & High efficiency.
- \* 150 Operating Junction Temperature
- \* Low Stored Charge Majority Carrier Conduction.
- \* Plastic Material used Carries Underwriters Laboratory Flammability Classification 94V-O
- \* Moisture Sensitivity Level: MSL-1



\* In compliance with EU RoHs 2002/95/EC directives

## **MAXIMUM RATINGS**

Characteristic	Symbol	SK220	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V <sub>RRM</sub> V <sub>RWM</sub> V <sub>R</sub>	200	V
RMS Reverse Voltage	V <sub>R(RMS)</sub>	140	V
Average Rectifier Forward Current	I <sub>O</sub>	2.0	Α
Non-Repetitive Peak Surge Current (Surge applied at rate load conditions halfware, single phase, 60Hz)	I <sub>FSM</sub>	50	А
Operating and Storage Junction Temperature Range	$T_{J}$ , $T_{STG}$	-65 to +150	

# **ELECTRIAL CHARACTERISTICS**


Characteristic	Symbol	SK220	Unit
Maximum Instantaneous Forward Voltage ( I <sub>F</sub> =2.0 Amp.)	$V_{F}$	0.95	V
Maximum Instantaneous Reverse Current ( Rated DC Voltage, $T_C = 25$ ) ( Rated DC Voltage, $T_C = 125$ )	I <sub>R</sub>	0.01 10	mA
Maximum Thermal Resistance Junction to case	$R_{ heta JC}$	55	/W
Typical Junction Capacitance ( Reverse Voltage of 4 volts & f=1 MHz )	$C_P$	80	₽F


### SCHOTTKY BARRIER RECTIFIERS

2.0 AMPERES 200 VOLTS



DO-214AC(SMA)






DIM	MILLIM	ETERS
DIIVI	MIN	MAX
Α	2.20	2.80
В	4.10	4.70
C	1.30	1.70
D	4.70	5.30
Е	1.90	2.50
F		1.30
G		0.30
Н	0.95	1.50


CASE---Transfer molded plastic

POLARITY---Cathode indicated polarity band






### FIG-2 TYPICAL FORWARD CHARACTERISITICS




## FIG-3 TYPICAL REVERSE CHARACTERISTICS




PERCENT OF RATED REVERSE VOLTAGE (%)

## FIG-4 TYPICAL JUNCTION CAPACITANCE



REVERSE VOLTAGE (Volts)



NUMBER OF CYCLES AT 60 Hz