

## Wire-wound Chip Power Inductors (CB series)

## CBC2012T1R0M



## ■ Features

- Item Summary  
1.0uH±20%, 0.7A, 0805/2012 (EIA/JIS)
- Lifecycle Stage  
Mass Production
- Standard packaging quantity (minimum)  
Taping Embossed 3000pcs

## ■ Products characteristics table

Inductance	1.0 uH ± 20 %
Case Size (EIA/JIS)	0805/2012
Rated Current (max)	0.7 A
Saturation Current (max)	0.7 A
Temperature Rise Current (max)	0.84 A
DC Resistance (max)	0.247 Ω
DC Resistance (typ)	0.19 Ω
LQ Measuring Frequency	7.96 MHz
Self Resonant Frequency (min)	100 MHz
Operating Temp. Range	-40 to +105 °C (Including-self-generated heat)
Temperature characteristic (Inductance change)	± 35 %
RoHS2 Compliance (10 subst.)	Yes
REACH Compliance (168 subst.)	Yes
Soldering	Reflow

## ■ External Dimensions

Dimension L	2.0 ±0.2 mm
Dimension W	1.25 ±0.2 mm
Dimension T	1.25 ±0.2 mm
Dimension e	0.5 ±0.2 mm

2017.01.02

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.  
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.  
 Before making final selection, please check product specification.




Wire-wound Chip Power Inductors (CB series)

**CBC2012T1R0M**



Dimension	unit : mm	unit : inch
Length :	2.0 +/- 0.2	( 0.079 +/- 0.008 )
Width :	1.25 +/- 0.2	( 0.049 +/- 0.008 )
Height :	1.25 +/- 0.2	( 0.049 +/- 0.008 )

Inductance :	1.0	uH	( test freq at 7.96MHz )
DC Resistance :	0.19 / 0.247	ohm	( typ / max )
Saturation Current :	700	mA	( max )
Temp. rise Current :	840	mA	( max )
Saturation current typical : 30% reduction from initial L value.			
Temp rise Current typical : Temperature will rise by 40 deg C			



The data is reference only. Electrical characteristics vary depending on environment or measurement condition. TAIYO YUDEN reserves the right to make change to the data at any time without notice. Before making final selection, please check product specification.