

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or unavteries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out or i, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor and is officers, employees, uniotificated use, even if such claim any manner.



SEMICONDUCTOR®

October 2013

FQP4N20L N-Channel QFET[®] MOSFET 200 V, 3.8 A, 1.35 Ω

Description


These N-Channel enhancement mode power field effect transistors are produced using Fairchild's proprietary, planar stripe, DMOS technology. This advanced technology is especially tailored to minimize on-state resistance, provide superior switching performance, and withstand high energy pulse in the avalanche and commutation modes. These devices are well suited for high efficiency switching DC/DC converters, switch mode power supplies, and motor control.

Features

• 3.8 A, 200 V, R_{DS(on)} = 1.35 Ω (Max.) @ V_{GS} = 10 V, I_D = 1.9 A

- Low Gate Charge (Typ. 4.0 nC)
- Low Crss (Typ. 6.0 pF)
- 100% Avalanche Tested





Absolute Maximum Ratings T_c = 25°C unless otherwise noted.


Symbol	Parameter Drain-Source Voltage		FQP4N20L	Unit V	
V _{DSS}			200		
I _D	Drain Current - Continuous (T _C = 25°	3.8	А		
	- Continuous (T _C = 100	2.4	A		
I _{DM}	Drain Current - Pulsed	(Note 1)	15.2	A	
V _{GSS}	Gate-Source Voltage		± 20	V	
E _{AS}	Single Pulsed Avalanche Energy	(Note 2)	52	mJ	
I _{AR}	Avalanche Current	(Note 1)	3.8	A mJ	
E _{AR}	Repetitive Avalanche Energy	(Note 1)	4.5		
dv/dt	Peak Diode Recovery dv/dt (Note 3)		5.5	V/ns	
P _D	Power Dissipation ($T_C = 25^{\circ}C$)	45	W		
	- Derate above 25°C		0.36	W/°C	
T _J , T _{STG}	Operating and Storage Temperature Range		-55 to +150	°C	
TL	Maximum lead temperature for soldering purposes, 1/8" from case for 5 seconds		300	°C	


Thermal Characteristics


Symbol	Parameter	FQP4N20L	Unit °C/W	
$R_{ extsf{ heta}JC}$	Thermal Resistance, Junction-to-Case, Max.	2.78		
$R_{\theta CS}$	Thermal Resistance, Case-to-Sink, Typ.	0.5	°C/W	
R_{\thetaJA}	Thermal Resistance, Junction-to-Ambient, Max.	62.5	°C/W	


Part Nu	mber	ber Top Mark	Package	Packing Method	Reel	Size	Tape W	idth	Quantity	
FQP4N	120L			0-220 Tube N		A	N/A		50 units	
lectri	cal Ch	naracteristics r	_c = 25°C unless oth	erwise noted.						
Symbol		Parameter		Test Conditions		Min	Тур	Max	Unit	
	rector	otion								
BV _{DSS}	Drain-S		ane Vos	_s = 0 V, I _D = 250 μA		200			V	
ABV _{DSS}	Drain-Source Breakdown Voltage					200			· ·	
ΔT_{J}		Breakdown Voltage Temperature Coefficient		$I_D = 250 \ \mu$ A, Referenced to 25°C			0.16		V/°C	
DSS	Zero Gate Voltage Drain Current		V _{DS}	$V_{DS} = 200 \text{ V}, V_{GS} = 0 \text{ V}$ $V_{DS} = 160 \text{ V}, T_{C} = 125^{\circ}\text{C}$				1	μA	
			nt V _{DS}					10	μA	
GSSF	Gate-B	Gate-Body Leakage Current, Forward		$V_{GS} = 20 \text{ V}, V_{DS} = 0 \text{ V}$				100	nA	
GSSR		ody Leakage Current, F		s = -20 V, V _{DS} = 0 V				-100	nA	
On Cha	racteri	stics								
V _{GS(th)}		nreshold Voltage	V _{DS}	= V _{GS} , I _D = 250 μA		1.0		2.0	V	
R _{DS(on)}	Static D)rain-Source	-	$= 10 \text{ V}, \text{ I}_{\text{D}} = 1.9 \text{ A}$			1.10	1.35		
20(01)	On-Res	sistance	V _{GS}	= 5 V, I _D = 1.9 A			1.13	1.40	Ω	
9 _{FS}	Forward	d Transconductance	V _{DS}	= 25 V, I _D = 1.9 A			3.2		S	
	1	acteristics								
C _{iss}		apacitance	V _{DS}	$V_{DS} = 25 V, V_{GS} = 0 V,$			240	310	pF	
C _{oss}		Capacitance		I.0 MHz			36	45	pF	
C _{rss}	Revers	e Transfer Capacitance					6	8	pF	
Switchi	ing Cha	aracteristics								
d(on)	Turn-O	n Delay Time	Van	V _{DD} = 100 V, I _D = 3.8 A,			7	25	ns	
t _r	Turn-O	n Rise Time		$= 25 \Omega$			70	150	ns	
d(off)	Turn-Of	ff Delay Time					15	40	ns	
f	Turn-Of	ff Fall Time			(Note 4)		40	90	ns	
ე ^g	Total G	ate Charge	V _{DS}	= 160 V, I _D = 3.8 A,			4.0	5.2	nC	
Q _{gs}	Gate-S	ource Charge		s = 5 V			1.0		nC	
ე _{gd}	Gate-D	rain Charge		(Note			1.9		nC	
Drain-S	ource	Diode Characteris	stics and M	aximum Ratings						
S	1	Im Continuous Drain-S						3.8	Α	
SM	Maximum Pulsed Drain-Source Diode Forward Current				15.2	А				
/ _{SD}		ource Diode Forward V		s = 0 V, I _S = 3.8 A)	1.5	V	
rr	Revers	e Recovery Time	V _{GS}	$V_{GS} = 0 V, I_S = 3.8 A,$			90		ns	
2 _{rr}	Reverse	e Recovery Charge	00	/ dt = 100 A/μs			0.25		μC	
. L = 5.4 mH	, I _{AS} = 3.8 A, di/dt ≤ 300 /	e-width limited by maximum jur V _{DD} = 50 V, R _G = 25 Ω, starti A/µs, V _{DD} ≤ BV _{DSS} , starting T _J =	ng T _J = 25°C.						0	


FQP4N20L — N-Channel QFET[®] MOSFET













Full Production

Not In Production

No Identification Needed

Obsolete

notice to improve design.

Datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.

Datasheet contains specifications on a product that is discontinued by Fairchild

Semiconductor. The datasheet is for reference information only.

Rev. 166

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death a

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC