規格承認書

PECIFICATION FOR APPROVAL

客 戶					
CUSTOMER	:				
項目	_				
ITEM	:	贴片式压电无源蜂鸣器(内部驱动)			
型號	_				
TYPE	:	GSC1407YB-3V4000			
描述					
DESCRIPTION	:	L14.0 x W14.0 x H7.0 mm 4000Hz 3V ≥80DB 正发音 LCP 材质			
客戶料號					
CUSTOMER NO). <u>:</u>				
規格書號					
SPECIFICATION NO.:					
版本					
EDITION NO.	:	V1.0			
日 期	•				
DATE	:	2018-3-9			

客戶承認

CUSTOMER CONFIRM AND SIGN

檢查	審核	承認
TESTED BY	CHECKED BY	APPROVED BY

東莞市赢海電子有限公司

DONGUAN INGHAI ELECTRONICS CO..LTD

DOTIGOTH IN TOTAL ELECTROTICS CONETS		
製作	審查	確認
ISSUED BY	CHECKED BY	APPROVED BY
周明	刘承成	

地址: 廣東省東莞市虎门镇怀德社区雅瑶工业区

網址: HTTP://WWW.INGHAI.COM

A. SCOPE

This specification applies SMD piezoelectric buzzer, GSC1407YB-3V4000

B. SPECIFICATION

No.	Item	Unit	Specification	Condition
1	Oscillation Frequency	KHz	4.0±0.5	
2	Operating Voltage	VAc	3 ~16	
3	Rated Voltage	VAC	5	
4	Current Consumption	mA	MAX. 5	at Rated Voltage
5	Sound Pressure Level	dB	MIN. 85	at 10cm at Rated Voltage
6	Tone Nature		Single	
7	Operating Temperature	$^{\circ}\!$	-20~ +70	
8	Storage Temperature	$^{\circ}\!\mathbb{C}$	-30 ~ +80	
9	Dimension	mm	14 x14 x H7	See appearance drawing
10	Weight (MAX)	gram	2.0	
11	Housing Material		LCP(Black)	
12	Leading Pin		Plated Brass(Au)	See appearance drawing
13	Environmental Protection Regulation		RoHS	


^{*}Applying rated voltage (Resonant frequency, Square wave)

Measuring condition

Part shall be measured under a condition (Temperature: $5 \sim 35$ °C, Humidity: $45\% \sim 85\%$ R.H., Atmospheric pressure: $860 \sim 1060$ hPa) unless the standard condition (Temperature: 25 ± 3 °C, Humidity: $60\pm10\%$ R.H. Atmospheric pressure: $860 \sim 1060$ hPa) is regulated to measure.


C. APPEARANCE DRAWING

Tolerance: ± 0.5 mm Except Specified




D: TEST METHOD:


The oscillation frequency, current consumption and sound pressure are measured by the measuring instruments shown below.



In the measuring test, buzzer is placed as follows:




E: FREQUENCY RESPONSE:



E:Recommended Temp. Profile for Reflow Oven (Fig.1)

(1)Recommendable reflow soldering condition is as follows (Reflow soldering is twice)

Note:It is requested that reflow soldering should be executed after heat of product goes down to normal.



Heat resistant line (Used when heat resistant reliability test is performed) (2)Manual soldering Manual soldering temperature 350 °C within 5 sec.

NO.	ITEM	TEST CONDITION AND REQUIREMENT
1	High Temperature Test (Storage)	After being placed in a chamber with 80±2°C for 96 hours and then being placed in normal condition for 2 hours. Allowable variation of SPL after test: ±10dB.
2	Low Temperature Test (Storage)	After being Placed in a chamber with -30±2°C for 96 hours and then being placed in normal condition for 2 hours. Allowable variation of SPL after test: ±10dB.
3	Humidity Test	After being Placed in a chamber with 90-95% R.H. at 40±2°C for 96 hours and then being placed in normal condition for 2 hours. Allowable variation of SPL after test: ±10dB.
4	Temperature Cycle Test	The part shall be subjected to 5 cycles. One cycle shall be consist of: +70°C +25°C +25°C -0.5

		Drop on a hard wood board of 4cm thick, any directions ,6 times,
5	Drop Test	at the height of 75cm.
		Allowable variation of SPL after test: ±10dB.
6		After being applied vibration of amplitude of 1.5mm with 10 to 55 Hz
	Vibration Test	band of vibration frequency to each of 3 perpendicular directions for
		2 hours .
		Allowable variation of SPL after test: ±10dB.
		Lead terminals are immersed in rosin for 5 seconds and then
7	Solderability	immersed in solder bath of +300±5°C for 3±1 seconds.
	Test	90% min. lead terminals shall be wet with solder
		(Except the edge of terminals).
8	Terminal Strength Pulling Test	The force of 9.8N(1.0kg) is applied to each terminal in axial direction for
		10 seconds.
		No visible damage and cutting off.

TEST CONDITION.

Standard Test Condition:a) Temperature: +5 ~ +35 ℃ b) Humidity: 45-85% c) Pressure: 860-1060mbar 一般测试条件: a) 温度: +5 ~ +35 ℃ b) 湿度: 45-85% c) 气压: 860-1060mbar Judgment Test Condition:a) Temperature: +25 ± 2 ℃ b) Humidity: 60-70% c) Pressure: 860-1060mbar 争议时测试条件: a) 温度: +25 ± 2 ℃ b) 湿度: 60-70% c) 气压: 860-1060mbar

F: PACKING:

