

PECIFICATION FOR APPROVAL

客 戶								
CUSTOMER	:							
項目								•
ITEM	TEM . 贴片式电磁无源蜂鸣器(外部驱动)							
型 號					-			
TYPE	YPE : GSC8525RA-16R2700							
描述								-
DESCRIPTION :	_	8.5 x 8.5 x 3 MM	2700Hz	16Ω 3V	>=85DB	LCP 材质	侧发音	
客戶料號								
CUSTOMER NO. :								
規格書號								
SPECIFICATION NO.:								
版本								
EDITION NO.	:	V1.0						
日期	-							-
DATE	: _	2012-11-16						

客戶承認

CUSTOMER CONFIRM AND SIGN

檢查	審核	承認
TESTED BY	CHECKED BY	APPROVED BY

東莞市贏海電子有限公司

DONGUAN INGHAI ELECTRONICS CO.,LTD

製作	審查	確認
ISSUED BY	CHECKED BY	APPROVED BY
周明		

地址: 廣東省東莞市長安鎮上沙管理區北橫路8號

電話 / TEL: 0769-83060958 傳真 / FAX: 0769-81608993

網址: HTTP://WWW.INGHAI.COM

A. SCOPE


This specification applies SMD piezoelectric buzzer,

B. SPECIFICATION


No.	ltem	Unit	Specification	Condition
1	Oscillation Frequency	Hz	2700	Vo-p=1/2duty , square wave
2 Operating Voltage		Vo-p	2 ~ 5	
3	3 Rated Voltage		3	
4	Current Consumption	mA	MAX. 90	at Rated Voltage
5	Sound Pressure Level	dB	Min.85	at 10cm at Rated Voltage
6	Coil Resistance	Ω	16±3	
7	Operating Temperature	°C	-20 ~ +80	
8	Storage Temperature	°C	-30 ~ +85	
9	9 Dimension		8.5 x 8.5 x 3 MM	See appearance drawing
10	Environmental Protection Regulation		RoHS	

C. APPEARANCE DRAWING


Tol : ± 0.3 Unit: mm



D:TEST METHOD:




E:FREQUENCY RESPONSE:



F. Soldering Condition

(1)Recommendable reflow soldering condition is as follows (Reflow soldering is twice)

Note: It is requested that reflow soldering should be executed after heat of product goes down to normal.



Heat resistant line

(Used when heat resistant reliability test is performed) (2)Manual soldering

Manual soldering temperature 350 °C within 5 sec.

G: Reliability Test

After any following tests the part shall meet specifications without any degradation in appearance and performance except SPL. SPL shall not deviate more than -10 dB from the initial value

1. Ordinary Temperature Life Test

The part shall be subjected to 96 hours at $25\pm10^\circ$ C. Input rated voltage Resonant frequency, 1/2 duty Square wave.

2. High Temperature Test

The part shall be capable of with standing a storage temperature of +85 $^\circ\!{\rm C}$ for 96 hours.

3. Low Temperature Test

The part shall be capable of with standing a storage temperature of -30 $^\circ\!\mathrm{C}$ for 96 hours.

4. Humidity Test

Temperature:+40 $^\circ\!C\pm3^\circ\!C$ Relative Humidity:90% \sim 95% Duration: 48 hours and expose to room temperature for 6 hours

5. Temperature Shock Test Temperature:70°C /1hour→ 25°C/3hours→-30°C/1hour→ 25°C/3hours (1cycle) Total cycle: 10 cycles

6. Drop Test

Standard Packaging From 120mm(Drop on hard wood or board of 5cm thick, three sides, six plain.)

7. Vibration Test Vibration:1000cycles /min. Amplitude:1.5mm, Duration: 1 hour in each 3 axes

Measuring condition

Part shall be measured under a condition (Temperature: $5\sim35^{\circ}$ C, Humidity: $45\%\sim85\%$ R.H., Atmospheric pressure: 860 ~1060 hPa) unless the standard condition (Temperature: $25\pm3^{\circ}$ C, Humidity: $60\pm10\%$ R.H. Atmospheric pressure: 860 ~1060 hPa) is regulated to measure.

Note:

As this product is not protected from foreign material entering, please make sure that any foreign materials (e.g. magnetic powder, washing solvent, flux, corrosive gas) do not enter this product in your production processes. The functional degradation (e.g. SPL down) may occur if foreign material enter it.

H:PACKING:

