


MOLDING TOOL	
INNER MOLD	OUTSIDE MOLD
0041/0044	0047/0048

REVISION			
REV.	DESCRIPTION	APPROVAL	DATE
A	NEW RELEASE	CUI MANMAN	10.09.03



WIRE LIST:

P1	P2
C1	1
C2	2
C3	3
15	5
	10
C5	6
	7
14	8
16	9
7	12
C4	13
8	14
6	15
SHELL	SHELL

1PCS/PE BAG(0.06mm) PACKING

字高:2.0MM  
字体:Arial  
移印颜色: coolgray 4C

⑦	PE BAG	PE BAG:60*90*0.06mm	1PCS
⑥	PVC	MOLDED 45 PVC BLACK (S001)	1PCS
⑤	SCREW	SCREW #4-40UNC,L=φ5.8*23mm GOLD FLASH	2PCS
④	CONN.	HDD 15P FEMALE CONNECTOR SOLDER TYPE CONTACT GOLD	1PCS
		FLASH.INSULATOR BLUE(2935C).FRONT SHELL GOLD FLASH	
		BACK SHELL TIN PLATED	
③	CONN.	DVI 24+5 MALE CONNECTOR SOLDER TYPE CONTACT GOLD FLASH	1PCS
		INSULATOR BLACK.FRONT SHELL GOLD FLASH BACK SHELL TIN PLATED	
②	CABLE	HOOK UP WIRE:UL1061 28AWG*1C TINNED COPPER WIRE,	7PCS
		INSULATION:YELLOW PVC OD=0.9±0.1mm.L=22±1mm.	
①	CABLE	HOOK UP WIRE:UL1061 28AWG*1C TINNED COPPER WIRE,	4PCS
		INSULATION:BLACK PVC OD=0.9±0.1mm.L=17±1mm.	
ITEM	NAME	DESCRIPTION	Q'TY

NOTES:  
1.360° SINGLE ELECTRIC COPPER FOIL AFTER INNER AND SPOT SOLDER MOLDING  
2.ALL MATERIALS/PROCESSES ARE ROHS COMPLIANT.

ELECTRONIC TEST CONDITION:  
100% OPEN SHORT & MISWIRE TEST.  
CONTACT RESISTANCE:1Ω /MAX  
INSULATION RESISTANCE:10MΩ /MIN.AT DC 300V

mm	TITLE	ENG	DATE
SCALE	DVI 24+5M TO HDD 15F ADAPTER	CHECKED	DATE
SHEET	CUS. P/N	APPROVED	DATE
DIMENSIONAL TOLERANCES UNLESS OTHERWISE NOTED	SCPDV24VGK		
.X ±			
.XXX ±	DRAW NO.		
REV. A	JZ-A008-RS		