Surface Mount Schottky Power Rectifier

This device employs the Schottky Barrier principle in a large area metal-to-silicon power diode. State-of-the-art geometry features epitaxial construction with oxide passivation and metal overlay contact. Ideally suited for low voltage, high frequency rectification, or as free wheeling and polarity protection diodes, in surface mount applications where compact size and weight are critical to the system.

Features

- Small Compact Surface Mountable Package with J-Bend Leads
- Rectangular Package for Automated Handling
- Highly Stable Oxide Passivated Junction
- Excellent Ability to Withstand Reverse Avalanche Energy Transients
- Guard-Ring for Stress Protection
- NRVBS Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable
- These are Pb-Free Devices

Mechanical Characteristics

- Case: Epoxy, Molded, Epoxy Meets UL 94 V-0
- Weight: 217 mg (Approximately), SMC 95 mg (Approximately), SMB
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead and Mounting Surface Temperature for Soldering Purposes: 260°C Max. for 10 Seconds
- Polarity: Notch in Plastic Body Indicates Cathode Lead
- Device Meets MSL 1 Requirements
- ESD Ratings:
 - Machine Model, C
 - Human Body Model, 3B



ON Semiconductor®

http://onsemi.com

SCHOTTKY BARRIER RECTIFIERS 3.0 AMPERES, 60 VOLTS





SMC **CASE 403**



SMB CASE 403A

MARKING DIAGRAMS





ORDERING INFORMATION

| Device | Package | Shipping [†] |
|--------------|------------------|------------------------|
| MBRS360T3G | SMC (Pb-Free) | 2,500 / Tape & Reel |
| NRVBS360T3G | SMC (Pb-Free) | 2,500 / Tape & Reel |
| MBRS360BT3G | SMB (Pb-Free) | 2,500 / Tape & Reel |
| NRVBS360BT3G | SMB (Pb-Free) | 2,500 / Tape & Reel |

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

MAXIMUM RATINGS

| Rating | Symbol | Value | Unit |
|--|--|--|------|
| Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage | V _{RRM} V _{RWM} V _R | 60 | V |
| Average Rectified Forward Current | I _{F(AV)} | 3.0 @ T _L = 137°C 4.0 @ T _L = 127°C | A |
| Nonrepetitive Peak Surge Current (Surge applied at rated load conditions halfwave, single phase, 60 Hz) | I _{FSM} | 125 | A |
| Storage Temperature Range | T _{stg} | – 65 to +175 | °C |
| Operating Junction Temperature (Note 1) | TJ | – 65 to +175 | °C |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. The heat generated must be less than the thermal conductivity from Junction-to-Ambient: $dP_D/dT_J < 1/R_{\theta JA}$.

THERMAL CHARACTERISTICS

| Characteristic | Symbol | Value | Unit | |
|---|------------------|------------|------|--|
| Thermal Resistance, Junction-to-Lead (Note 2) SMC Package SMB Package | R _{θJL} | 11 15 | °C/W | |
| Thermal Resistance, Junction-to-Ambient (Note 2) SMC Package SMB Package | R _{θJA} | 136 145 | °C/W | |
| Thermal Resistance, Junction-to-Ambient (Note 3) SMC Package SMB Package (Note 4) | R _{θJA} | 71 73 | °C/W | |
| ELECTRICAL CHARACTERISTICS | | | • | |
| Maximum Instantaneous Forward Voltage (Note 5) | V _F | | V | |

| Maximum Instantaneous Forward Voltage (Note 5) ($i_F = 3.0 \text{ A}, T_J = 25^{\circ}\text{C}$) | V _F | 0.63 | V |
|---|----------------|-------------|----|
| Maximum Instantaneous Reverse Current (Note 5) (Rated dc Voltage, $T_J = 25^{\circ}$ C) (Rated dc Voltage, $T_J = 100^{\circ}$ C) | İR | 0.03 3.0 | mA |


Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.


2. Mounted with minimum recommended pad size, PC Board FR4.


3. 1 inch square pad size (1 x 0.5 inch for each lead) on FR4 board.

Typical Value; 1 inch square pad size (1 x 0.5 inch for each lead) on FR4 board. 4.

5. Pulse Test: Pulse Width = 300 μ s, Duty Cycle \leq 2.0%.










Figure 8. Thermal Response, Junction-to-Ambient, SMC Package






Figure 9. Typical Thermal Response, Junction-to-Ambient, SMB Package

PACKAGE DIMENSIONS

SMC CASE 403-03 ISSUE E




11



NOTES: 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. 2. CONTROLLING DIMENSION: INCH. 3. D DIMENSION SHALL BE MEASURED WITHIN DIMENSION P. 4. 403-01 THRU -02 OBSOLETE, NEW STANDARD 403-03.

| | MILLIMETERS | | | INCHES | | | |
|-----|--------------------|------|------|--------|-------|-------|--|
| DIM | MIN | NOM | MAX | MIN | NOM | MAX | |
| Α | 1.90 | 2.13 | 2.41 | 0.075 | 0.084 | 0.095 | |
| A1 | 0.05 | 0.10 | 0.15 | 0.002 | 0.004 | 0.006 | |
| b | 2.92 | 3.00 | 3.07 | 0.115 | 0.118 | 0.121 | |
| С | 0.15 | 0.23 | 0.30 | 0.006 | 0.009 | 0.012 | |
| D | 5.59 | 5.84 | 6.10 | 0.220 | 0.230 | 0.240 | |
| E | 6.60 | 6.86 | 7.11 | 0.260 | 0.270 | 0.280 | |
| HE | 7.75 | 7.94 | 8.13 | 0.305 | 0.313 | 0.320 | |
| L | 0.76 | 1.02 | 1.27 | 0.030 | 0.040 | 0.050 | |
| L1 | 0.51 REF 0.020 REF | | | | | | |


SOLDERING FOOTPRINT*




*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PACKAGE DIMENSIONS

SMB CASE 403A-03 **ISSUE H**







NOTES DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
CONTROLLING DIMENSION: INCH.


3. D DIMENSION SHALL BE MEASURED WITHIN DIMENSION P.

| | MILLIMETERS | | | INCHES | | |
|-----|-------------|------|------|-----------|-------|-------|
| DIM | MIN | NOM | MAX | MIN | NOM | MAX |
| Α | 1.90 | 2.20 | 2.28 | 0.075 | 0.087 | 0.090 |
| A1 | 0.05 | 0.10 | 0.19 | 0.002 | 0.004 | 0.007 |
| b | 1.96 | 2.03 | 2.20 | 0.077 | 0.080 | 0.087 |
| С | 0.15 | 0.23 | 0.31 | 0.006 | 0.009 | 0.012 |
| D | 3.30 | 3.56 | 3.95 | 0.130 | 0.140 | 0.156 |
| Е | 4.06 | 4.32 | 4.60 | 0.160 | 0.170 | 0.181 |
| HE | 5.21 | 5.44 | 5.60 | 0.205 | 0.214 | 0.220 |
| L | 0.76 | 1.02 | 1.60 | 0.030 | 0.040 | 0.063 |
| L1 | 0.51 REF | | | 0.020 REF | | |





SOLDERING FOOTPRINT*



*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and 💷 are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support:

Phone: 421 33 790 2910 Japan Customer Focus Center Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

ON Semiconductor: MBRS360T3G MBRS360BT3G NRVBS360BT3G