



DATE: 2005/09/08

•	

ITEM: QUARTZ CRYSTAL

TYPE: DSX321G

NOMINAL FREQUENCY: 16.00000MHz

1C216000CC0B

SPEC No.: 1N216000CC0B

"RoHS product "

Please acknowledge receipt of the specification attached hereto signing and returning to us one copy thereof.

RECEIVED OF SPECIFICATION				
DATE				
RECEIVED	(signature) (name)			

Pioneering New Breakthroughs in Electronics

DAISHINKU CORP.

1389 Shinzaike, Hiraoka-cho, Kakogawa, Hyogo 675-0194 Japan Phone(0794)25-3141 Fax(0794)25-1134

|--|

ENG.

1. SCOPE

(This specification applies to DSX321G 16MHz Crystal Unit.)

Country	Spec. No.
Indonesia	1C216000CC0B
Thailand	1N216000CC0B

2. ELECTRICAL CHARACTERISTICS

(This test shall be performed under the conditions of temp.at 25 +/- 3deg. C, humidity 60% max.)

2. 1 NOMINAL FREQUENCY 16.000000 MHz

2. 2 MODE Fundamental

2. 3 LOADING CAPACITANCE 12.0 pF

2. 4 FREQUENCY TOLERANCE +/- 10 ppm Max. at +25 deg.C +/- 3 deg.C

2. 5 DRIVE LEVEL 10 uW +/- 2 uW

2. 6 EQUIVALENT SERIES RESISTANCE 60 ohms Max. / Series

2. 7 OPERATING TEMPERATURE RANGE -40 deg.C to +85 deg.C

2. 8 FREQUENCY TEMPERATURE CHARACTERISTICS +/-30 ppm Max/ -40 deg. to +85 deg.C

2. 9 SHUNT CAPACITANCE 2.0 pF Max.

2.10 INSULATION RESISTANCE 500 Mohms Min. / DC100V +/- 15V

2.11 STORAGE TEMPERATURE RANGE -40 deg.C to +85 deg.C

3.CONSTRUCTION

3. 1 HOLDER DSX321G Ceramic Base

3. 2 DIMENSIONS AND MARKING Refer to Fig.-1 and Table-1.

3. 3 EMBOSS CARRIER TAPE & REEL Refer to Fig.-2,3,4,5 and Table-2.

3. 4 PACKING Refer to Fig.-6.

4.OTHER SPECIFICATIONS


4. 1 REFLOW CONDITIONS (REFERENCE) Refer to Fig.-7.

4. 2 LAND PATTERN (REFERENCE) Refer to Fig.-8.

4. 3 Environmental and mechanical performance shall be specified by attached general specification.

TITLE		Trigonometry	Unit	Scale
	DSX321G TYPE SURFACE MOUNT TYPE			
	QUARTZ CRYSTAL SPECIFICATION			
Date		Drawing No.	Rev.	Page
	2005/09/08	1C216000CC0B		1 / 7
	2003/09/08	1N216000CC0B		1 / /

< DIMENSIONS AND MARKING >



(Fig.-1)

Marking is Laser Marking:

Marking should be printed as follows:

Logo , Nominal Frequency , manufactured year & month

Logo and manufacturing location (1)

Made in Thailand -> marked as "D"upper bar.

Made in Indonesia -> marked as_"D" under bar.

Nominal Frequency (2) = Mark two dights from upper

(ex. 16.0000 MHz --> 16)

Manufacturing lot No.(3)

(year) ex. 2005 shall be marked as '5' (The last digit of the year)

(Month) ex. September shall be marked as 'J' (As shown in Table-1.)


(Table-1)

	Jan.	Feb.	Mar.	Apr.	May.	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
Ī	Α	В	С	D	Е	F	G	Н	J	K	L	М


TITLE		Trigonometry	Unit	Scale
	DSX321G TYPE SURFACE MOUNT TYPE			
	QUARTZ CRYSTAL SPECIFICATION			
Date		Drawing No.	Rev.	Page
	2005/09/08	1C216000CC0B		2 / 7
	2003/09/00	1N216000CC0B		2 / /

< EMBOSS CARRIER TAPE & REEL >

(1)Dimensions of embossed carrier tape



(2)Dimensions of tape reel



(Fig.-3)

TITLE		Trigonometry	Unit	Scale
	DSX321G TYPE SURFACE MOUNT TYPE			
	QUARTZ CRYSTAL SPECIFICATION			
Date		Drawing No.	Rev.	Page
	2005/09/08	1C216000CC0B		2 / 7
	2003/09/06	1N216000CC0B		3 / /

(Table-2)

(UNIT:mm)

	Item		Mark	Dimensions Angle
	Diamete	r	Α	180 dia. +0.0 / -3.0
Elango	Inside of Frange Outside of Frange		W1	9.0 + / - 0.3
Flange			W2	11.4 + / - 1.0
	Inside Diam	eter	В	60 dia. +1.0 / -0.0
			F1	3.0 + / - 0.2
		Width	F2	4.0 + / - 0.2
	Center Core Slit		F3	5.0 + / - 0.2
Center		Length	V	11.9
Core		Angle	q	120 deg.
	Spindle Diameter		С	13 dia. +/-0.2
	Key Seats	Width	Е	2.0 +/-0.5
		Length	Ū	10.5 +/-0.4
		Angle	q	120 deg.

(3)Storage condition

Temperature: +40 deg.C Max. Relative Humidity: 80% Max.

(4)Standard packing quantity 3,000 pcs/reel for 180 dia.

(5)Material of the tape

Tape	Material	
Carrier tape	Polystyrene+Carbon	
Cover tape	Polyester	

(6)Label contents

Type

Our specification No.

Your Part No.

Lot No.

Nominal Frequency

Quantity

Our Company Name


Producting Country

Stick a label on the each reel.

TITLE		Trigonometry	Unit	Scale
	DSX321G TYPE SURFACE MOUNT TYPE			
	QUARTZ CRYSTAL SPECIFICATION			
Date		Drawing No.	Rev.	Page
	2005/09/08	1C216000CC0B		1 / 7
	2003/09/08	1N216000CC0B		4 / /

(7)Taping dimension

Leader	Cover-tape	The length of cover-tape in the leader is more than 400mm
		including empty embossed area.
	Carrier-tape	After all products were packaged, must remain more than
		twenty pieces or 400mm empty area, which should be sealed
		by cover-tape.
Terminal	Cover-tape	The tip of cover-tape shall be fixed temporary by paper
		tape and roll around the core of reel one round.
	Carrier-tape	The empty embossed area which are sealed by cover-tape
		must remain more than 40mm.



(8) Joint of tape

The carrier-tape and cover-tape should not be jointed.


(9) Release strength of cover tape

It has to between 0.1N to 0.7N under following condition.

Pulling direction 165 deg. to 180 deg.

Speed 300mm/min.

Otherwise unless specified.




(Fig.-5)

Other standards shall be based on JIS C 0806₋₁₉₉₀.

TITLE	Trigonometry	Unit	Scale
DSX321G TYPE SURFACE MOUNT TYPE			
QUARTZ CRYSTAL SPECIFICATION			
Date	Drawing No.	Rev.	Page
2005/09/08	1C216000CC0B		E / 7
2005/09/06	1N216000CC0B		5 / /

< PACKING >

(1)STORAGE METHOD



Label contents

The type of product Lot No. Specification Quantity Shipment Day Remark

(Fig-6)

(2)BOX SIZE


From lot size packingsize shall be changed.

In the upper and lower part and the opening in box it shall be protected products using aircushion sheets.

TITLE		Trigonometry	Unit	Scale
DSX	321G TYPE SURFACE MOUNT TYPE			
QUA	RTZ CRYSTAL SPECIFICATION			
Date		Drawing No.	Rev.	Page
	2005/09/08	1C216000CC0B		6 / 7
	2003/09/08	1N216000CC0B		0 / /

< REFLOW CONDITIONS (REFERENCE) >


During the solder reflow process, please complete within following temperature, period. Reflow soldering shall be allowed only two times.



Total time: 240 s Max.

(Fig.-7)

< LAND PATTERN (REFERENCE) >



unit : mm

(Fig.-8)

TITLE		Trigonometry	Unit	Scale
	DSX321G TYPE SURFACE MOUNT TYPE			
	QUARTZ CRYSTAL SPECIFICATION			
Date		Drawing No.	Rev.	Page
	2005/09/08	1C216000CC0B		7 / 7
	2003/09/00	1N216000CC0B		, , ,

1.MECHANICAL ENDURANCE

1.1 SHOCK

After the following test, parts shall conform specification 3-1-3.

10cycles(60times) drop from 150 [cm] heights to concrete.

Further, parts shall be solderd on substrate, fixed bakelite materials (about 100[g]).

Substrate materials : Glass Epoxy

1 cycle : each 1 times of 6 directions

1.2 VIBRATION

After the following test, parts shall conform specification 3-1-2.

and no abnormal appearance shall be observed.

(1)Frequency of Vibration : 10[Hz] to 55[Hz]

(2)Amplitude(p-p) : Sine waves of 1.5[mm]

(3) Vibration axis : X.Y.Z

(4) Vibration period : 2 [h] for each axis

1.3 SUBSTRATE BENDING

After the following test,parts shall conform specification3-1-2. and no abnormality shall be observed in external appearance and sealing tightnen and others shall be based on ET-7403 of EIAJ.

Mount the specimen on substrate.


Apply the following pressure

 Direction
 : see Fig.-1

 Speed
 : 0.5 [mm/s]

 Hours
 : 5 +/- 1 [s]

 Amount of substrate
 : 3 [mm] Max.



(Fig.-1)

TITLE		Trigonometry	Unit	Scale
DSX321G TYF	PE SURFACE MOUNT TYPE			
QUARTZ CRY	STAL SPECIFICATION			
Date		Drawing No.	Rev.	Page
	2005/09/08	1C216000CC0B		Attached sheet
	2005/09/06	1N216000CC0B		1 / 4


1.4 SHEAR

After the following test, parts shall conform specification3-1-2. and no abnormality shall be observed in external appearance and sealing tightness and others shall be based on ET-7403 of EIAJ.

Mount the specimen on substrate.

Apply the following pressure

Weight : 10 [N] Hours : 10 +/- 1 [s] Direction : see Fig.-2



(Fig.-2)


1.5 BODY STRENGTH

After the following test, parts shall conform specification3-1-2. and no abnormality shall be observed in external appearance and sealing tightness and others shall be based on ET-7403 of EIAJ.

Mount the specimen on substrate.

Apply the following pressure

Weight : 10 [N] Hours : 10 +/- 1 [s] Direction : see Fig.-3



(Fig.-3)

TITLE		Trigonometry	Unit	Scale
	DSX321G TYPE SURFACE MOUNT TYPE			
	QUARTZ CRYSTAL SPECIFICATION			
Date		Drawing No.	Rev.	Page
	2005/09/08	1C216000CC0B		Attached sheet
	2003/09/08	1N216000CC0B		2 / 4

1.6 SEAL

Less than 2.0×10⁻⁹ [Pa m³/sec]. by Helium leak detector. Also, no serial bubble is observed by Fluorinert tests.

1.7 SOLDERABILITY

After the following test, more than 90[%] of terminal shall be covered by new solder.

3 seconds +/- 1 second dip in 235 [deg.C] +/- 5 [deg.C] solder. (Use rosin type flux for solder.)

2.ENVIRONMENTAL ENDURANCE

2.1 HUMIDITY

Two hours past at room temperature after following test, parts shall conform specification3-1-3. 240 hours +60 [deg.C] +/- 2 [deg.C], relative humidity 85[%] +/- 5[%].

2.2 LOW TEMPERATURE


Two hours past at room temperature after following test, parts shall conform specification3-1-3. 240 hours -40 [deg.C] +/- 2 [deg.C].

2.3 HIGH TEMPERATURE

Two hours past at room temperature after following test, parts shall conform specification3-1-3. 240 hours +85 [deg.C] +/- 2 [deg.C].

2.4 TEMPERATURE CYCLE

Two hours past at room temperature after 25 cycles of following test, parts shall conform specification3-1-3.



2.5 RESISTANCE TO SOLDERING HEAT

24 hours past at room temperature from following test, parts shall conform specification3-1-2.

VPS:30 Seconds in FC-70 vapor(215 [deg.C] Boiling Point)

TITLE	Trigonometry	Unit	Scale
DSX321G TYPE SURFACE MOUNT TYPE			
QUARTZ CRYSTAL SPECIFICATION			
Date	Drawing No.	Rev.	Page
2005/09/08	1C216000CC0B		Attached sheet
2005/09/06	1N216000CC0B		3 / 4

3.SPECIFICATION

Frequency Variation and Equivalent Resistance shall be within Table-1 after the test.

(Table-1)

	Frequency Variation	Equivalent Resistance
3-1-1	±1[ppm]	±10[%] or 1.5[ohm] max. (Use larger specification)
3-1-2	±2[ppm]	±15[%] or 2[ohms] max. (Use larger specification)
3-1-3	±5[ppm]	±20[%] or 3[ohms] max. (Use larger specification)
3-1-4	±10[ppm]	±20[%] or 3[ohms] max. (Use larger specification)

TITLE		Trigonometry	Unit	Scale
	DSX321G TYPE SURFACE MOUNT TYPE			
	QUARTZ CRYSTAL SPECIFICATION			
Date		Drawing No.	Rev.	Page
	2005/09/08	1C216000CC0B		Attached sheet
	2003/09/06	1N216000CC0B		4 / 4

2005-2054 REVISION RECORD

Rev.No	Date	Reason	Contents	Approved	Checked	Drawn
-	2005/09/08		The first edition.	M. lizuka	H. Matsuda	K. Nakanishi