

ITEM :

DATE : 2006/04/27

Techfaith Wireless Communication	Technology (Shanghai) Ltd	J.
----------------------------------	---------------------------	----

QUARTZ CRYSTAL

TYPE :

DSX321G

NOMINAL FREQUENCY :

24.00000MHz

SPEC No. :

1B224000BC0E 1C224000BC0E

USER PARTS NO . :

Please acknowledge receipt of this specification by signing and returning a copy to us.

RECEIPT			
DATE			
	(signature)		
RECEIVED	(name)		

General Manufacture of Quartz Devices

DAISHINKU CORP.

1389 Shinzaike, Hiraoka-cho, Kakogawa, Hyogo 675-0194 Japan http://www.kds.info/english.html

mp.//www.kds.imo/engilsh.m

Phone(81)794-25-3141

Fax (81)794-25-1134

C.ENG.


ENG.

	CTRICAL CHARACTERISTICS s test shall be performed under the conditions of temp.at :	25 +/- 3deg. C, humidity 60% max.)
1-1	NOMINAL FREQUENCY	24.000000 MHz
1-2	MODE	Fundamental
1-3	LOADING CAPACITANCE	12.0 pF
1-4	FREQUENCY TOLERANCE	+/- 20 ppm Max. at +25 deg.C +/- 3 deg.C
1-5	DRIVE LEVEL	10 uW +/- 2 uW
1-6	EQUIVALENT SERIES RESISTANCE	60 ohms Max. / Series
1-7	OPERATING TEMPERATURE RANGE	-10 deg.C to +70 deg.C
1-8	FREQUENCY TEMPERATURE CHARACTERISTICS	+/- 30 ppm Max. / -10 deg.C to +70 deg.C
1-9	SHUNT CAPACITANCE	2.0 pF Max.
1-10	INSULATION RESISTANCE	500 Mohms Min. / DC100V +/- 15V
1-11	STORAGE TEMPERATURE RANGE	-40 deg.C to +85 deg.C
2.CON	STRUCTION	
2-1	HOLDER	DSX321G Ceramic Base
2-2	DIMENSIONS AND MARKING	Refer to Fig1 and Table-1.
3.OTHE	ER SPECIFICATIONS	
3-1	EMBOSS CARRIER TAPE & REEL	Refer to Fig2,3,4,5 and Table-2.
3-2	PACKING	Refer to Fig6.
3-3	REFLOW CONDITIONS (REFERENCE)	Refer to Fig7.
3-4	LAND PATTERN (REFERENCE)	Refer to Fig8.
		the effective contraction of the state

4. Environmental and mechanical performance shall be specified by attached general specification.

TITLE DSX321G TYPE SURFACE MOUNT TYPE QUARTZ CRYSTAL SPECIFICATION	Trigonometry	Unit	Scale
Date	Drawing No.	Rev.	Page
2006/04/27	1B224000BC0E 1C224000BC0E		1 / 7

< DIMENSIONS AND MARKING >



unit : mm Tolerance : +/-0.1

(Fig.-1)

Marking is Laser Marking:

Marking should be printed as follows:

Logo, Nominal Frequency, manufactured year & month

Logo and manufacturing location (1)

Producing District	Marking	Our Specification.No.
Japan	D	1B224000BC0E
Indonesia	<u>D</u>	1C224000BC0E

Nominal Frequency (2) = Mark two dights from upper

24.0000 MHz --> (ex. 24)

Manufacturing lot No.(3)


shall be marked as ' 6 ' (The last digit of the year) (year) ex. 2006 shall be marked as ' D ' (As shown in Table-1.) (Month) ex. April

(Table-1)

Jan.	Feb.	Mar.	Apr.	May.	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
Α	В	С	D	E	F	G	H	J	K	L	М

TITLE	Trigonometry	Unit	Scale
DSX321G TYPE SURFACE MOUNT TYPE			
QUARTZ CRYSTAL SPECIFICATION			
Date	Drawing No.	Rev.	Page
2006/04/27	1B224000BC0E		
2000/01/21	1C224000BC0E		2 / 7

< EMBOSS CARRIER TAPE & REEL >



1C224000BC0E

2006/04/27

3

1

7

		(Tal	ble-2)		
				(UNIT:mm)	
	Item		Mark	Dimensions Angle	
	Diameter		Α	180 dia. +0.0 / -3.0	
Flongo	Inside of Fra	inge	W1	9.0 + / - 0.3	
Flange	Outside of Fra		W2	11.4 + / - 1.0	
			В	60 dia. +1.0 / -0.0	
				F1	3.0 + / - 0.2
		Width	F2	4.0 + / - 0.2	
	Center Core Slit		F3	5.0 + / - 0.2	
Center		Length	V	11.9	
Core		Angle	q	120 deg.	
	Spindle Diam	neter	С	13 dia. +/-0.2	
		Width	E	2.0 +/-0.5	
	Key Seats	Length	U	10.5 +/-0.4	
		Angle	q	120 deg.	

(3)Storage condition

Temperature : +40 deg.C Max.

Relative Humidity : 80% Max.

(It is a guaranteed term because it obtains an excellent soldering: 6 months)

(4)Standard packing quantity

3,000 pcs/reel for 180 dia.


(5)Material of the tape

Таре	Material
Carrier tape	Polystyrene+Carbon
Cover tape	Polyester

(6)Label contents Type Our specification No. Your Part No. Lot No. Nominal Frequency Quantity Our Company Name Producting Country


Stick a label on the each reel.

TITLE DSX321G TYPE SURFACE MOUNT TYPE QUARTZ CRYSTAL SPECIFICATION	Trigonometry	Unit	Scale
Date	Drawing No.	Rev.	Page
2006/04/27	1B224000BC0E 1C224000BC0E		4 / 7



< PACKING >

(1)STORAGE METHOD



(Fig-6)

(2)BOX SIZE


From lot size packingsize shall be changed. In the upper and lower part and the opening in box it shall be protected products using

in the upper and lower part and the opening in box it shall be protected products using aircushion sheets.

TITLE DSX321G TYPE SURFACE MOUNT TYPE QUARTZ CRYSTAL SPECIFICATION	Trigonometry	Unit	Scale
Date	Drawing No.	Rev.	Page
2006/04/27	1B224000BC0E 1C224000BC0E		6 / 7

< REFLOW CONDITIONS (REFERENCE) >

During the solder reflow process, please complete within following temperature, period. Reflow soldering shall be allowed only two times.



7

1 1 54001			
1.1 SHOCK After the following test parts shall conform specifi	cation3-1-2		
After the following test,parts shall conform specifi 10cycles(60times) drop from 150 [cm] heights to			
Further, parts shall be solderd on substrate, fixed			
	ass Epoxy		
	ch 1 times of 6 directions		
1.2 VIBRATION After the following test,parts shall conform specifi	cation3-1-1		
and no abnormal appearance shall be observed.			
	[Hz] to 55[Hz]		
(2)Amplitude(p-p) : Sir	ne waves of 1.5[mm]		
(3)Vibration axis : X.V	ſ.Z		
(4)Vibration period : 2 [h] for each axis		
1.3 SUBSTRATE BENDING			
After the following test,parts shall conform specifi	cation3-1-1.		
and no abnormality shall be observed in external	appearance and sealing		
tightnen and others shall be based on ET-7403 of	f EIAJ.		
Mount the specimen on substrate.			
Apply the following pressure			
	e Fig1		
	5 [mm/s]		
	-/- 1 [s]		
Amount of substrate : 3 [mm] Max.		
pressure jig	o		
e de la companya de			
L	P.C.B.		

	45+/-2		
(Fig.	-1)		
TITLE	Trigonometry	Unit	Scale
DSX321G TYPE SURFACE MOUNT TYPE	Trigonometry	Unit	Scale
DSX321G TYPE SURFACE MOUNT TYPE QUARTZ CRYSTAL SPECIFICATION			
DSX321G TYPE SURFACE MOUNT TYPE	Trigonometry Drawing No.	Unit Rev.	Page
DSX321G TYPE SURFACE MOUNT TYPE QUARTZ CRYSTAL SPECIFICATION			


1.4 SHEAR

After the following test, parts shall conform specification3-1-1. and no abnormality shall be observed in external appearance and sealing tightness and others shall be based on ET-7403 of EIAJ.

Mount the specimen on substrate.

Apply the following pressure

Weight	:	10 [N]
Hours	:	10 +/- 1 [s]
Direction	:	see Fig2



(Fig.-2)


1.5 BODY STRENGTH

After the following test, parts shall conform specification3-1-1. and no abnormality shall be observed in external appearance and sealing tightness and others shall be based on ET-7403 of EIAJ.

Mount the specimen on substrate.

Apply the following pressure

Weight	:	10 [N]
Hours	:	10 +/- 1 [s]
Direction	:	see Fig3



(Fig.-3)

TITLE DSX321G TYPE SURFACE MOUNT TYPE QUARTZ CRYSTAL SPECIFICATION	Trigonometry	Unit	Scale
Date	Drawing No.	Rev.	Page Attached sheet
2006/04/27	1B224000BC0E 1C224000BC0E		2 / 5

1.6 SEAL

Less than 2.0×10^{-9} [Pa m³/sec]. by Helium leak detector. Also, no serial bubble is observed by Fluorinert tests.

1.7 SOLDERABILITY

After the following test, more than 90[%] of terminal shall be covered by new solder. 3 seconds +/- 1 second dip in 235 [deg.C] +/- 5 [deg.C] solder. (Use rosin type flux for solder.)

2.ENVIRONMENTAL ENDURANCE

2.1 HUMIDITY

Two hours past at room temperature after following test, parts shall conform specification3-1-2. 240 hours +60 [deg.C] +/- 2 [deg.C] , relative humidity 85[%] +/- 5[%].

2.2 LOW TEMPERATURE


Two hours past at room temperature after following test, parts shall conform specification3-1-2. 240 hours -40 [deg.C] +/- 2 [deg.C].

2.3 HIGH TEMPERATURE

Two hours past at room temperature after following test, parts shall conform specification3-1-2. 240 hours +85 [deg.C] +/- 2 [deg.C].

2.4 TEMPERATURE CYCLE

Two hours past at room temperature after 25 cycles of following test, parts shall conform specification3-1-2.



2.5 RESISTANCE TO SOLDERING HEAT 24 hours past at room temperature from following test, parts shall conform specification3-1-2. VPS:30 Seconds in FC-70 vapor(215 [deg.C] Boiling Point)

	Trigonomotry	l locit	Casla
TITLE	Trigonometry	Unit	Scale
DSX321G TYPE SURFACE MOUNT TYPE			
QUARTZ CRYSTAL SPECIFICATION			
Date	Drawing No.	Rev.	Page
			Attached sheet
	1B224000BC0E		
2006/04/27	1C224000BC0E		3 / 5
	1022 1000B00E		Ŭ, Ŭ

3.SPECIFICATION

Frequency Variation and Equivalent Resistance shall be within Table-1 after the test.

		(Table-1)	
Frequency Variation Equivalent Resistance			
3-1-1	±2[ppm]	±15[%] or 2[ohms] max. (Use larger specification)	
3-1-2	±5[ppm]	±20[%] or 3[ohms] max. (Use larger specification)	
3-1-3	±10[ppm]	±20[%] or 3[ohms] max. (Use larger specification)	

TITLE	Trigonometry	Unit	Scale
DSX321G TYPE SURFACE MOUNT TYPE			
QUARTZ CRYSTAL SPECIFICATION			
Date	Drawing No.	Rev.	Page
			Attached sheet
2006/04/27	1B224000BC0E		
2000/04/27	1C224000BC0E		4 / 5

[DSX321G SERIES , IN USE]

1.SOLDERING

Please perform the attached Reflow conditions to reference within 2 times.

2.MOUNT

Although it corresponds to automatic mounting, please carry out the loading test by the loading machine to be used, and check that there is no influence in the characteristic. Please be careful of the Curve not to influence the characteristic of a product, and a soldering state at the process which makes a substrate generate the Curve, the break of a board etc. .

3.WASHING

About use of the washing liquid of a basin system, an alcoholic system, and a chlorofluorocarbon-replacing material system, it is checking that it is satisfactory. However please consult in advance about other washing liquid. Although the check about ultrasonic washing is performed, since it is an examination with a simple substance, the check for the second time by the use state is recommended.

4.THE CAUTIONS ON USE

The piece of crystal it is processed very smaller than the conventional thing inside DSX321G series crystal unit may be damaged,

if excessive excitation electric power is applied.

Please use it below with the value specified on a catalog and specifications.

Please refrain from forming patterns under crystal resonators since there is

a possibility to cause crack in base.

If the temperature is higher than 280 [deg.C], there is a possibility for the sealing glass to remelt. Avoid using the product at temperature higher than specified.

5.HANDLING OF A PRODUCT

DSX321G series has sufficient intensity to fall and vibration. However when too much shock is added according to a certain cause, the use after a characteristic check is recommended.

6.STORAGE

Since the soldering nature of a terminal may be degraded, please avoid storage in high temperature and a humid place. Please keep it in the place which direct rays do not hit and dew condensation does not generate.

TITLE	Trigonometry	Unit	Scale
DSX321G TYPE SURFACE MOUNT TYPE			
QUARTZ CRYSTAL SPECIFICATION			
Date	Drawing No.	Rev.	Page
			Attached sheet
2006/04/27	1B224000BC0E		
2000/04/27	1C224000BC0E		5 / 5

2006-0570 REVISION RECORD

Rev.No	Date	Reason	Contents	Approved	Checked	Drawn
-	2006/04/27		The first edition.	T. Nakamura	H. Matsuda	K. Nakanishi
Ţ						