

Metal oxide varistor

Disk Type

Series/Type: L32K460PK401 Ordering code: B72232M0461K401

Date: 2016-03-09

Version: a

© EPCOS AG 2016. Reproduction, publication and dissemination of this publication, enclosures hereto and the information contained therein without EPCOS' prior express consent is prohibited.

EPCOS AG is a TDK Group Company.



Disk Type L32K460PK401

Applications

Overvoltage protection.

Suitable for use in industrial applications.

Features

· High peak surge current rating of 25kA


Nomenclature

L = Disc type, metallized 32 = Rated disk diameter

K = Tolerance of varistor voltage at 1 mA: ±10%

460 = Max. AC voltage
P = Epoxy resin coating
K401 = Customized cable leads

Dimensional drawing in mm





| Metal oxide varistor | B72232M0461K401 |
|----------------------|-----------------|
| Disk Type | L32K460PK401 |


Electrical data

| Maximum Ratings (85 °C) | | | | |
|------------------------------|--------|-------------|---|------------|
| Max. operating AC voltage | | V_{RMS} | = | 460 V |
| Max. operating DC voltage | | V_{DC} | = | 615 V |
| Surge current (8/20 µs) | 1 time | I_{max} | = | 25000 A |
| Energy absorption (2 ms) | | W_{max} | = | 660 J |
| Average power dissipation | | P_{max} | = | 1.2 W |
| Characteristics (25 °C): | | | | |
| Varistor voltage at 1 mA | | V_V | = | 750 V ±10% |
| Clamping voltage at 200 A | | $V_{C,max}$ | = | 1240 V |
| Typical capacitance at 1 kHz | | С | = | 1200 pF |




Disk Type L32K460PK401

v/i characteristics



Derating





Disk Type L32K460PK401

Special electrical data for use in accordance with TRMSCAAP2 REV 2

Maximum continuous operating voltage (U_c) 440 V_{RMS} Rated voltage (U_r) 480 V_{RMS} Nominal lightning discharge current In (8/20 μ s) 5 kA

Peak residual voltage for 8/20 µs current impulse

of the following impulse:

1 kA

5 kA $2500 \text{ V}_{\text{peak}} \text{ max}.$

10 kA

steep current impulse residual voltage 2500 V_{peak} max.

virtual front time T1: 2 µs ±10%

virtual time to half value

of the tail: $<20~\mu s$ peak value of current : $5~kA~\pm5\%$

long duration current impulse withstand test

peak current 75 A virtual duration of peak 1000 µs

rectangular pulse shape in accordance with IEC 60-1

number of groups of applications 4 number of impulses per group 5

interval between groups 25 - 30 minutes interval between impulses 50 - 60 seconds

visual examination: no visible damage

electrical measurement: change of varistor voltage less than 10 %

operating duty test

initial measurement: residual voltage at $ln = 5 kA (8/20 \mu s)$

conditioning: 20 impulses at $In = 5 \text{ kA} (8/20 \mu\text{s})$ in 4 groups of 5 impulses;

interval between impulses: 50 - 60 seconds interval between groups: 25 - 30 minutes superimposed on continuous operating voltage +20%

 $(1.2 * U_c = 528 V_{RMS})$



Disk Type L32K460PK401

Special electrical data for use in accordance with TRMSCAAP2 REV 2 (cont'd)

high current impulse 4/10 us:

1 impulse at Imax = 30 kA preheat to 60 °C ±3 °C 1 impulse at Imax = 30 kA

rated voltage $U_r = 480 \text{ V}$ for 10 seconds

continuous operating voltage $U_c = 440 \text{ V}$ for 30 minutes

cool to ambient , 20 °C ±15 °C

requirement: power dissipation decreases at least during

the last 15 minutes of U_c application

measurement:residual voltage at $In = 5 \text{ kA} (8/20 \mu\text{s})$

requirement: change of residual voltage less 10 %

no visible damage



Disk Type L32K460PK401

Cautions and warnings

General

- EPCOS metal oxide varistors (SIOVs) are designed for specific applications and should not be used for purposes not identified in our specifications, application notes and data books unless otherwise agreed with EPCOS during the design-in-phase.
- 2. Ensure suitability of SIOVs through reliability testing during the design-in phase. The SIOVs should be evaluated taking into consideration worst-case conditions.
- 3. For applications of SIOVs in line-to ground circuits based on various international and local standards there are restrictions existing or additional safety measures required.

Storage

- 1. Store SIOVs only in original packaging. Do not open the package before storage.
- 2. Storage conditions in original packaging:

Storage temperature: -25 °C ... +45 °C Relative humidity: <75% annual average,

<95% on maximum 30 days a year.

Dew precipitation: Is to be avoided.

- 3. Avoid contamination of SIOVs surface during storage, handling and processing.
- 4. Avoid storage of SIOVs in harmful environments which can affect the function during long-term operation (examples given under operation precautions).
- 5. The SIOV type series should be soldered within the time specified.

SIOV-S, -Q, -LS 24 month ETFV and SFS types 12 month.

Handling

- 1. SIOVs must not be dropped.
- 2. Components must not be touched with bare hands. Gloves are recommended.
- Avoid contamination of the surface of SIOV electrodes during handling, be careful of the sharp edge of SIOV electrodes.



Disk Type L32K460PK401

Soldering (where applicable)

- 1. Use rosin-type flux or non-activated flux.
- 2. Insufficient preheating may cause ceramic cracks.
- 3. Rapid cooling by dipping in solvent is not recommended.
- 4. Complete removal of flux is recommended.

Mounting

- 1. Potting, sealing or adhesive compounds can produce chemical reactions in the SIOV ceramic that will degrade the component's electrical characteristics.
- 2. Overloading SIOVs may result in ruptured packages and expulsion of hot materials. For this reason the SIOVs should be physically shielded from adjacent components.

Operation

- 1. Use SIOVs only within the specified temperature operating range
- 2. Use SIOVs only within the specified voltage and current ranges.
- 3. Environmental conditions must not harm the SIOVs. Use SIOVs only in normal atmospheric con-

ditions. Avoid use in the presence of deoxidizing gases (chlorine gas, hydrogen sulfide gas, ammonia gas, sulfuric acid gas, etc), corrosive agents, humid or salty conditions, Avoid contact with any liquids and solvents.

Display of ordering codes for EPCOS products

The ordering code for one and the same EPCOS product can be represented differently in data sheets, data books, other publications, on the EPCOS website, or in order-related documents such as shipping notes, order confirmations and product labels. The varying representations of the ordering codes are due to different processes employed and do not affect the specifications of the respective products. Detailed information can be found on the Internet under www.epcos.com/orderingcodes



Important notes

The following applies to all products named in this publication:

- 1. Some parts of this publication contain statements about the suitability of our products for certain areas of application. These statements are based on our knowledge of typical requirements that are often placed on our products in the areas of application concerned. We nevertheless expressly point out that such statements cannot be regarded as binding statements about the suitability of our products for a particular customer application. As a rule, EPCOS is either unfamiliar with individual customer applications or less familiar with them than the customers themselves. For these reasons, it is always ultimately incumbent on the customer to check and decide whether an EPCOS product with the properties described in the product specification is suitable for use in a particular customer application.
- 2. We also point out that in individual cases, a malfunction of electronic components or failure before the end of their usual service life cannot be completely ruled out in the current state of the art, even if they are operated as specified. In customer applications requiring a very high level of operational safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health (e.g. in accident prevention or life-saving systems), it must therefore be ensured by means of suitable design of the customer application or other action taken by the customer (e.g. installation of protective circuitry or redundancy) that no injury or damage is sustained by third parties in the event of malfunction or failure of an electronic component.
- 3. The warnings, cautions and product-specific notes must be observed.
- 4. In order to satisfy certain technical requirements, some of the products described in this publication may contain substances subject to restrictions in certain jurisdictions (e.g. because they are classed as hazardous). Useful information on this will be found in our Material Data Sheets on the Internet (www.epcos.com/material). Should you have any more detailed questions, please contact our sales offices.
- 5. We constantly strive to improve our products. Consequently, the products described in this publication may change from time to time. The same is true of the corresponding product specifications. Please check therefore to what extent product descriptions and specifications contained in this publication are still applicable before or when you place an order. We also reserve the right to discontinue production and delivery of products. Consequently, we cannot guarantee that all products named in this publication will always be available. The aforementioned does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.
- 6. Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms of Delivery for Products and Services in the Electrical Industry" published by the German Electrical and Electronics Industry Association (ZVEI).
- 7. The trade names EPCOS, Alu-X, CeraDiode, CeraLink, CeraPad, CeraPlas, CSMP, CSSP, CTVS, DeltaCap, DigiSiMic, DSSP, ExoCore, FilterCap, FormFit, LeaXield, MiniBlue, MiniCell, MKD, MKK, MotorCap, PCC, PhaseCap, PhaseCube, PhaseMod, PhiCap, PQSine, SIFERRIT, SIFI, SIKOREL, SilverCap, SIMDAD, SiMic, SIMID, SineFormer, SIOV, SIP5D, SIP5K, TFAP, ThermoFuse, WindCap are **trademarks registered or pending** in Europe and in other countries. Further information will be found on the Internet at www.epcos.com/trademarks.