

Radial Lead Type

OS-CON



Series : **SXE**


Features

- Super high voltage (100 V.DC max.)
- RoHS compliance, Halogen free


Specifications

Size code	E7	F8	E12	F13
Category temperature range	-55 °C to +125 °C			
Rated voltage range	100 V.DC		63 V.DC to 100 V.DC	100 V.DC
Rated capacitance range	6.8 μF	15 μF	15 μF to 33 μF	18 μF to 22 μF
Capacitance tolerance	±20 % (120 Hz / + 20 °C)			
Leakage current	Please see the attached characteristics list			
Dissipation factor (tan δ)	Please see the attached characteristics list			
Endurance	+125 °C, 1000 h, rated voltage applied			
	Capacitance change	Within ±20 % of the initial value		
	tan δ	≤ 200 % of the initial limit		
	DC leakage current	Within the initial limit		
Damp heat (Steady State)	+60 °C, 90 % to 95 %, 1000 h, No-applied voltage			
	Capacitance change	Within ±20 % of the initial value		
	tan δ	≤ 150 % of the initial limit		
	DC leakage current	Within the initial limit (after voltage processing)		

Marking



Dimensions (not to scale)



Characteristics list

Series	Rated voltage (V.DC)	Rated capacitance (μF)	Case size (mm)		Size code	Specifications					Part number
			φD	L		Ripple* ¹ current (mAr.m.s.)	Allowable* ¹ ripple current (mAr.m.s.)	ESR* ² (mΩ max.)	tan δ* ³	LC* ⁴ (μA)	
SXE	63	33	8.0	12.0	E12	930	2950	25	0.12	104	63SXE33M
	100	6.8	8.0	7.0	E7	340	1100	60	0.12	34	100SXE6R8M
		15	10.0	8.0	F8	630	2000	60	0.12	75	100SXE15MX
		15	8.0	12.0	E12	730	2350	40	0.12	75	100SXE15M
		18	10.0	13.0	F13	940	3000	30	0.12	90	100SXE18M
22	10.0	13.0	940	3000		30	0.12	110	100SXE22M		

*¹ Ripple current (100 kHz / +105 °C < Tx ≤ 125 °C), Allowable ripple current (100 kHz / Tx ≤ 105 °C)

*² ESR (100 kHz to 300 kHz / +20 °C) *³ tan δ (120 Hz / +20 °C) *⁴ After 2 minutes

◆ Please refer to each page in this catalog for "Reflow conditions" and "Taping specifications".

Frequency correction factor for ripple current

Frequency	120 Hz ≤ f < 1 kHz	1 kHz ≤ f < 10 kHz	10 kHz ≤ f < 100 kHz	100 kHz ≤ f < 500 kHz
Coefficient	0.05	0.3	0.7	1

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use.

Should a safety concern arise regarding this product, please be sure to contact us immediately.