

308 Constitution Drive Menlo Park, CA USA www.circuitprotection.com

PolySwitch® PTC Devices

Overcurrent Protection Device

PRODUCT: RXEF030

DOCUMENT: SCD25217

REV LETTER: H

REV DATE: DECEMBER 06, 2011

PAGE NO.: 1 OF 1

Specification Status: Released

Electrical Rating

Voltage: 72 V max (AC or DC) Current: 40 A max (AC or DC)


Insulating Material:

Cured, Flame Retardant Epoxy Polymer meets UL94 V-0 Requirements

Lead Material:

24 AWG Tin Plated Copper Clad Steel

Marking:








TABLE I. DIMENSIONS:

	Α		В		С		D		Е	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
mm:		7.4		12.7	4.3	5.8	7.6			3.0
in*:		(0.29)		(0.50)	(0.17)	(0.23)	(0.30)			(0.12)

^{*}Rounded off approximation

TABLE II. PERFORMANCE RATINGS:

	I HOLD RATED CURRENT	CURRENT RATINGS		INITIAL RESISTANCE VALUES		TIME TO TRIP	ONE HOUR POST-TRIP RESISTANCE STANDARD TRIP	TRIPPED- STATE POWER DISSIPATION	
F	AMPERES	AMPERES		OHMS		SECONDS AT	OHMS	WATTS	WATTS
	AT 20°C	AT 20°C		AT 20°C		20°C, 1.5A	AT 20°C	AT 20°C	AT 20°C
	HOLD	HOLD	TRIP	MIN	MAX	MAX	MAX	NOMINAL	MAX
	0.30	0.30	0.60	0.88	1.33	3.0	2.10	0.49	0.77

Agency Recognitions:

UL, CSA, TUV

Reference Documents:

PS300

Precedence:

This specification takes precedence over documents referenced herein.

Effectivity:

CAUTION:

Reference documents shall be the issue in effect on the date of invitation for bid.

Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

Materials Information

ROHS Compliant ELV Compliant

Pb-Free

Halogen Free*

Directive 2002/95/EC Compliant Directive 2000/53/EC Compliant





© 2005, 2011 Tyco Electronics Corporation, a TE Connectivity Ltd. Company. All rights reserved.

^{*} Halogen Free refers to: Br≤900ppm, Cl≤900ppm, Br+Cl≤1500ppm.