

## **Switchmode Schottky Barrier Power Rectifiers**

Using the Schottky Barrier principle with high temperature operation metal. The properitary barrier technology allows for reliable operation up to  $150^{\circ}$ C junction temperature. Typical application are in switching Mode Power Supplies such as adaptators, Photovoltaic Solar cell protection,freewheeling and polarity protection diodes.

### **Features**

- \* Ultra Low Forward Voltage.
- \*Low Switching noise.
- \*High Current Capacity
- \*Low Power Loss & High efficiency.
- \*150°C Operating Junction Temperature
- \*Low Stored Charge Majority Carrier Conduction.
- \*Plastic Material used Carries Underwriters Laboratory

Flammability Classification 94V-O



\* In compliance with EU RoHs 2002/95/EC directives

## **MAXIMUM RATINGS**

Characteristic	Symbol	SR504L	Unit
Peak Repetitive Reverse Voltage Working Peak Reverse Voltage DC Blocking Voltage	V <sub>RRM</sub> V <sub>RWM</sub> V <sub>R</sub>	40	V
RMS Reverse Voltage	$V_{R(RMS)}$	28	V
Average Rectifier Forward Current	I <sub>F(AV)</sub>	5	Α
Peak Repetitive Forward Current (Rate V <sub>R</sub> , Square Wave, 20kHz)	I <sub>FM</sub>	10	Α
Non-Repetitive Peak Surge Current (Surge applied at rate load conditions halfware, single phase, 60Hz)	I <sub>FSM</sub>	200	Α
Operating and Storage Junction Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	-65 to +150	$^{\circ}\!\mathbb{C}$

# THERMAL RESISTANCES


Typical Thermal Resistance junction to body	R <sub>θ j-c</sub>	55	°C/w
---	--------------------	----	------


## **ELECTRIAL CHARACTERISTICS**

Characteristic	Symbol		SR504L	-	Unit
Maximum Instantaneous Forward Voltage		Min	Тур.	Max.	
( $I_F = 0.1 \text{ Amp T}_C = 25^{\circ}C$ )	V <sub>F</sub>		0.28	0.30	V
( $I_F$ =2.5 Amp $T_C$ = 25 $^{\circ}$ C)	V F		0.39	0.42	V
( $I_F$ =5.0 Amp $T_C$ = 25 $^{\circ}$ C )			0.44	0.49	
Maximum Instantaneous Reverse Current					
( Rated DC Voltage, T <sub>C</sub> = 25°C)	$I_R$		0.2		mA
( Rated DC Voltage, T <sub>C</sub> = 100℃)			30		

### SCHOTTKY BARRIER RECTIFIERS

5 AMPERES 40VOLTS





DIM	MILLIMETERS		
DIIVI	MIN	MAX	
Α	5.00	5.60	
В	25.40		
С	8.50	9.50	
D	1.20	1.30	

CASE--Transfer molded plastic

POLARITY--Cathode indicated

polarity band

