

# **Positive Thermal Coefficent Diodes**

## RLVR240-012~055 Series

The RLVR240 Series is designed to protect against short duration high voltage fault currents (power cross or power induction surge) typically found in telecom applications. The series can be used to help telecom networking equipment meet the protection requirements specified in ITU K.20 and K.21.

## **Features**


- 0.12 0.55 hold current range, 240VAC operating voltage
- 240VAC interrupt rating
- Fast time—to-trip
- · Binned and sorted narrow resistance ranges available
- RoHS compliant, Lead- Free and Halogen-Free\*

# **Applications**

- Customer Premises Equipment (CPE)
- Central Office (CO)/ telecom centers
- LAN/WAN equipment
- Access equipment
- PC peripherals
- Point-of-sale (POS) equipment
- PCMCIA cards
- USB port protection USB 2.0, 3.0 & OTG
- HDMI 1.4 Source protection
- Computers&peripherals
- General Electronics




#### **Dimension**





# **Part Marking System**



		А	В	С	D	Е	F
Type Number	Figure	mm	mm	mm	mm	mm	mm
		Max	Max	Max	Min	typ	Min
RLVR240-012	1	8.3	12.9	3.8	7.6	5.1	0.6
RLVR240-016	1	9.9	13.8	3.8	7.6	5.1	0.6
RLVR240-025	2	9.6	18.8	3.8	7.6	5.1	0.6
RLVR240-033	2	11.4	29.0	3.8	7.6	5.1	0.6
RLVR240-040	2	11.5	20.9	3.8	7.6	5.1	0.6
RLVR240-055	2	14.0	22.4	4.1	7.6	5.1	0.6

Fi ure 2

## **Electriacl Characteristics**

Type Number	lhold	Itrip	Vmax	Imax	P d max.	Resis	stance
	(A)	(A)	(VAC)	(A)	(W)	Rmin (Ω)	R1max (Ω)
RLVR240-012	0.12	0.30	240	1	1	3.0	6.5
RLVR240-016	0.16	0.37	240	3	1.5	2.5	4.1
RLVR240-025	0.25	0.56	240	3	1.5	1.3	2.1
RLVR240-033	0.33	0.74	240	3	1 .5	0.77	1.24
RLVR240-040	0.40	0.90	240	3	1.5	0.60	0.97
RLVR240-055	0.55	1.25	240	3	1.5	0.45	0.73

Ihold = Hold current: maximum current device will pass without tripping in 23°C still air.

Rmin = Minimum resistance of device in initial (un-soldered) state.

Itrip = Trip current: minimum current at which the device will trip in 23°C still air.

Rtyp = Typical resistance of device in initial (un-soldered) state.

Vint = Maximum voltage the device can withstand without damage at rated current (Imax)

Vop= The device regular operation voltage

Imax = Maximum fault current device can withstand without damage at rated voltage (Vmax)

Pd = Power dissipated from device when in the tripped state at 23°C still air.

R<sub>1</sub>max = Maximum resistance of device at 20°C measured one hour after tripping.

Caution: Operation beyond the specified rating may result in damage and possible arcing and flame.

### Soldering Parameters - Solder Reflow


Condition	Reflow		
PeakTemp/ DurationTime	260°C <u>≥</u> 5 Sec		
≧ 220°C	30 Sec ~ 60 Sec		
Preheat 160°C ~ 190°C	60 Sec ~ 90 Sec		
Storage Condition	0°C~35°C, <u>≤</u> 70%RH		

- Recommended reflow methods: IR, vapor phase oven, hot air oven, N<sub>2</sub> environment for lead-free.
- Devices are not designed to be wave soldered to the bottom side of the board.
- Devices can be cleaned using standard industry methods and solvents.

Note: If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

## Physical Specifications

	Lead Material	Tin-plated Copper			
	Soldering Characteristics	Solderability per MIL-STD-202, Method 208E			
	Insulating Material	Cured, flame retardant epoxy polymer meets UL94V-0 requirements.			
	Device Labeling	Marked with 'LF', voltage, current rating, and date code.			



#### **Environmental Specifications**

Operating/Storage Temperature	-40°C to +85°C	
Maximum Device Surface Temperature in Tripped State	125°C	
Passive Aging	65°C/85°C, 1000 hours	
Humidity Aging	+85°C, 85% R.H,.1000 hours	
Thermal Shock	MIL-STD-202F, Method 107G +125°C to -55°C 10 times	
Solvent Resistance	MIL-STD-202, Method 215F	
Moisture Sesitivity Level	Level 1, J-STD-020C	

Email: jack@ruilon.com

Website: http://www.ruilon.com

RUILONG.YUAN CO.,LTD Tel: +86- 0755-82908296 Fax: +86- 0755-82908002

RuiLongYuan Electronics are trademarks.

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. RUILONYUAN Electronics reserves the right to change or update, without notice, any information contained in this publication; to change, without notice, the design, construction, processing, or specification of any product; and to discontinue or limit production or distribution of any product. This publication supersedes and replaces all information previously supplied. Without expressed or written consent by an officer of RUILONYUAN Electronics, RUILONYUAN Electronics does not authorize the use of any of its products as components in nuclear facility applications, aerospace, or in critical life support devices or systems. RUILONYUAN Electronics expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. RUILONYUAN Electronics' only obligations are those in the RUILONYUAN Electronics Standard Terms and Conditions of Sale and in no case will RUILONYUAN Electronics be liable for any incidental, indirect, or consequential damages.