








PRODUCT NO.	1
DISC10THGET	2
RoHS compliant	3



RECOMMENDED P.C.B. LAYOUT (TOP VIEW)

- NOTES :
- 1> Specification:
 - 1> Operating force: 1000gf Max
 - 2> Operating Temperature: -40° to +85°
 - 3> Storage Temperature: -40° to +85°
 - 4> Mechanical Life: 3000cycles minimum
 - 5> Electrical Life: 2000cycles 25mA 24VDC
 2. PLATING:
 - GOLD FLASH 1u"(min.) SOLDER TAIL,
 - 3u" GOLD PLATING ON THE CONTACT AREA,
 - WITH 50u" NICKEL UNDERPLATING OVERALL.

3. PART NUMBER DESCRIPTION



Number	Part Name	Material	Finished
①	Actuator	UL94 VO	White
②	Cover	UL94 VO	Black
③	Movable	Copper Alloy	3u"Gold
④	Terminal	Brass	1u"Gold
⑤	Base	UL94 VO	Black
⑥	Terminal Contact	Brass	3u"Gold
⑦	Mylar	UL94 VO	0.05mm

TOLERANCE UNLESS OTHERWISE SPECIFIED		INSPECTION COPY	
LINER	ANGLES	PROJECTION	
0 ± 0.25	0. ± 2'	BY DISC SERIES PITCH 2.54mm	
.00 ± 0.15	.0 ± 1'	PRODUCT FAMILY DISC SERIES	
.000 ± 0.10	.00 ± 0.5'	PRAT NO. DISC10THGET	
DESIGN kathy		2012/04/12	
DRAWING		FILE NO. DISC10THGET-A	
CHECK		SIZE UNIT SCALE SHEET REV.	
APPRO.		A4 mm 2 : 1 10F-1 A	

RE 东莞市睿康实业有限公司
Dongguan Kingtek Industrial Co., Ltd.