UNISONIC TECHNOLOGIES CO., LTD

2SC4672

NPN SILICON TRANSISTOR


LOW FREQUENCY TRANSISTOR (50V,2A)

DESCRIPTION

The UTC 2SC4672 is a low frequency transistor. Excellent DC current gain characteristics.

FEATURES


*Low Saturation Voltage, Typically $V_{CE(SAT)}$ =0.1V at I_C / I_B =1A / 50mA *Excellent DC Current Gain Characteristics




ORDERING INFORMATION

Order Number	Package	Pin Assignment			De alsie e	
		1	2	3	Packing	
2SC4672G-x-AB3-R	SOT-89	В	С	Е	Tape Reel	

Note: Pin Assignment: B: Base C: Collector E: Emitter



MARKING



www.unisonic.com.tw 1 of 2

■ ABSOLUATE MAXIUM RATINGS (T_A= 25°C, unless otherwise specified)

PARAMETER	SYMBOL	RATINGS	UNIT
Collector to Base Voltage	V_{CBO}	60	V
Collector to Emitter Voltage	V_{CEO}	50	V
Emitter to Base Voltage	V_{EBO}	6	V
Collector Current	lc	2	А
Collector Current (Pulse) (Note 1)	I _{CP}	5	А
Collector Dissipation	Pc	500	mW
Junction Temperature	TJ	+150	°C
Storage Temperature	T_{STG}	-40 ~ +150	°C

Note: 1.Single pulse, P_W=10ms

■ ELECTRICAL CHARACTERISTICS (T_A= 25°C, unless otherwise specified)

PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNIT
Collector-Base Breakdown Voltage	BV_CBO	I _C =50μA	60			V
Collector-Emitter Breakdown Voltage	BV_CEO	I _C =1mA	50			V
Emitter-Base Breakdown Voltage	BV_{EBO}	I _E =50μA	6			V
Collector Cutoff Current	I_{CBO}	V _{CB} =60V			0.1	μΑ
Emitter Cutoff Current	I _{EBO}	V _{EB} =5V			0.1	μΑ
Collector-Emitter Saturation Voltage	$V_{CE(SAT)}$	I _C /I _B =1A/50mA (Note)		0.1	0.35	V
DC Current Transfer Ratio	h _{FE}	V _{CE} =2V, I _C =0.5A (Note)	120		400	
Transition Frequency	f⊤	V _{CE} =2V, I _E =-0.5A, f=100MHz		210		MHz
Output Capacitance	Сов	V _{CB} =10V, I _E =0A,f=1MHz		25		pF


Note: Measured using pulse current.


lacktriangle CLASSIFICATION OF h_{FE}


RANK	A	В
RANGE	120 ~ 240	200 ~ 400


^{2.} Absolute maximum ratings are those values beyond which the device could be permanently damaged. Absolute maximum ratings are stress ratings only and functional device operation is not implied.


■ TYPICAL CHARACTERISTICS











Ambient Temperature, T_a(°C)

UTC assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all UTC products described or contained herein. UTC products are not designed for use in life support appliances, devices or systems where malfunction of these products can be reasonably expected to result in personal injury. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice.

