

ITEM :

CRYSTAL RESONATOR

DSX211SH 26.000MHz

(TAIWAN) 1ZZHAE26000AB0L

(THAILAND) 1ZZNAE26000AB0L

If there is a change in this specifications, the specification number may be changed.

	RECEIPT
DATE	
RECEIVED	(signature) (name)



1. ELECTRICAL CHARACTERISTICS

(This test shall be performed under the conditions of temp.at 25 \pm 3°C, Relative Humidity 60% max.)

(1) NOMINAL FREQUENCY	26.000000 MHz
(2) OVERTONE ORDER	Fundamental
(3) LOAD CAPACITANCE(CL)	7.3 pF
(4) FREQUENCY TOLERANCE	±10 ppm max. (at +25 ± 3 °C)
(5) DRIVE LEVEL	10 ± 2 µW
(6) SERIES RESISTANCE	100 Ω max. (at Series)
(7) OPERATING TEMPERATURE RANGE	-40 ~ +85 °C
(8) FREQUENCY CHARACTERISTICS OVER TEMPERATURE	±15 ppm max. / -40 ~ +85 °C (ref. to +25°C)
(9) SHUNT CAPACITANCE	2.0 pF max.
(10) INSULATION RESISTANCE	500 M Ω min. / DC 100 ± 15V
(11) STORAGE TEMPERATURE RANGE	-40 ~ +85 °C
(12) FREQUENCY AGING	±15 ppm max. / 10 years
2. CONSTRUCTION (1) DIMENSIONS AND MARKING	Refer to 4.
3. OTHER SPECIFICATIONS (1) EMBOSS CARRIER TAPE & REEL	Refer to 5.
(2) PACKING	Refer to 6.
(3) REFLOW CONDITIONS (REFERENCE)	Refer to 7.
(4) LAND PATTERN (REFERENCE)	Refer to 8.
(5) RELIABILITY SPECIFICATION	Refer to 9.~11.
(6) OTHER HANDLING INSTRUCTIONS	Refer to 12.
TITLE	REMARK
DSX211SH TYPE QUARTZ CRYSTAL SPECIFICATIO	
DATE	SPEC. No. REV. PAGE
2017/12/14	1ZZNAE26000AB0L 1 / 12 1ZZHAE26000AB0L

DAISHINKU CORP.


1ZZHAE26000AB0L

4. DIMENSIONS AND MARKING

$\begin{array}{c} 2.05 \pm 0.1 \\ \hline \\ 0 \\ \hline \hline \\ 0 \\ \hline \\ 0 \\ \hline \hline \hline \hline$	$\langle T O P V I E W \rangle$ #4 #1 UNIT:mm TOLERANCE : ±0.1		
Figure-1			
	ted as follows by producing district 1ZZNAE26000AB0L ,Logo: D , Fr 1ZZHAE26000AB0L ,Logo: D , Fr		
Nominal Frequency (2) = Mark two digits from upp	* Made in THAILAND * Made in TAIWAN er decimal point	: Top Bar with : Under Bar wi	
 (ex. 26.000000 MHz> 26) Manufacturing lot No.(3) Year : The last digit of the year week : We gave the sequence of week numbers there are starting from 1st of Jan. Howev The week means are from Sunday to Sat (ex. 2017/12/14> 750) 	er,add '0' figure to the first week during t	the nine weeks	
TITLE DSX211SH TYPE QUARTZ CRYSTAL SPECIFICATION	REMARK		
DATE	SPEC. No.	REV.	PAGE
2017/12/14	1ZZNAE26000AB0L 1ZZHAE26000AB0L		2 / 12
DAISHINKU	CORP.	DM-Z000	02:Style-010 Ver.1

5. EMBOSS CARRIER TAPE & REEL

(1) Dimensions of embossed carrier tape



symbol	Ao	Во	Ko	Po	P1	P2
spec.	1.9±0.1	2.3±0.1	0.65±0.1	4.0±0.1	4.0±0.1	2.0±0.05
symbol	E	F	Do	D1	W	Т
spec.	1.75±0.1	3.5±0.05	Φ1.55±0.05	Φ1.1±0.05	8.0±0.2	0.25±0.02

(2) Dimensions of tape reel




Figure-3

TITLE DSX211SH TYPE QUARTZ CRYSTAL SPECIFICATION	REMARK		
DATE 2017/12/14	SPEC. No. 1ZZNAE26000AB0L 1ZZHAE26000AB0L	REV.	PAGE 3 / 12

				(UNIT:mm)
Proc	ducts			DSX211SH
Iten	ı		Mark	Dimensions Angle
	Dia	ameter	A	180 Φ +0 -3
Flange	Inside	of Frange	W1	9.0 ± 0.3
	Outside	e of Frange	W2	11.4 ± 1
	Inside	Diameter	В	Ф60 +1.0-0
			F1	3.0 +0.5 -0
	Center	Width	F2	4.0 +0.5 -0
Hub	Core Slit		F3	5.0 +0.5 -0
nub		Angle	q	120°
	Spindle	e Diameter	С	13 Φ ± 0.5
	Key Ditch	Width	E	2 ± 0.5
	Ļ	L	Į	Ļ

(3) Storage condition Temperature : +40 °C max. Relative Humidity : 80% max.

(It is a guaranteed term because it obtains an excellent soldering: 6 months)

(4) Standard packing quantity

3,000 pcs/reel

(5) Material of the tape

Таре	Material
Carrier tape	PS Conductive
Cover tape	Polyester

TITLE DSX211SH TYPE QUARTZ CRYSTAL SPECIFICATION	REMARK		
DATE 2017/12/14	SPEC. No. 1ZZNAE26000AB0L 1ZZHAE26000AB0L	REV.	PAGE 4 / 12

(6) Label contents

Type Our specification No. Your Part No. Lot No. Nominal Frequency Quantity Our Company Name

Stick a label on the each reel.

(7) Taping dimension

	Cover-tape	The length of cover-tape in the	leader is more than 400mm		
Leader		including empty embossed are			
	Carrier-tape		ed, must remain more than twent	y pieces	
			hould be sealed by cover-tape.		
	Cover-tape		xed temporary by paper tape and	d roll around	
Terminal		the core of reel one round.			
	Carrier-tape	The empty embossed area wh	ch are sealed by cover-tape mus	t remain	
		more than 40mm.			
(9) Release stre It has to be Pulling d Speed Otherwis 165 ~ 180 °	tape and cover-tape ength of cover tape etween 0.1 ~ 0.7N lirection 165 ~ 300mr se unless specified	Figure-4 Figure-4	Leader		
TITLE		RE	MARK		
DSX211SH TYPE Q	UARTZ CRYSTAL				
DATE			SPEC. No.	REV.	PAGE
	2017/12/14	17	ZNAE26000AB0L		5 / 12
			ZHAE26000AB0L		


6. PACKING

(1) STORAGE METHOD

<image/>			
(2) BOX SIZE			
From lot size packingsize shall be changed. In the upper and lower part and the opening in box it sha aircushion sheets.	all be protected products using		
TITLE DSX211SH TYPE QUARTZ CRYSTAL SPECIFICATION	REMARK		
DATE	SPEC. No.	REV.	PAGE
2017/12/14	1ZZNAE26000AB0L 1ZZHAE26000AB0L		6 / 12

7. REFLOW CONDITIONS (REFERENCE)

During the solder reflow process, please complete within following temperature, period. Reflow soldering shall be allowed only 2 times.



9. MECHANICAL ENDURANCE			
 (1) SHOCK (NATURAL DROP) After the following test, parts shall conform specification 11.E Drop on 3 times from height of 50cm onto min. 30mm thickn 			
 (2) VIBRATION After the following test,parts shall conform specification 11.E and no abnormal appearance shall be observed. Frequency of Vibration : 10 ~ 55 Hz Amplitude(p-p) : Sine waves of 0.8m Vibration axis : X.Y.Z Vibration period : 2h for each axis 			
 (3) SEAL Less than 1.0×10⁻⁸ Pa m³/s by Helium leak detector. Also, no serial bubble is observed by Fluorocarbon tests. (4) SOLDERABILITY 			
After the following test, more than 95% of terminal shall be 3 ± 0.5 s dip in +245 \pm 5 °C solder. (Solder composition : Sn-3Ag-0.5Cu) (Use rosin type flux for			
 (5) RESISTANCE TO SOLDERING HEAT (REFLOW) 48h past at room temperature from following test, parts shall perform the attached Reflow conditions to reference. 	conform specification 11.B.		
 (6) RESISTANCE TO SOLDERING HEAT (HAND SOLDERIN 48h past at room temperature from following test,parts shall +350 °C max , 3s max. Each terminal once. 			
 (7) SUBSTRATE BENDING After the following test,parts shall conform specification 11.E and no abnormality shall be observed in external appearance tightnen and others shall be based on ET-7403 of EIAJ. Mount the specimen on substrate. Apply the following pressure Direction : see right figure Speed : about 0.5 mm/s Hours : 5 ± 1 s Amount of substrate : 3 mm max. 		20	св
	45+/-2	45+/ - 2 (un	2 it:mm)
TIT 2 DSX211SH TYPE QUARTZ CRYSTAL SPECIFICATION	REMARK		
DATE	SPEC. No.	REV.	PAGE
2017/12/14	1ZZNAE26000AB0L 1ZZHAE26000AB0L		8 / 12

Mount the specimen on substrate. Apply the following pressure Weight : 10 N Hours : 10 ± 1 s Direction : see right figure	R0.5 specimen
(9) BODY STRENGTH After the following test, parts shall conform specification and no abnormality shall be observed in external appea tightness and others shall be based on ET-7403 of EIA	arance and sealing
Mount the specimen on substrate. Apply the following pressure Weight : 5N Hours : 10 ± 1 s Direction : see right figure	R0.5 specimen
	<u> ≁</u>
TITLE DSX211SH TYPE QUARTZ CRYSTAL SPECIFICATION	REMARK

DAISHINKU CORP.

1ZZHAE26000AB0L

10. ENVIRONMENTAL ENDURANCE

(1) LOW TEMPERATURE

2h past at room temperature after following test, parts shall conform specification 11.B. 240h , $\,$ -40 \pm 3 $^{\circ}\text{C}.$

(2) HUMIDITY


2h past at room temperature after following test, parts shall conform specification 11.B. 240h , $+60 \pm 2$ °C , relative humidity 90 ~ 95%.

(3) HIGH TEMPERATURE

2h past at room temperature after following test, parts shall conform specification 11.B. 240h , $+85 \pm 2$ °C.

(4) TEMPERATURE CYCLE

2h past at room temperature after 25 cycles of followingtest, parts shall conform specification 11.B.



11. SPECIFICATION

Frequency Variation and Equivalent Resistance shall be within Table below after the reliability test.

Spec.	Frequency Variation	Equivalent Resistance		
Α	±2ppm	± 15 % or 2.0 Ω max. (Use larger specification)		
B ±5ppm		±20 % or 3.0 Ω max. (Use larger specification)		

TITLE DSX211SH TYPE QUARTZ CRYSTAL SPECIFICATION	REMARK		
DATE 2017/12/14	SPEC. No. 1ZZNAE26000AB0L 1ZZHAE26000AB0L	REV.	PAGE 10 / 12

12. DSX211SH TYPE QUARTZ CRYSTAL HANDLING INSTRUCTIONS

(1) SOLDERING

Please perform the attached Reflow conditions to reference within 2 times.

(2) MOUNT

Crystal products are designed to be compatible with automatic mounting. Be sure to have a mounting test in advance by using the actual mounting machine and check that the characteristics of the products are not damaged by the automatic mounting. In the process where the boad is warped, such as board separation process, be careful that the warping does not influence the characteristics and soldering of crystal products. Since mounting by Ultrasonic welding and processing have a possibility of an excessive vibration spreading inside a crystal resonator and becoming the cause of characteristic deterioration and not oscillating, it does not recommend.

(3) WASHING

About use of the washing liquid of a basin system, an alcoholic system, and a chlorofluorocarbon-replacing material system, it is checking that it is satisfactory. However please consult in advance about other washing liquid. Although the check about ultrasonic washing is performed, since it is an examination with a simple substance, the check for the second time by the use state is recommended.

(4) THE CAUTIONS ON USE

The piece of crystal it is processed very smaller than the conventional thing inside DSX211SH series crystal unit may be damaged, if excessive excitation electric power is applied. Please use it below with the value specified on a catalog and specifications. Please refrain from forming patterns between crystal land pattern's since there is a possibility to cause crack in base.

(5) HANDLING OF A PRODUCT

DSX211SH series has sufficient intensity to fall and vibration. However when too much shock is added according to a certain cause, the use after a characteristic check is recommended.

(6) STORAGE

Since the soldering nature of a terminal may be degraded, please avoid storage in high temperature and a humid place. Please keep it in the place which direct rays do not hit and dew condensation does not generate.

TITLE DSX211SH TYPE QUARTZ CRYSTAL SPECIFICATION	REMARK		
DATE 2017/12/14	SPEC. No. 1ZZNAE26000AB0L 1ZZHAE26000AB0L	REV.	PAGE 11 / 12

Rev.No	Date	Reason	Contents	Approved	Checked	Drawn
-	2017/12/14	-	The first edition.	T.Hanaki		M.Nagaishi
_						

2017-1051 REVISION RECORD