

## Surface Mount Schottky Barrier Rectifier

Reverse Voltage - 40V Forward Current - 3.0A **FEATURES** 

- Metal silicon junction, majority carrier conduction
- For surface mounted applications
- Low power loss, high efficiency
- High forward surge current capability
- For use in low voltage, high frequency inverters,

free wheeling, and polarity protection applications

## MECHANICAL DATA

- Case: SMAF
- Terminals: Solderable per MIL-STD-750, Method 2026
- Approx. Weight:27mg 0.00086oz

### Absolute Maximum Ratings and Electrical characteristics

## PINNING

PIN	DESCRIPTION					
1	Cathode					
2	Anode					



Ratings at 25 °C ambient temperature unless otherwise specified. Single phase, half wave, 60Hz resistive or inductive load, for capacitive load, derate by 20 %

Parameter	Symbols	\$\$34FL	Units
Maximum Repetitive Peak Reverse Voltage	Vrrm	40	v
Maximum RMS voltage	V <sub>RMS</sub>	28	V
Maximum DC Blocking Voltage	V <sub>DC</sub>	40	V
Maximum Average Forward Rectified Current	I <sub>F(AV)</sub>	3.0	А
Peak Forward Surge Current,8.3ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I <sub>FSM</sub>	80	А
Max Instantaneous Forward Voltage at 3 A	VF	0.45	V
Maximum DC Reverse Current T <sub>a</sub> = 25°C at Rated DC Reverse Voltage T <sub>a</sub> =100°C	I <sub>R</sub>	0.3 5	mA
Typical Junction Capacitance 1)	Cj	450	pF
Typical Thermal Resistance <sup>2)</sup>	Reja	40	°C/W
Operating Junction Temperature Range		-55 ~ +125	°C
Storage Temperature Range	T <sub>stg</sub>	-55 ~ +150	°C

1) Measured at 1MHz and applied reverse voltage of 4 V D.C.

2) P.C.B. mounted with 0.2 X 0.2" (5 X 5 mm) copper pad areas.


SHIKE MAKE CONSCIOUS PRODUCT

CONSCIOUS PRODUCTS BEGIN WITH CONSCIOUS PEOPLE







# SS34FL




### Fig.1 Forward Current Derating Curve









SHIKE MAKE CONSCIOUS PRODUCT CONSCIOUS PRODUCTS BEGIN WITH CONSCIOUS PEOPLE

www.shike.tw

#### Fig.2 Typical Reverse Characteristics






Fig.4 Typical Junction Capacitance





Peak Forward Surage Current (A)








## PACKAGE OUTLINE

Plastic surface mounted package; 2 leads

SMAF








Top View



UNIT		А	С	D	E	e	g	HE	Z
mm –	max	1.1	0.20	3.7	2.7	1.6	1.2	4.9	
	min	0.9	0.12	3.3	2.4	1.3	0.8	4.4	7°
mil -	max	43	7.9	146	106	63	47	193	<u>(</u>
	min	35	4.7	130	94	51	31	173	

## The recommended mounting pad size



SHIKE MAKE CONSCIOUS PRODUCT CONSCIOUS PRODUCTS BEGIN WITH CONSCIOUS PEOPLE

