



SPECIFICATIONS
 Current rating: 2A AC/DC
 Voltage rating: 250V AC/DC
 Contact resistance: 20m Ω max.
 Withstand voltage: 800V AC/min
 Insulation resistance: 1000M Ω/min.
 Temperature range: -25°C~+85°C
 Applicable PC board thickness: 0.031"~0.063"(0.8~1.6)

Material:
 Post: Brass, Tin plated
 Base: PA9T, UL94V-0

Poles	Part No.	Dimension mm		
		A	B	C
2	2001SMTM-2P	8.0	4.7	2.0
3	2001SMTM-3P	10.0	6.7	4.0
4	2001SMTM-4P	12.0	8.7	6.0
5	2001SMTM-5P	14.0	10.7	8.0
6	2001SMTM-6P	16.0	12.7	10.0
7	2001SMTM-7P	18.0	14.7	12.0
8	2001SMTM-8P	20.0	16.7	14.0
9	2001SMTM-9P	22.0	18.7	16.0
10	2001SMTM-10P	24.0	20.7	18.0
11	2001SMTM-11P	26.0	22.7	20.0
12	2001SMTM-12P	28.0	24.7	22.0
13	2001SMTM-13P	30.0	26.7	24.0
14	2001SMTM-14P	32.0	28.7	26.0
15	2001SMTM-15P	34.0	30.7	28.0

APPROVED:	DATE:	TITLE: 2001SMTM-XP (贴片)			
CHECKED:	DATE:	CLIENT P/N /			
DRAWN:	DATE:	UNIT	mm	SCALE	free
LYP	2008-05-28	FILE NO.	Clmktw-2001-0014	REV.	A

深圳市矽科盟实业有限公司
 Ckmtw CHANKLEMENT INDUSTRYCO., LTD