





General Description

FIR7N65FG , the silicon N-channel Enhanced VDMOSFETs, is obtained by the self-aligned planar Technology which reduce the conduction loss, improve switching performance and enhance the avalanche energy. The transistor can be used in various power switching circuit for system miniaturization and higher efficiency. The package form is TO-220F, which accords with the RoHS standard.



Schematic diagram



Features

- | Fast Switching
- | Low ON Resistance
- | Low Gate Charge
- | Low Reverse transfer capacitances
- | 100% Single Pulse avalanche energy Test

Marking Diagram



Y = Year
 A = Assembly Location
 WW = Work Week
 VT = Version & Thickness
 FIR7N65F = Specific Device Code

Absolute Maximum Ratings (Ta = 25°C unless otherwise noted; reference only)

Characteristics		Symbol	Ratings	Unit
Drain-Source Voltage		V _{DS}	650	V
Gate-Source Voltage		V _{GS}	±30	V
Drain Current	T _C =25°C	I _D	7.0	A
	T _C =100°C		4.4	
Drain Current Pulsed		I _{DM}	28	A
Power Dissipation(T _C =25°C) -Derate above 25°C		P _D	35	W
			0.28	W/°C
Single Pulsed Avalanche Energy(Note 1)		E _{AS}	350	mJ
Operation Junction Temperature Range		T _J	-55~+150	°C
Storage Temperature Range		T _{stg}	-55~+150	°C



Thermal Characteristics

Characteristics	Symbol	Ratings	Unit
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	3.57	°C/W
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	120	°C/W

Electrical Characteristics ($T_a = 25^\circ C$ unless otherwise noted; reference only)

Characteristics	Symbol	Test conditions	Min.	Typ.	Max.	Unit
Drain -Source Breakdown Voltage	B_{VDSS}	25 °C, $V_{GS}=0V$, $I_D=250\mu A$	650	--	--	V
		125 °C, $V_{GS}=0V$, $I_D=250\mu A$	650	--	--	V
Drain-Source Leakage Current	I_{DSS}	25 °C, $V_{DS}=650V$, $V_{GS}=0V$	--	--	1	uA
		125 °C, $V_{DS}=520V$, $V_{GS}=0V$	--	--	10	uA
		150 °C, $V_{DS}=520V$, $V_{GS}=0V$	--	--	100	uA
Gate-Source Leakage Current	I_{GSS}	$V_{GS}=\pm 30V$, $V_{DS}=0V$	--	--	± 100	nA
Gate Threshold Voltage	$V_{GS(th)}$	$V_{GS}=V_{DS}$, $I_D=250\mu A$	2.0	--	4.0	V
Static Drain- Source On State Resistance	$R_{DS(on)}$	$V_{GS}=10V$, $I_D=2A$	--	1.25	1.5	Ω
Input Capacitance	C_{iss}	$V_{DS}=25V$, $V_{GS}=0V$, $f=1.0MHz$		1130		pF
Output Capacitance	C_{oss}		--	93	--	
Reverse Transfer Capacitance	C_{rss}		--	5.5	--	
Turn-on Delay Time	$t_{d(on)}$	$V_{DD}=325V$, $I_D=4.0A$, $R_G=10\Omega$	--	19	--	ns
Turn-on Rise Time	t_r		--	21	--	
Turn-off Delay Time	$t_{d(off)}$		--	42	--	
Turn-off Fall Time	t_f		--	19	--	
Total Gate Charge	Q_g	$V_{DS}=520V$, $I_D=4.0A$, $V_{GS}=10V$	--	24	--	nC
Gate-Source Charge	Q_{gs}		--	5.1	--	
Gate-Drain Charge	Q_{gd}		--	9.5	--	

Source-Drain Diode Ratings And Characteristics

Characteristics	Symbol	Test conditions	Min.	Typ.	Max.	Unit
Continuous Source Current	I_S	Integral Reverse P-N Junction Diode in the MOSFET	--	--	7.0	A
Pulsed Source Current	I_{SM}		--	--	28	
Diode Forward Voltage	V_{SD}	$I_S=4.0A$, $V_{GS}=0V$	--	--	1.4	V
Reverse Recovery Time	T_{rr}	$I_S=4.0A$, $V_{GS}=0V$, $dI_F/dt=100A/\mu s$	--	382	--	ns
Reverse Recovery Charge	Q_{rr}		--	1980	--	nC

Notes:

1. $L=10mH$, $I_{AS}= 8.4A$, $V_{DD}=100V$, $R_G=10\Omega$, starting $T_J=25^\circ C$;
2. Pulse Test: Pulse width $\leq 300\mu s$, Duty cycle $\leq 2\%$;
3. Essentially independent of operating temperature.

Characteristics Curve:




Figure 1 Maximum Forward Bias Safe Operating Area




Figure 2 Maximum Power Dissipation vs Case Temperature




Figure 3 Maximum Continuous Drain Current vs Case Temperature




Figure 4 Typical Output Characteristics




Figure 5 Maximum Effective Thermal Impedance Junction to Case




Figure 6 Typical Transfer Characteristics




Figure 7 Typical Body Diode Transfer Characteristics




Figure 8 Typical Drain to Source ON Resistance vs Drain Current




Figure 9 Typical Drian to Source on Resistance vs Junction Temperature




Figure 10 Typical Threshold Voltage vs Junction Temperature




Figure 11 Typical Breakdown Voltage vs Junction Temperature




Figure 12 Typical Capacitance vs Drain to Source Voltage




Figure 13 Typical Gate Charge vs Gate to Source Voltage

Test Circuit and Waveform




Figure 17. Gate Charge Test Circuit




Figure 18. Gate Charge Waveform




Figure 19. Resistive Switching Test Circuit




Figure 20. Resistive Switching Waveforms




Figure 21. Diode Reverse Recovery Test Circuit




Figure 22. Diode Reverse Recovery Waveform




Figure 23. Unclamped Inductive Switching Test Circuit







Figure 24. Unclamped Inductive Switching Waveforms



Package Dimensions

TO-220F



Units: mm
COMMON DIMENSIONS
(UNITS OF MEASURE=MILLIMETER)

SYMBOL	MIN	NOM	MAX
A	4.50	4.70	4.90
A1	2.34	2.54	2.74
A2		0.70 REF	
A3	2.56	2.76	2.96
b	0.70	0.80	0.90
b1	1.17	1.2	1.25
b2	1.17	1.2	1.25
c	0.45	0.50	0.60
D	15.67	15.87	16.07
D1	15.55	15.75	15.95
D2	10.0	10.2	10.4
E	9.96	10.16	10.36
e		2.54BSC	
H1	6.48	6.68	6.88
L	12.68	12.98	13.28
L1	-	-	3.50
L2		6.50REF	
ΦP	3.08	3.18	3.28
Q	3.20	3.30	3.40
θ 1	1°	3°	5°
A4	0.53	0.56	0.59



Declaration

- FIRST reserves the right to change the specifications, the same specifications of products due to different packaging line mold, the size of the appearance will be slightly different, shipped in kind, without notice! Customers should obtain the latest version information before ordering, and verify whether the relevant information is complete and up-to-date.
- Any semiconductor product under certain conditions has the possibility of failure or failure, The buyer has the responsibility to comply with safety standards and take safety measures when using FIRST products for system design and manufacturing, To avoid potential failure risks, which may cause personal injury or property damage!
- Product promotion endless, our company will wholeheartedly provide customers with better products!

ATTACHMENT

Revision History

Date	REV	Description	Page
2018.01.01	1.0	Initial release	