


# Chip tantalum capacitors

TC Series P Case Datasheet


#### ●Features

- 1) Small package, large capacitance chip tantalum capacitor.
- 2) Low impedance capacitors.
- 3) Screening by thermal shock.

#### Dimensions



#### ●Part No. Explanation



1 Series name

TC

2 Case style

P: 2012-12 (0805) size

(3) Rated voltage

Rated voltage (V)	4	6.3	10	16	20	25
CODE	0G	0J	1A	1C	1D	1E

4 Nominal capacitance

Nominal capacitance in pF in 3 digits: 2 significant figures followed by the figure representing the number of 0's.

(5) Capacitance tolerance

M: ±20%

6 Taping

8 : Reel width : 8mm

R : Positive electrode on the side opposite to sprocket hole

TC Series P Case Datasheet

#### Rated table

Capacitance		Rated voltag	ge (V.DC)		
. (μF)	4	6.3	10	16	25
1.0 (105)			Р	Р	Р
1.5 (155)			Р		
2.2 (225)		Р	Р		
3.3 (335)			Р		
4.7 (475)		Р	Р		
10 (106)	Р	Р	Р		
15 (156)		Р			
22 (226)	Р	Р			

Remark) Case size codes (P) in the above show products line-up.

### Marking

The indications listed below should be given on the surface of a capacitor.

(1) Polarity : The polarity should be shown by □ bar. (on the anode side)

(2) Rated DC voltage: A voltage code is shown as below table.

(3) Capacitance : A capacitance code is shown as below table.

Voltage Code	Rated DC Voltage (V)
g	4
j	6.3
А	10
С	16
D	20
Е	25

Capacitance Code	Nominal Capacitance (μF)
А	1.0
Е	1.5
J	2.2
N	3.3
S	4.7
а	10
е	15
j	22

Visual typical example

voltage code and capacitance code are variable with parts number.

[P case]

EX.)  $\frac{j}{(1)}$   $\frac{J}{(2)}$ 

(1) voltage code (2) capacitance code



TC Series P Case

## ● Characteristics

Iter	m					Р	erfo	orm	ance	Te	st condition	ons (based on J	IS C 5101–1 an	d JIS C 5101–3)
Operating Temp		-55	°C	to +	12	5°C				Volta	ge reduct	ion when tempe	rature exceeds	+85°C
Maximum operatemperature wit derating	ating h no voltage	+85	°C											
Rated voltage (	V.DC)	4 (	5.3	10	10	3 20	) 2	25		at 85°C				
Category voltag	je (V.DC)	2.5	4	6.3	1	13	3 1	16		at 12	5°C			
Surge voltage (	V.DC)	5.0 8 13 20 26 32								at 85	°C			
DC Leakage cu	rrent	Sha " Sta					the	va	lue on	As pe	er 4.5.1 Jl	C 5101-1 S C 5101-3 d voltage for 1m	iin	
Capacitance tol	erance	Sha ±20		e sa	itis	fied	allo	owa	ince range.	As pe Meas Meas	er 4.5.2 JI		PHz s +1.5V.DC uivalent series c	ircuit
Tangent of loss (Df, tan $\delta$ )	angle	Sha " St					the	e va	lue on	As per 4.8 JIS C 5101-1 As per 4.5.3 JIS C 5101-3 Measuring frequency : 120±12Hz Measuring voltage : 0.5Vrms +1.5V.DC Measuring circuit : DC Equivalent series circuit				
Impedance		Shall be satisfied the value on  " Standard list "					e va	lue on	As per 4.10 JIS C 5101-1 As per 4.5.4 JIS C 5101-3 Measuring frequency: 100±10kHz Measuring voltage: 0.5Vrms or less Measuring circuit: DC Equivalent series circuit					
Resistance to Soldering heat	Appearance	There should be no significant abnormality. The indications should be clear.								As per 4.14 JIS C 5101-1 As per 4.6 JIS C 5101-3 Dip in the solder bath				
	L.C.	Les	s th	nan i	ini	ial li	mit				n the sold er temp	er bath : 260±10	)°C	
TC				TCP0J226M8R: Within ±20% of initial value TCP1A106M8R: Within ±20% of initial value Others: Within ±10% of initial value						Duration : 5±0.5s Repetition : 1 After the specimens, leave it at room temperature for over 24h and then measure the sample.				
	Df (tan δ)	Les	s th	an 1	150	)% c	of in	nitia	l limit					
Temperature cycle	Appearance								nificant abnormality. De clear.	As per 4.16 JIS C 5101-1 As per 4.10 JIS C 5101-3				
	L.C.	TCF Oth			M8				han 150% of initial limit than initial limit		etition : 5 o	cycles s 1 to 4) without Temp.	discontinuation Time	
	⊿C / C	15 t	1 to $10\mu F$ : Within $\pm 10\%$ of initial value 15 to $33\mu F$ : Within $\pm 20\%$ of initial value TCP1A106M8R : Within $\pm 20\%$ of initial value				±20% of initial value		1 2 3	-55±3°C Room temp. 125±2°C	30±3min. 3min.or less 30±3min.			
	Df (tan δ)	Less than 150% of initial limit						nitia	l limit	4 Room temp. 3min.or less  After the specimens, leave it at room temperature for over 24h and then measure the sample.				ture for
Moisture resistance	Appearance								nificant abnormality.	As per 4.22 JIS C 5101-1 As per 4.12 JIS C 5101-3				
	L.C.	TCF Oth			M				han 150% of initial limit than initial limit	cond	ition that	ne sample under the temperature 0 to 95% RH,res	and humidity ar	e
	⊿C/C	With	nin :	±20°	%	of in	itial	l va	lue	leave	it at roor	n		
71/2 20 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1				temperature for over 24h and then measure the sample.										



**TC Series P Case** Datasheet

Iten	n	Performance	Test conditions (based on JIS C 5101–1 and JIS C 5101–3)					
Temperature	Temp.	-55°C	As per 4.29 JIS C 5101-1 As per 4.13 JIS C 5101-3					
Stability	⊿c/c	Within 0/–15% of initial value	As per 4.15 315 C 5101-5					
	Df (tan δ)	Shall be satisfied the voltage on " Standard list "						
L	L.C.	-						
	Temp.	+85°C						
	⊿C/C	Within +15/0% of initial value						
	Df (tan δ)	Shall be satisfied the voltage on " Standard list "						
	L.C.	Less than 1000% of initial limit						
	Temp.	+125°C						
	⊿C/C	Within +20/0% of initial value						
	Df (tan δ)	Shall be satisfied the voltage on " Standard list "						
	L.C.	Less than 1250% of initial limit						
Surge voltage	Appearance	There should be no significant abnormality.	As per 4.26JIS C 5101-1					
	L.C.	Shall be satisfied the voltage on " Standard list "	As per 4.14JIS C 5101-3 Apply the specified surge voltage via the serial resistance of					
	⊿C/C	TCP0J226M8R: Within ±20% of initial value Others: Within ±10% of initial value	1kΩ every 5±0.5 min.					
	Df (tan δ)	Less than 150% of initial limit						
Loading at	Appearance	There should be no significant abnormality.	As per 4.23 JIS C 5101-1					
High temperature L.C	L.C.	TCP0J226M8R : Less than 150% of initial limit Others : Less than initial limit	As per 4.15 JIS C 5101-3 After applying the rated voltage for 1000+36/0 h without discontinuation via the serial resistance of $3\Omega$ or less at a temperature of $85\pm2^{\circ}\text{C}$ , leave the sample at room temperature / humidity for over 24h and measure the value.					
	⊿C/C	TCP0J226M8R : Within ±20% of initial value Others : Within ±10% of initial value						
	Df (tan δ)	Less than 150% of initial limit						
Terminal strength	Capacitance	The measured value should be stable.	As per 4.35 JIS C 5101-1					
Si Ongui	Appearance	There should be no significant abnormality.	As per 4.9 JIS C 5101-3 A force is applied to the terminal until it bends to 1mm and by a prescribed tool maintain the condition for 5s. (See the figure below)  (Unit: mm)  F (Apply force)  thickness=1.6mm					
Adhesiveness		The terminal should not come off.	As per 4.34 JIS C 5101-1 As per 4.8 JIS C 5101-3 Apply force of 5N in the two directions shown in the figure below for 10±1s after mounting the terminal on a circuit board.					


Iten	n .	Performance	Test conditions (JIS C 5101-1 and JIS C 5101-3)			
Dimensions		Refer to "External dimensions"	Measure using a caliper of JIS B 7507 Class 2 or higher grade.			
Resistance to solvents		The indication should be clear	As per 4.32 JIS C 5101-1 As per 4.18 JIS C 5101-3 Dip in the isopropyl alcohol for 30±5s, at room temperature.			
Solderability		3/4 or more surface area of the solder coated terminal dipped in the soldering bath should be covered with the new solder.	As per 4.15.2 JIS C 5101-1 As per 4.7 JIS C 5101-3 Dip speed=25±2.5mm / s Pre-treatment(accelerated aging): Leave the sample on the boiling distilled water for 1 h. Solder temp.: 245±5°C Duration : 3±0.5s Solder : M705 Flux : Rosin 25% IPA 75%			
Vibration Capacitance Appearance		Measure value should not fluctuate during the measurement.	As per 4.17 JIS C 5101-1 Frequency : 10 to 55 to 10Hz/min. Amplitude : 1.5mm			
		There should be no significant abnormality.	Time: 2h each in X and Y directions  Mounting: The terminal is soldered on a print circuit board.			

# ●Standard products list


Part No.	Rated voltage 85°C	Category voltage 125°C	Surge voltage 85°C	Cap. 120Hz	Tolerance	Leakage current 25°C	Df 120Hz (%)			Impedance 100kHz
	(V)	(V)	(V)	(μF)	(%)	1WV.60s (μΑ)	–55°C	25°C 85°C	125°C	(Ω)
TC P 0G 106 M8R	4	2.5	5	10	± 20	0.5	30	20	30	9.3
TC P 0G 226 M8R	4	2.5	5	22	± 20	0.9	30	20	30	7.7
TC P 0J 225 M8R	6.3	4	8	2.2	± 20	0.5	30	20	30	17.5
TC P 0J 475 M8R	6.3	4	8	4.7	± 20	0.5	30	20	30	11.8
TC P 0J 106 M8R	6.3	4	8	10	± 20	0.6	30	20	30	8.3
TC P 0J 156 M8R	6.3	4	8	15	± 20	0.9	30	20	30	7.7
TC P 0J 226 M8R	6.3	4	8	22	± 20	1.4	38	25	38	5.0
TC P 1A 105 M8R	10	6.3	13	1.0	± 20	0.5	15	10	15	17.5
TC P 1A 155 M8R	10	6.3	13	1.5	± 20	0.5	30	20	30	16.1
TC P 1A 225 M8R	10	6.3	13	2.2	± 20	0.5	30	20	30	14.4
TC P 1A 335 M8R	10	6.3	13	3.3	± 20	0.5	30	20	30	11.8
TC P 1A 475 M8R	10	6.3	13	4.7	± 20	0.5	30	20	30	9.3
TC P 1A 106 M8R	10	6.3	13	10	± 20	1.0	30	20	30	7.7
TC P 1C 105 M8R	16	10	20	1.0	± 20	0.5	15	10	15	16.1
TC P 1E 105 M8R	25	16	32	1.0	± 20	0.6	30	20	30	9.3

TC Series P Case Datasheet

## Packaging specifications



#### ●Reel dimensions



# **Notice**

#### **Precaution on using ROHM Products**

1. Our Products are designed and manufactured for application in ordinary electronic equipments (such as AV equipment, OA equipment, telecommunication equipment, home electronic appliances, amusement equipment, etc.). If you intend to use our Products in devices requiring extremely high reliability (such as medical equipment (Note 1), transport equipment, traffic equipment, aircraft/spacecraft, nuclear power controllers, fuel controllers, car equipment including car accessories, safety devices, etc.) and whose malfunction or failure may cause loss of human life, bodily injury or serious damage to property ("Specific Applications"), please consult with the ROHM sales representative in advance. Unless otherwise agreed in writing by ROHM in advance, ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of any ROHM's Products for Specific Applications.

(Note1) Medical Equipment Classification of the Specific Applications

JAPAN	USA	USA EU				
CLASSⅢ	CLASSⅢ	CLASS II b	CL ACCIII			
CLASSIV	CLASSIII	CLASSⅢ	CLASSIII			

- 2. ROHM designs and manufactures its Products subject to strict quality control system. However, semiconductor products can fail or malfunction at a certain rate. Please be sure to implement, at your own responsibilities, adequate safety measures including but not limited to fail-safe design against the physical injury, damage to any property, which a failure or malfunction of our Products may cause. The following are examples of safety measures:
  - [a] Installation of protection circuits or other protective devices to improve system safety
  - [b] Installation of redundant circuits to reduce the impact of single or multiple circuit failure
- 3. Our Products are designed and manufactured for use under standard conditions and not under any special or extraordinary environments or conditions, as exemplified below. Accordingly, ROHM shall not be in any way responsible or liable for any damages, expenses or losses arising from the use of any ROHM's Products under any special or extraordinary environments or conditions. If you intend to use our Products under any special or extraordinary environments or conditions (as exemplified below), your independent verification and confirmation of product performance, reliability, etc, prior to use, must be necessary:
  - [a] Use of our Products in any types of liquid, including water, oils, chemicals, and organic solvents
  - [b] Use of our Products outdoors or in places where the Products are exposed to direct sunlight or dust
  - [c] Use of our Products in places where the Products are exposed to sea wind or corrosive gases, including Cl<sub>2</sub>, H<sub>2</sub>S, NH<sub>3</sub>, SO<sub>2</sub>, and NO<sub>2</sub>
  - [d] Use of our Products in places where the Products are exposed to static electricity or electromagnetic waves
  - [e] Use of our Products in proximity to heat-producing components, plastic cords, or other flammable items
  - [f] Sealing or coating our Products with resin or other coating materials
  - [g] Use of our Products without cleaning residue of flux (even if you use no-clean type fluxes, cleaning residue of flux is recommended); or Washing our Products by using water or water-soluble cleaning agents for cleaning residue after soldering
  - [h] Use of the Products in places subject to dew condensation
- 4. The Products are not subject to radiation-proof design.
- 5. Please verify and confirm characteristics of the final or mounted products in using the Products.
- 6. In particular, if a transient load (a large amount of load applied in a short period of time, such as pulse. is applied, confirmation of performance characteristics after on-board mounting is strongly recommended. Avoid applying power exceeding normal rated power; exceeding the power rating under steady-state loading condition may negatively affect product performance and reliability.
- 7. De-rate Power Dissipation (Pd) depending on Ambient temperature (Ta). When used in sealed area, confirm the actual ambient temperature.
- 8. Confirm that operation temperature is within the specified range described in the product specification.
- 9. ROHM shall not be in any way responsible or liable for failure induced under deviant condition from what is defined in this document.

#### Precaution for Mounting / Circuit board design

- 1. When a highly active halogenous (chlorine, bromine, etc.) flux is used, the residue of flux may negatively affect product performance and reliability.
- 2. In principle, the reflow soldering method must be used on a surface-mount products, the flow soldering method must be used on a through hole mount products. If the flow soldering method is preferred on a surface-mount products, please consult with the ROHM representative in advance.

For details, please refer to ROHM Mounting specification

#### **Precautions Regarding Application Examples and External Circuits**

- 1. If change is made to the constant of an external circuit, please allow a sufficient margin considering variations of the characteristics of the Products and external components, including transient characteristics, as well as static characteristics.
- 2. You agree that application notes, reference designs, and associated data and information contained in this document are presented only as guidance for Products use. Therefore, in case you use such information, you are solely responsible for it and you must exercise your own independent verification and judgment in the use of such information contained in this document. ROHM shall not be in any way responsible or liable for any damages, expenses or losses incurred by you or third parties arising from the use of such information.

#### **Precaution for Electrostatic**

This Product is electrostatic sensitive product, which may be damaged due to electrostatic discharge. Please take proper caution in your manufacturing process and storage so that voltage exceeding the Products maximum rating will not be applied to Products. Please take special care under dry condition (e.g. Grounding of human body / equipment / solder iron, isolation from charged objects, setting of lonizer, friction prevention and temperature / humidity control).

#### **Precaution for Storage / Transportation**

- 1. Product performance and soldered connections may deteriorate if the Products are stored in the places where:
  - [a] the Products are exposed to sea winds or corrosive gases, including Cl2, H2S, NH3, SO2, and NO2
  - [b] the temperature or humidity exceeds those recommended by ROHM
  - [c] the Products are exposed to direct sunshine or condensation
  - [d] the Products are exposed to high Electrostatic
- 2. Even under ROHM recommended storage condition, solderability of products out of recommended storage time period may be degraded. It is strongly recommended to confirm solderability before using Products of which storage time is exceeding the recommended storage time period.
- 3. Store / transport cartons in the correct direction, which is indicated on a carton with a symbol. Otherwise bent leads may occur due to excessive stress applied when dropping of a carton.
- 4. Use Products within the specified time after opening a humidity barrier bag. Baking is required before using Products of which storage time is exceeding the recommended storage time period.

#### **Precaution for Product Label**

QR code printed on ROHM Products label is for ROHM's internal use only.

#### **Precaution for Disposition**

When disposing Products please dispose them properly using an authorized industry waste company.

#### **Precaution for Foreign Exchange and Foreign Trade act**

Since concerned goods might be fallen under listed items of export control prescribed by Foreign exchange and Foreign trade act, please consult with ROHM in case of export.

#### **Precaution Regarding Intellectual Property Rights**

- 1. All information and data including but not limited to application example contained in this document is for reference only. ROHM does not warrant that foregoing information or data will not infringe any intellectual property rights or any other rights of any third party regarding such information or data.
- 2. ROHM shall not have any obligations where the claims, actions or demands arising from the combination of the Products with other articles such as components, circuits, systems or external equipment (including software).
- 3. No license, expressly or implied, is granted hereby under any intellectual property rights or other rights of ROHM or any third parties with respect to the Products or the information contained in this document. Provided, however, that ROHM will not assert its intellectual property rights or other rights against you or your customers to the extent necessary to manufacture or sell products containing the Products, subject to the terms and conditions herein.

#### **Other Precaution**

- 1. This document may not be reprinted or reproduced, in whole or in part, without prior written consent of ROHM.
- 2. The Products may not be disassembled, converted, modified, reproduced or otherwise changed without prior written consent of ROHM.
- In no event shall you use in any way whatsoever the Products and the related technical information contained in the Products or this document for any military purposes, including but not limited to, the development of mass-destruction weapons.
- 4. The proper names of companies or products described in this document are trademarks or registered trademarks of ROHM, its affiliated companies or third parties.

Notice-PGA-E Rev.001

#### **General Precaution**

- 1. Before you use our Products, you are requested to care fully read this document and fully understand its contents. ROHM shall not be in an y way responsible or liable for failure, malfunction or accident arising from the use of a ny ROHM's Products against warning, caution or note contained in this document.
- 2. All information contained in this docume nt is current as of the issuing date and subject to change without any prior notice. Before purchasing or using ROHM's Products, please confirm the latest information with a ROHM sale s representative.
- 3. The information contained in this doc ument is provided on an "as is" basis and ROHM does not warrant that all information contained in this document is accurate an d/or error-free. ROHM shall not be in an y way responsible or liable for any damages, expenses or losses incurred by you or third parties resulting from inaccuracy or errors of or concerning such information.

**Notice – WE** © 2015 ROHM Co., Ltd. All rights reserved. Rev.001



# TCP1A106M8R - Web Page

**Distribution Inventory** 

Part Number	TCP1A106M8R
Package	TCP
Unit Quantity	3000
Minimum Package Quantity	3000
Packing Type	Taping
Constitution Materials List	inquiry
RoHS	Yes