

n -BalanceTM Current Mode PWM Controller

FEATURES

- ♦ Less than 75mW Standby Power
- ◆ Programmable OLP Debounce Time
- ◆ Proprietary ☐ -BalanceTM Control to Boost Light Load Efficiency
- Proprietary "Zero OCP/OPP Recovery Gap" Control
- ◆ Proprietary "Audio Noise Free OCP Compensation"
- ◆ Dmax up to 80%
- ♦ Fixed 65KHz Switching Frequency
- ◆ Built-in Frequency Shuffling
- **♦** Built-in Soft Start Function
- Frequency Reduction and Burst Mode Control for Energy Saving
- ♦ Built-in Synchronous Slope Compensation
- **♦** Cycle-by-Cycle Current Limiting
- ♦ Built-in Leading Edge Blanking (LEB)
- **♦** Current Mode Control
- Pin Floating Protection
- ♦ Very Low Startup Current
- **♦** Audio Noise Free Operation
- ♦ VDD UVLO, OVP & Clamp

APPLICATIONS

Offline AC/DC Flyback Converter for

- ◆ AC/DC Adaptors
- **♦** Open-frame SMPS
- Laptop Charger

GENERAL DESCRIPTION


SF5533W is a high performance, high efficiency, highly integrated current mode PWM controller for offline flyback converter applications. The OLP debounce time can be programmed in SF5533W. In SF5533W, PWM switching frequency with shuffling is fixed 65KHz and is trimmed to tight range. When the output power demands decrease, the IC decreases switching frequency based on the proprietary n -BalanceTM control to boost power conversion efficiency at the light load. When output power falls below a given value, the IC enters into burst mode and can achieve less than 75mW no load power.

The IC can achieve "Zero OCP/OPP Recovery Gap" using SiFirst's proprietary control algorithm. SF5533W also has built in proprietary "Audio Noise Free OCP Compensation", which can achieve constant power limiting and can achieve audio noise operation at heavy loading when line input is around 90VAC.

SF5533W integrates functions and protections of Under Voltage Lockout (UVLO), VDD Over Voltage Protection (OVP), Cycle-by-cycle Current Limiting (OCP), Pins Floating Protection, Over Load Protection (OLP), Gate Clamping, RT Pin Short-to-GND Protection, VDD Clamping, Leading Edge Blanking (LEB), Soft Start, etc.


SF5533W is available in SOT23-6 package.

TYPICAL APPLICATION






Pin Configuration



Ordering Information

Part Number	Top Mark	Pacl	Tape & Reel	
SF5533WLGT	.33WYWW	SOT23-6	Green	Yes

Marking Information




Dot: Pin1 Mark

33W:Part number SF5533W YWW: Year&Week Code



Block Diagram



Pin Description

Pin Num	Pin Name	I/O	Description
1	GND	Р	Ground
2	FB	I	Voltage feedback pin. The loop regulation is achieved by connecting a photo-coupler to this pin. PWM duty cycle is determined by this pin voltage and the current sense signal at Pin 4.
3	СТ	I	Pin for program OLP debounce time. If this pin is floating, the OLP time is 55ms. If an external capacitor is connected between CT and GND, the OLPdebounce time can be programmable.
4	CS	I	Current sense input pin.
5	VDD	Р	IC power supply pin.
6	GATE	0	Totem-pole gate driver output to drive the external MOSFET.



Absolute Maximum Ratings (Note 1)

Parameter	Value	Unit	
VDD DC Supply Voltage		35	V
VDD DC Clamp Current		10	mA
GATE pin	20	V	
FB, CT, CS voltage range		-0.3 to 7	V
Paul and Thomas Paul (00700 0)	θја	250	000
Package Thermal Resistance (SOT23-6)	θјς	70	°C/W
Maximum Junction Temperature		150	°C
Operating Temperature Range	-40 to 85	°C	
Storage Temperature Range	-65 to 150	°C	
Lead Temperature (Soldering, 10sec.)	260	°C	
ESD Capability, HBM (Human Body Model	3	kV	
ESD Capability, MM (Machine Model)	250	V	

Recommended Operation Conditions (Note 2)

Parameter	Value	Unit
Supply Voltage, VDD	10 to 25	V
Operating Frequency	50 to 130	kHz
Operating Ambient Temperature	-40 to 85	°C

Note 1. Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

Note 2. The device is not guaranteed to function outside its operating conditions.



ELECTRICAL CHARACTERISTICS


(T_A = 25°C, RT=100K ohm, VDD=18V, if not otherwise noted)


Symbol	Parameter	Test Conditions	Min	Тур	Max	Unit
Supply Voltage	Section (VDD Pin)				_	
UVLO(ON)	VDD Under Voltage		14.5	15.5	16.5	V
C V LO(OIV)	Lockout Exit (Startup)		17.5	10.0	10.0	\ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \
UVLO(OFF)	VDD Under Voltage		8	9	10	V
` ,	Lockout Enter		<u> </u>			
I_Startup	VDD Start up Current	VDD =12.5V		5	20	uA
I_VDD_Op	Operation Current	V _{FB} =3V,CL=1nF		2.0	3.5	mA
VDD_OVP	VDD Over Voltage			27		V
	Protection trigger					
V _{DD} _Clamp	VDD Zener Clamp Voltage	$I(V_{DD}) = 10 \text{ mA}$		35.5		V
T_Softstart	Soft Start Time			4		mSec
Feedback Input	Section(FB Pin)					
V _{FB} _Open	FB Open Voltage		4.1	4.5	5	V
I _{FB} _Short	FB short circuit current	Short FB pin to GND		0.33		mA
Avcs	PWM Input Gain	ΔV _{FB} /ΔV _{cs}		1.6		V/V
	FB under voltage gate					
VFB_min_duty	clock is off.			1.0		V
\/ DI	Power Limiting ER			2.7		\/
V_{TH} PL	Threshold Voltage			3.7		V
T DI	Power limiting Debounce	Nata 0				0
T_{D} PL	Time	Note 3		55		mSec
Z _{FB} _IN	Input Impedance			14		Kohm
_	Input Section (CS Pin)	,	1		-1	1
	Internal current limiting	<u> </u>				l
Vth_OC_min	threshold	Zero duty cycle	0.70	0 0.75	0.80	V
	Internal current limiting					
Vth_OC_max	threshold			1.0		V
	SENSE Input Leading					
T_blanking	Edge Blanking Time			250		nSec
	Over Current Detection					
T _D _OC	and Control Delay	CL=1nF at GATE,		65		nSec
Oscillator Secti					1	1
	Normal Oscillation					
Fosc	Frequency		60	65	70	KHz
ΔF(shuffle)/Fosc	Frequency shuffling range	Note 4	-4		4	%
,	Frequency Temperature		<u>'</u>			
∆f_Temp	Stability	-20°C to 100 °C (Note 4)		5		%
	Frequency Voltage			†_		1
Δf _VDD	Stability	VDD = 12-25V,		5		%
Duty_max	Maximum Duty cycle		75	80	85	%
•	Burst Mode Base		+		55	
F_BM	Frequency			22		KHz
OI P Debounce	Program Section (CT Pin)	<u> </u>	<u>l</u>		1	1
I_CT	Output Current of CT Pin	<i>,</i> 	10	14	18	uA
	Comparator threshold for		10	14	10	
V _{TH} _CT	OLP debounce time			3	1	V
Cata Drive Out						
Gate Drive Outp		15 00 m/A (-1-1-)	1	1	T 4	1 1/
VOL	Output Low Level	lo = 20 mA (sink)	 		1	V
VOH	Output High Level	lo = 20 mA (source)	7.5			V
VG_Clamp	Output Clamp Voltage	VDD=24V		16		V
<u> </u>	Level					
T_r	Output Rising Time	CL = 1nF		150		nSec
T f	Output Falling Time	CL = 1nF		60		nSec


Note 3. The OLP debounce time is proportional to the period of switching cycle. Note 4. Guaranteed by design.





CHARACTERIZATION PLOTS

















OPERATION DESCRIPTION

SF5533W is a high performance, highly efficiency current mode PWM controller for offline flyback converter applications. The built-in proprietary "Efficiency Equalization" with high level protection features improves the SMPS reliability and performance without increasing the system cost.

♦ UVLO and Startup Operation

Fig.1 shows a typical startup circuit. Before the IC begins switching operation, it consumes only startup current (typically 3uA) and current supplied through the startup resistor Rst charges the VDD hold-up capacitor Cdd. When VDD reaches UVLO turn-on voltage of 15.5V(typical), SF5533W begins switching and the IC current consumed increased to 2mA (typical). The hold-up capacitor Cdd continues to supply VDD before the energy can be delivered from auxiliary winding Na. During this process, VDD must not drop below UVLO turn-off voltage (typical 9V). The selection of Rst and Cdd should be a trade off between the power loss and startup time.



♦ Low Operating Current


The operating current in SF5533W is as small as 2mA (typical). The small operating current results in higher efficiency and reduces the VDD hold-up capacitance requirement.

♦ Soft Start

SF5533W features an internal 4ms (typical) soft start that slowly increases the threshold of cycle-by-cycle current limiting comparator during startup sequence. It helps to prevent transformer saturation and reduce the stress on the secondary diode during startup. Every restart attempt is followed by a soft start activation.

◆ "Zero OCP/OPP Recovery Gap" Control

The definition of OCP or OPP recovery gap of a power adaptor is illustrated in Fig.2. assuming an adaptor is at full loading mode. If the loading keeps increasing, then the system will output maximum power P_opp, which will trigger OPP protection at the same time. After the OPP protection is triggered, usually the system will enter into the auto-recovery mode, in burst manner. If the svstem demand decreases power P recovery, then system will enter into normal mode again, as shown in Fig.2. The difference between P_opp and P_recovery is defined as "OPP Recovery Gap", which can cause system startup failure especially in 90VAC full load startup.



SF5533W can achieve "**Zero OCP/OPP Recovery Gap**" in the whole universal AC input range using SiFirst's proprietary control algorithm.

♦ Oscillator with Frequency Shuffling

PWM switching frequency in SF5533W is fixed to 65KHz and is trimmed to tight range. To improve system EMI performance, SF5533W operates the system with $\pm 4\%$ frequency shuffling around setting frequency.

Synchronous Slope Compensation

InSF5533W, the synchronous slope compensation circuit is integrated by adding voltage ramp onto the current sense input voltage for PWM generation. This greatly improves the close loop stability at CCM and prevents the sub-harmonic oscillation and thus reduces the output ripple voltage.

◆ Programmable OLP Debounce Time

Connecting a capacitor C_{CT} from CT pin to GND according to the equation below to program the OLP debounce time. In OLP debounce time, an internal current (14uA, typical) charges C_{CT} , when CT pin voltage reaches 3V, an internal 55ms debounce is triggered. When internal 55ms debounce time is over, the OLP protection is triggered and the system will enter into auto recovery protection mode.



$$T_{\mathrm{OLP_debource}} = \frac{3V * C_{\mathrm{CT}}}{14uA} + 55 \, ms$$

If CT pin is floating, the OLP debounce time is 55ms. Otherwise, the OLP debounce time can be programmed by CT capacitor.

♦ Proprietary η -Balance™ Control

The efficiency requirement of power conversion is becoming tighter than before. These new energy standards focus on the average efficiency of the whole loading range. Therefore, the light load efficiency is becoming more and more important. In SF5533W, a proprietary η -BalanceTM control is integrated to boost the light load efficiency. As shown in Fig.3, when the loading becomes light, the IC will reduce the PWM switching frequency according to an optimized frequency reduction curve. The specific frequency reduction curve and the power at a frequency are determined by the output of η -BalanceTM control. For example, P1 is at full load. P2 is at 75% full load. P3 and P4 are 50% and 25% full load respectively. The η -BalanceTM control can provide higher average efficiency than conventional frequency reduction technique, as illustrated in Fig.3





Fig.3

◆ Leading Edge Blanking (LEB)

Each time the power MOSFET is switched on, a turn-on spike occurs across the sensing resistor. The spike is caused by primary side capacitance and secondary side rectifier reverse recovery. To avoid premature termination of the switching pulse, an internal leading edge blanking circuit is built in. During this blanking period (250ns, typical), the PWM comparator is disabled and cannot switch off the gate driver. Thus, external RC filter with a small time constant is enough for current sensing.

♦ Burst Mode Control


When the loading is very small, the system enters into burst mode. When VFB drops below Vskip, SF5533W will stop switching and output voltage starts to drop, which causes the VFB to rise. Once VFB rises above Vskip, switching resumes. Burst mode control alternately enables and disables switching, thereby reducing switching loss in standby mode.



◆ Audio Noise Free OCP Compensation

Conventional OCP compensation may have audio noise issue when AC line is around 90VAC and heavy loading. As shown in Fig.5, when increasing from full load to hiccup load at 90VAC, VFB may oscillate in conventional OCP compensation system. The oscillation can generate large audio noise. In SF5533W, a proprietary "Audio Noise Free OCP Compensation" is integrated, which can achieve constant power limiting with no audio noise generated.





♦ Auto Recovery Mode Protection

As shown in Fig.6, once a fault condition is detected, switching will stop. This will cause VDD to fall because no power is delivered form the auxiliary winding. When VDD falls to UVLO(OFF) (typical 9V), the protection is reset and the operating current reduces to the startup current, which causes VDD to rise, as shown in Fig.4. However, if the fault still exists, the system will experience the above mentioned process. If the fault has gone, the system resumes normal operation. In this manner, the auto restart can alternatively enable and disable the switching until the fault condition is disappeared.






Fig.6

Over Load Protection (OLP) / Over Current Protection (OCP) / Over Power Protection (OPP) / Open Loop Protection (OLP)

When OLP/OCP/OPP/Open Loop occurs, a fault is detected. If this fault is present for more than $T_{\rm OLP_debouxe}$, the protection will be triggered, the IC will experience an auto-recovery mode protection as mentioned above, as shown in Fig.7. The $T_{\rm OLP_debouxe}$ debounce time is to prevent the false trigger from the power-on and turn-off transient.






Soft Gate Drive


SF5533W has a fast totem-pole gate driver with 300mA capability. Cross conduction has been avoided to minimize heat dissipation, increase efficiency, and enhance reliability. An internal 16V clamp is added for MOSFET gate protection at higher than expected VDD input. A soft driving waveform is implemented to minimize EMI.




PACKAGE MECHANICAL DATA

SOT-23-6L PACKAGE OUTLINE DIMENSIONS







Symbol	Dimensions In Millimeters		Dimensions In Inches		
	Min	Max	Min	Max	
Α	1.000	1.300	0.039	0.051	
A1	0.000	0.150	0.000	0.006	
A2	1.000	1.200	0.039	0.047	
b	0.300	0.500	0.012	0.020	
С	0.100	0.200	0.004	0.008	
D	2.800	3.020	0.110	0.119	
Е	1.500	1.700	0.059	0.067	
E1	2.600	3.000	0.102	0.118	
е	0.950	(BSC)	0.037 (BSC)		
e1	1.800	2.000	0.071	0.079	
L	0.300	0.600	0.012	0.024	
θ	00	8º	00	80	



IMPORTANT NOTICE

SiFirst Technology Nanhai, Ltd (SiFirst) reserves the right to make corrections, modifications, enhancements, improvements and other changes to its products and services at any time and to discontinue any product or service without notice. Customers should obtain the latest relevant information before placing orders and should verify that such information is current and complete.

SiFirst warrants performance of its hardware products to the specifications applicable at the time of sale in accordance with SiFirst's standard warranty. Testing and other quality control techniques are used to the extent SiFirst deems necessary to support this warranty. Except where mandated by government requirements, testing of all parameters of each product is not necessarily performed.

SiFirst assumes no liability for application assistance or customer product design. Customers are responsible for their products and applications using SiFirst's components. To minimize the risks associated with customer products and applications, customers should provide adequate design and operating safeguards.

Reproduction of SiFirst's information in SiFirst's data books or data sheets is permissible only if reproduction is without alteration and is accompanied by all associated warranties, conditions, limitations, and notices. Reproduction of this information with alteration is an unfair and deceptive business practice. SiFirst is not responsible or liable for such altered documentation. Information of third parties may be subject to additional restrictions.

Resale of SiFirst's products or services with statements different from or beyond the parameters stated by SiFirst for that product or service voids all express and any implied warranties for the associated SiFirst's product or service and is an unfair and deceptive business practice. SiFirst is not responsible or liable for any such statements.

SiFirst's products are neither designed nor intended for use in military applications. SiFirst will not be held liable for any damages or claims resulting from the use of its products in military applications.

SiFirst's products are not designed to be used as components in devices intended to support or sustain human life. SiFirst will not be held liable for any damages or claims resulting from the use of its products in medical applications.