



- 6.3 x 6.3 mm footprint
- Multiple heights
- Ground pin option

# Typical Applications

- Metering
- White goods
- Home and garden equipment



# **Specification**

FUNCTION: Momentary action

CONTACT ARRANGEMENT: 1 make contact = SPST N.O.

TERMINALS: G type for SMT

## Mechanical

TRAVEL:

0.20 mm  $\pm$ 0.15 mm for 160 &250 gf 0.30 mm  $\pm$ 0.15 mm for 320 gf OPERATING LIFE: 100,000 cycles

**OPERATION FORCE:** 

160 gf ±50 gf blue actuator 250 gf ±50 gf red actuator 320 gf ±80 gf black actuator

### **Packaging**

Switches in reels of 1,500 pieces. Dimensions of reels according to EIA 481B External diameter 330 mm

### **Electrical**

MAXIMUM VOLTAGE: 12 VDC
MAXIMUM CURRENT DC: 50 mA
DIELECTRIC STRENGTH: 250 VA C (1mn)
CONTACT RESISTANCE: 100 m O

CONTACT RESISTANCE: 100 m  $\Omega$  INSULATION RESISTANCE:  $\geq$  100 M  $\Omega$ 

BOUNCE TIME: < 5 ms

#### **Environmental**

OPERATING TEMPERATURE: -20°C to 85°C

#### **Process**


SOLDERING: This component is suited to the following methods: Infrared Reflow Soldering in accordance with IEC61760-1

NOTE: Specifications listed above are for switches with standard options.

For information on specific and custom switches, consult Customer Service Center.

# **How To Order**


Our easy build-a-switch concept allows you to mix and match options to create the switch you need. To order, select desired option from each category and and place it in the appropriate box.






# PTS641 Series SMT Top Actuated Switches


# **NO GROUND PIN** H = 2.5, 3.1, or 3.4 mm














RECOMMENDED PCB LAYOUT

# **GROUND PIN** H = 2.5, 3.1, or 3.4 mm









RECOMMENDED PCB LAYOUT



B-97