

MH282 is an unipolar Hall effect sensor IC. It incorporates advanced chopper stabilization technology to provide accurate and stable magnetic switch points. The design, specifications and performance have been optimized for applications of solid state switches.

The output transistor will be switched on (BoP) in the presence of a sufficiently strong South pole magnetic field facing the marked side of the package. Similarly, the output will be switched off (BRP) in the presence of a weaker South field and remain off with "0" field.

The package type is in a Halogen Free version was verified by third party organization. Halogen Free package is available by customer's option.

Features and Benefits

- DMOS Hall IC Technology.
- Reverse bias protection on power supply pin.
- Solid-State Reliability.
- Chopper stabilized amplifier stage.
- Unipolar, output switches with absolute value of South pole from magnet.
- Operation down to 3.0V.
- High Sensitivity for direct reed switch replacement applications.
- 100% tested at 125°C for K Spec.
- Custom sensitivity / Temperature selection are available.
- Good ESD Protection.

Applications

- Solid state switch
- Limit switch
- Current limit
- Interrupter
- Current sensing
- Magnet proximity sensor for reed switch replacement

	Company Name and Product Category		
XXXXXXXXX - X	MH:MST Hall Effect/MP:MST Power IC		
	Part number		
Sorting Code	181,182,183,184,185,248,249,276,477,381,381F,381R,382		
Package type	If part # is just 3 digits, the forth digit will be omitted.		
	Temperature range		
Temperature Code	E: 85 °C, I: 105 °C, K: 125 °C, L: 150 °C		
Part number	Package type		
	UA:TO-92S,VK:TO-92S(4pin),VF:TO-92S(5pin),SO:SOT-23,		
Company Name and Product Category	SQ:QFN-3,ST:TSOT-23,SN:SOT-553,SF:SOT-89(5pin),		
	SS:TSOT-26,SD:DFN-6		
	Sorting		
	α, β ,Blank		


Ordering Information



Part No.	Temperature Suffix	Package Type	
MH282KUA	K (-40°C to $+ 125$ °C)	UA (TO-92S)	
MH282KSO	K (-40°C to $+ 125$ °C)	SO (SOT-23)	
MH282EUA	E (-40°C to + 85°C)	UA (TO-92S)	
MH282ESO	E (-40°C to + 85°C)	SO (SOT-23)	

KUA spec is using in industrial and automotive application. Special Hot Testing is utilized.

Functional Diagram



Absolute Maximum Ratings At (Ta=25 °C)

Characteristics		Values	Unit		
Supply voltage,(VDD)		28	V		
Output Voltage,(Vo)		28	V		
Reverse Voltage, (VDD)		-28	V		
Magnetic flux density		Unlimited	Gauss		
Output current, (<i>Iour</i>)		50	mA		
Operating Temperature Range, (Ta)		"E" version	-40 to +85	°C °C	
		"K" version	-40 to +125		
Storage temperature range, (<i>Ts</i>)		-55 to +150	°C		
Maximum Junction Temp,(<i>Tj</i>)		150	°C		
Thermal Resistance	$(heta_{j})$	a) UA / SO	206 / 543	°C/W	
	$(heta_{jc})$ UA / SO		148 / 410	°C/W	
Package Power Dissipation, (P_D) UA / SO		606 / 230	mW		

Note: Do not apply reverse voltage to V_{DD} and V_{OUT} Pin, It may be caused for Miss function or damaged device.




Electrical Specifications

DC Operating Parameters : $T_A = +25 \,^{\circ}C$, $V_{DD} = 12V$

Parameters	Test Conditions	Min	Тур	Max	Units
Supply Voltage,(VDD)	Operating	3.0		24.0	V
Supply Current,(<i>I</i> _{DD})	B <bop< td=""><td></td><td>2.5</td><td>5.0</td><td>mA</td></bop<>		2.5	5.0	mA
Output Saturation Voltage,(V _{Sat})	IOUT = $20 \text{ mA}, \text{B} > \text{B}_{\text{OP}}$			400.0	mV
Output Leakage Current, (Ioff)	IOFF B $<$ Brp, Vout = 20V			10.0	uA
Output Rise Time, (<i>T</i> _R)	RL=1k Ω , CL=20pF		0.04	0.45	uS
Output Fall Time, (<i>T_F</i>)	RL=820 Ω ; CL=20pF		0.18	0.45	uS
Electro-Static Discharge	НМВ	4			KV
Operate Point,(<i>Bop</i>)		60		100	Gauss
Release Point,(<i>B_{RP}</i>)		40		80	Gauss
Hysteresis, (BHYS)			20		Gauss


Typical application circuit






Sensor Location, Package Dimension and Marking MH282 Package


UA Package




Hall Chip location




Output Pin Assignment (Top view)



Hall Plate Chip Location (Bottom view)





0,15 0,00

Package (SOT-23)

(Top View)

NOTES:

0,60 0,30

- 1. PINOUT (See Top View at left :)
 - $Pin \ 1 \qquad V_{DD}$
 - Pin 2 Output
 - Pin 3 GND
- 2. Controlling dimension: mm
- 3. Lead thickness after solder plating will be 0.254mm maximum