

ITEM :

CRYSTAL OSCILLATOR

TYPE :

DSA321SDN

NOMINAL FREQUENCY :

26.000MHz

SPEC No. :

1XTV26000PCA

Please acknowledge receipt of this specification by signing and returning a copy to us.

	RECEIPT
DATE	
RECEIVED	(signature) (name)

General Manufacturer of Quartz Devices



675-0194 Japan Phone (81)79-425-3141 Fax (81)79-425-1134 http://www.kds.info/index en.htm

C.ENG. A. Hishikawa H. Takase

ENG.

- 1. Device Name VC-TCXO
- 2. Model Name DSA321SDN
- 3. Nominal Frequency 26.000 MHz
- 4. Mass 0.03g max.

5. Absolute Maximum Ratings

	Item	Symbol		Rating		unit	
1	Supply Voltage	Vcc		-0.3~+4.6		V	
2	Storage Temperature Range	T_ _{STG}	-40~+85			°C	
6. Recommended Operating Conditions							
	Item	Symbol	min.	typ.	max.	unit	
1	Supply Voltage	V _{CC}	+2.66	+2.8	+2.94	V	
2	Load Impedance (resistance part)	$L_{OAD}R$	9	10	11	kΩ	
	(parallel capacitance)	L _{OAD} _C	9	10	11	pF	
3	Control Voltage Range	V _{CONT}	+0.5	+1.5	+2.5	V	
4	Operating Temperature Range	T_ _{OPR}	-30	-	+85	°C	

7. Electrical Characteristics

 $(T_A=-30 \sim +85^{\circ}C, L_{OAD}_R//C=10 k\Omega//10 pF, V_{CC}=+2.8V, V_{CONT}=+1.5V, unless otherwise noted)$

	ltere	Conditions		Limits		Notes	
	Item	Conditions	min.	min. typ.			unit
1	Current Consumption		-	-	+1.5	mA	
2	Output Level		0.8	-	-	V_{P-P}	1
3	Symmetry	GND level (DC cut)	40/60	-	60/40	%	
4	Harmonics		-	-	-5	dBc	
5	Frequency Stability						
	1.Tolerance	After 2 times reflow Ref. to nominal frequency	-	-	±1.5	ppm	2,3
	2.vs Temperature	T _A =-30~+85°C Ref. to frequency (T _A =+25°C)	-	-	±2.5	ppm	
	3.vs Supply Voltage	V _{CC} =+2.8V±5%	-	-	±0.2	ppm	
	4.vs Load Variation	L _{OAD} _R//C=(10kΩ//10pF)±10%	-	-	±0.2	ppm	
	5.vs Aging	T _A =Room ambient	-	-	±1.0	ppm/year	
6	Start Up Time	@90% of final Vout level	-	-	2.0	ms	
7	Frequency Control 1.Control Range	V _{CONT} =+1.5V±1.0V	±25	-	-	ppm	4
	2.Input Resistance		500	-	-	kΩ	
8	SSB Phase Noise	Relative to f0 level offset 1kHz	-	-	-130	dBc/Hz	

Notes


1. Clipped sine wave (DC-coupled)

2. T_A=+25°C

3. Please leave after reflow in 2h or more at room ambient.

4. Positive slope (Frequency becomes high in proportion to frequency control voltage.)

TITLE	Remark		
DSA321SDN TYPE SPECIFICATION			
Date	Spec. No.	Rev.	Page
2015/05/13	1XTV26000PCA	-	1/13



	Item	Description	ause.13) except 1		quirements	0	
1	Drop			- Ne	quirements		
1	ыор	Natural drop (On concrete)	luciant 100a)				
		Mounting on the set or test fixture.(Tota	ii weight Tuug)				
		Height : 150cm		df/f=<±1.0p	pm		
		Direction : X,Y,Z, 6directions		•	•		
		Test cycle : 3cycles					
		Reference specification : EIAJ-ED-470	2A Method5				
2	Vibration	Sweep range : 10~500Hz					
		Sweep speed : 11min/cycle					
		Amplitude : 1.5mm (10~55Hz)					
		Acceleration : 200m/s ² (55~500Hz)		df/f=<±0.5p	pm		
		Direction : X,Y,Z, 3directions					
		Test cycle : 10cycles					
		Reference specification : IEC 60068-2-	6				
3	Shock	Acceleration : 1000m/s ²					
		Direction : X,Y,Z, 6directions					
		Duration : 6ms		df/f=<±0.5p	pm		
		Test cycle : 3cycles/each directions					
		Reference specification : IEC 60068-2-	27				
4	PCB bend	PWB : t=1.6mm					
•	strength	Pressure speed : 1.0mm/s		df/f=<±0.5ppm			
	ouongui	Bend width : $1 \rightarrow 2 \rightarrow 3$ mm		No visible damage.			
		Duration : $10\pm1s$		No leak damage.			
		Reference specification : IEC 60068-2-	21 1 61	No leak damage.			
5	Adherence nature	PWB : t=1.6mm	21001				
5	Aunerence nature		df/f=<+0.5p				
		Direction : X,Y, 2directions	df/f=<±0.5ppm				
		Pressure : 10N		visible damage.			
		Duration : 10±1s	04.11.0	No leak damage.			
		Reference specification : IEC 60068-2-	21 063				
6	Package strength	Pressure : 10N		df/f=<±0.5ppm No mechanical damage.			
		Duration : 10±1s					
		Reference specification : IEC 60068-2-	77	No leak damage.			
7	Gross leak	It is immersed for 3min into +125±5°C					
		Chlorofluorocarbon (CFCs) liquid.	No continuous air bubbles.				
		Reference specification : IEC 60068-2-					
8	Fine leak	It shall be measured by the helium leak					
		after pressurization for 60min by the pr	windian for Comin by the pressure			~	
		of $(3.92\pm0.49) \times 10^5$ Pa in a helium gas	atmosphere.	Less than 1.0x10 ⁻⁹ Pa m ³ /s.			
		Reference specification : IEC 60068-2-	17				
9	Solderability	Solder bath temperature : +245±5°C		A new unifo	orm coating of	soldei	
		Duration : 3±0.3s		shall cover	a minimum of	95%	
		Reference specification : IEC 60068-2-	58	of the surfa	ce being imme	ersed.	
0	Resistance to	1) Solder iron method			-		
	soldering heat	Bit size : $B(\varphi 3)$ Bit temperature : +350	0±10°C	df/f=<±0.5ppm			
	Ŭ	Duration : 3+1/-0s /each terminal		dV _{OUT} =<±0			
		It shall be measured after 2h at room te	emperature.	No visible d			
		humidity. Reference specification : IEC					
		2) Reflow	00000 2 20				
		In refer to temperature profile shown in	clause13	$df/f = < \pm 1.0 n$	nm		
		Test cycle : 3cycles		df/f=<±1.0ppm dV _{OUT} =<±0.2V _{P-P}			
			mooratura				
		It shall be measured after 2h at room te humidity. Reference specification : IEC		No visible d	anaye.		
			0000-2-00	1			
LE			nark				
	321SDN TYPE SPECIF		nai N				
ite			Spec. No.		Rev.	Pag	
	/05/13						

11. Environmental Characteristics All test is performed after 3 times reflow (Clause13) Item Description Requirements 1 Low temperature df/f=<±1.0ppm Temperature : -40±3°C storage dVout=<±0.2VP-P Duration: 1000h It shall be measured after 2h at room temperature. The electrical characteristics humidity. Reference specification : IEC 60068-2-1 Ab are satisfied. 2 High temperature Temperature : +85±2°C df/f=<±1.0ppm storage $dV_{OUT} = < \pm 0.2V_{P-P}$ Duration: 1000h The electrical characteristics It shall be measured after 2h at room temperature, are satisfied. humidity. Reference specification : IEC 60068-2-2 Bb 3 Humidity Temperature : +85±2°C df/f=<±1.0ppm R.H. 85±5% $dV_{OUT} = < \pm 0.2V_{P-P}$ Duration: 1000h The electrical characteristics It shall be measured after 2h at room temperature. are satisfied. humidity. Reference specification : IEC 60068-2-3 HTB 4 Temperature : +85±2°C df/f=<±1.0ppm Duration: 1000h $dV_{OUT} = < \pm 0.2V_{P-P}$ BIAS : Max value of supply voltage The electrical characteristics It shall be measured after 2h at room temperature, are satisfied. humidity. Reference specification : IEC 60068-2-2 Bb 5 THB Temperature : +40±2°C R.H. 90~95% df/f=<±1.0ppm $dV_{OUT} = <\pm 0.2V_{P-P}$ Duration: 1000h The electrical characteristics BIAS : Max value of supply voltage are satisfied. It shall be measured after 2h at room temperature, humidity. Reference specification : IEC 60068-2-3 6 Thermal shock Thermal shock : $-40\pm3^{\circ}C$: 0.5h \Leftrightarrow $+85\pm2^{\circ}C$: 0.5h df/f=<±1.0ppm Test cycle : 200cycles dV_{OUT}=<±0.2V_{P-P} Shift time : 2~3min The electrical characteristics It shall be measured after 2h at room temperature, are satisfied. humidity. Reference specification : IEC pub.68-2-14.Na 7 ESD Model : Machine Model (MM) V=±200V (C1=200pF, R1=0Ω) df/f=<±1.0ppm

Number of times : 3times

(Connect to test terminal)

Number of times : 3times

(Connect to test terminal)

Each terminal except common terminal.

Each terminal except common terminal.

Reference specification : EIA/JESD22-A115

Model : Human Body Model (HBM) V=±1500V (C1=100pF, R1=1500Ω)

Reference specification : EIA/JESD22-A114

TITLE	Remark		
DSA321SDN TYPE SPECIFICATION			
Date	Spec. No.	Rev.	Page
2015/05/13	1XTV26000PCA	-	4/13

DAISHINKU CORP.

 $dV_{OUT} = < \pm 0.2V_{P-P}$

are satisfied.

df/f=<±1.0ppm


are satisfied.

dVout=<±0.2VP-P

The electrical characteristics

The electrical characteristics

12. Flatness of Terminal When the component is placed on the flat surface, the gap	from the connecting terminal shall no	t exceed 0.05	mm.
	Gap : 0.05mm max.		
13. Reflow Profile	·		
+260°C			
Time			
1 Preheat +160 2 Primary Heat +220 3 Peak +260			
TITLE	Remark		
DSA321SDN TYPE SPECIFICATION Date 2015/05/13	Spec. No. 1XTV26000PCA	Rev. –	Page 5/13



ree

15. Packing Condition

- 15.1 Taping package
 - (1) Emboss tape format and dimensions See Fig.1
 - (2) Quantity on reel 2000pcs. max. / reel
 - (3) Taping specification
 - See Fig.2
 - No lack of a product. (4) Reel specification
 - See Fig.3
 - (5) Taping material list See right table.

15.2 Packing

- The products packed in the antistatic bag.
- *Moisture sensitivity level : IPC/JEDEC Standard J-STD-033 / Level 1
- No dry pack required and baking after re-storage is unnecessary.

15.3 Packing box


Max 10 reels/packing box. However, in the case of less than 10 reels, It is contained by any boxes. The space in a box is fill up with a cushion.

15.4 Label detail

A Lot label is put on a reel and a shipping label and Pb-Free label is put on a packing box.

Lot label		Shipping label		Pb-free	Label
TYPE SPEC NO. PARTS NO. LOT NO. FREQ. Q'TY	(Model Name) (Spec. Number) (User's Parts Number) (Lot Number) (Nominal Frequency) (Quantity)	ITEM SPEC DELIVERY DATE Q'TY NOTES DAISHINKU CORF	(Model Name) (Spec. Number) (Delivery Date) (Quantity) (User's Parts Number)	Pb-1	
KDS	DAISHINKU CORP.				1 1

Lot label (Example)



Formation of a lot number

e.g. AH5101001			
<u> </u>	<u>_H_</u>	5101	001
Manufacturing site code	Product code	year/ month/ day	Serial No.

Taping material List

Emboss : PS (Conductivity)

Reel : PS (Conductivity)


Cover Tape : PET + Olefin Resin (Conductivity)

The notation method of a manufacture year, month, and day. (4digits alphanumeric character)


Y	<u>YMDD</u> (4digits) e.g.) $2015 /01 /01 \rightarrow 5101$											
Y Year 1digit (Last digit of Year)												
Month 1digit alphanumeric symbol												
DD Day 2digits numerical characters of day												
Month	Jan.	Feb.	Mar.	Apr.	May.	Jun.	Jul.	Aug.	Sep.	Oct.	Nov.	Dec.
Symbol	1	2	3	4	5	6	7	8	9	0	Ν	D


TITLE	Remark		
DSA321SDN TYPE SPECIFICATION			
Date	Spec. No.	Rev.	Page
2015/05/13	1XTV26000PCA	-	7/13

Lot Label		
Antistatic Bag	ir Cushion	
	b-free Label	
The product is packed up with the method which do	bes not break in the handling by a shipping	g agent.
TLE SA321SDN TYPE SPECIFICATION	Remark	
ate 015/05/13	Spec. No. 1XTV26000PCA	Rev. Page - 8/13



DM-Z0002: Style-010 Ver.1





16. Notes on mounting and handling

16.1 Storage environment

- (1) The temperature and humidity of a storage place, Please give +5~+40°C and 40~85% as a standard.
- (2) Please use this product within one year from the packing label date of issue.
- (3) Please avoid the place which generates corrosive gas, and the place with much dirt.
- (4) Please keep it in a place with little temperature change.
- Dew condensation arises owing to a rapid temperature change and solderability becomes bad.
- 16.2 Be cautions to static electricity and high voltage.
- 16.3 This product has sufficient durability to fall and vibration. However, conditions may change to the fall after mounting to a PWB, and vibration. When you should drop on a floor the PWB which mounted the product or too much shock is added. Please use after a performance check.
- 16.4 Please check that the curvature of the substrate at the time of substrate cutting does not affect product. Moreover, especially when a product is near the position of a PWB guide pin, and the position of PWB break, be careful.
- 16.5 The part concerned does not correspond to washing.

16.6 Please repair at +260°C in 10s with hot air or +350°C in 5s with solder Iron.

17. Mandatory control

17.1 Ozone-depleting substance

It regulates by the U.S. air purifying method (November, 1990 establishment). ODS of CLASS1 and CLASS2 is not contained or used.

17.2 PBDE, PBBs

PBDE, PBBs are not contained into all the material currently used for this product.

17.3 RoHS

Following material restricted by RoHS (2011/65/EU) is not included or used. Lead, mercury, cadmium, hexavalent, chromium, PBB and PBDE.

17.4 Law Concerning Examination and Regulation of Manufacture, etc. of Chemical Substances

All the material currently used for this product is based on "Law Concerning Examination and Regulation of Manufacture, etc. of Chemical Substances". It is a registered material.

17.5 Lead

Leads, such as solder, are not used for this product. (Lead Free)

17.6 About the existence of silver and mercury use

The silver of very small quantity is contained in the conductive adhesives used for adhesion of Blank. Moreover, mercury is used. It does not get down.

18. The country of origin / factory name / address

Country of origin:	Japan
Factory name:	DAISHINKU Corp. Tottori Production Div.
Address:	7-3-21 Wakabadai minami, Tottori 689-1112

TITLE	Remark		
DSA321SDN TYPE SPECIFICATION			
Date	Spec. No.	Rev.	Page
2015/05/13	1XTV26000PCA	-	12/13

2015-0507 REVERSION RECORD

Rev. No.	Date	Reason	Contents	Approved	Checked	Drawn
-	2015/05/13	-	Initial Release	A.Hishikawa	H.Takase	S.Fujihira
				1	<u> </u>	
				1		
				1		