

MXD8544A

0.1-3.0GHz SP4T Antenna Tuning Switch



This document contains information that is confidential and proprietary to Maxscend Microelectronics Company Limited (Maxscend) and may not be reproduced in any form without express written consent of Maxscend. No transfer or licensing of technology is implied by this document.



General Description

The MXD8544A is a CMOS silicon-on-insulator (SOI), single-pole, four-throw (SP4T) switch. The high linearity and ruggedness performance and extremely low insertion loss makes the device an ideal choice for GSM/WCDMA/LTE handset antenna tuning application.

The MXD8544A SP4T switch is provided in a compact LGA 1.1mm x 1.5mm x 0.36mm package. A functional block diagram is shown in Figure 1. The pin configuration and package are shown in Figure 2. Signal pin assignments and functional pin descriptions are provided in Table 1.

Applications

- GSM/WCDMA/LTE band and mode switching
- Antenna tuning switch

Features

- Broadband frequency range: 0.1 to 3.0 GHz
- Low insertion 0.50dB @ 2.7 GHz
- High P0.1dB of 43.3dBm
- Positive low voltage control: VC = 1.0 to 3.0 V,
 VDD = 2.5 to 3.3 V, Small LGA (10-pin,
 1.1mm x 1.5mm x 0.36mm) package

Functional Block Diagram and Pin Function




Figure 1.Functional Block Diagram




Figure 2.Pin-out (Top View)



Application Circuit




Figure 3. MXD8544A Application Circuit

Table 1. Pin Description

| Table 1. Pir | n Descriptio | n | | | |
|--------------|--------------|------------------|---------|------|------------------|
| Pin No. | Name | Description | Pin No. | Name | Description |
| 1 | RF1 | RF port 1 | 6 | V2 | Control Logic #2 |
| 2 | RF2 | RF port 2 | 7 | GND | Ground |
| 3 | V3 | Control Logic #3 | 8 | RF4 | RF port 4 |
| 4 | VDD | DC power supply | 9 | RF3 | RF port 3 |
| 5 | V1 | Control Logic #1 | 10 | ANT | Antenna port |

Truth Table

Table 2.

| State | V1 | V2 | V3 | RF Path | |
|---|----|----|----|--------------------|--|
| 1 | 0 | 0 | 1 | All Ron | |
| 2 | 0 | 1 | 1 | ANT to RF1 and RF2 | |
| 3 | 1 | 0 | 1 | ANT to RF3 and RF4 | |
| 4 | 0 | 0 | 0 | ANT to RF1 | |
| 5 | 0 | 1 | 0 | ANT to RF2 | |
| 6 | 1 | 0 | 0 | ANT to RF3 | |
| 7 | 1 | 1 | 0 | ANT to RF4 | |
| 8 1 | | 1 | 1 | All isolation | |
| Note: "1" = 1.0 V to 3.00 V. "0" = 0 V to +0.3 V. | | | | | |

Recommended Operation Range

Table 3.

| Parameters | Symbol | Min | Тур | Max | Units |
|-----------------------------|---------------------|-----|-----|-----|-------|
| Operation Frequency | f1 | 0.1 | ı | 3.0 | GHz |
| Power supply | V_{DD} | 2.5 | 2.8 | 3.3 | V |
| Switch Control Voltage High | V _{CTL_} H | 1.0 | 1.8 | 3.0 | V |
| Switch Control Voltage Low | V _{CTL_L} | 0 | 0 | 0.3 | V |



Specifications

Table 4.Electrical Specifications

| D | 0 | Specification | | 11 | T4 O P(| |
|-------------------------------------|---------------------------------------|---------------|--|------------|----------|--|
| Parameter | Symbol | Min. | Typical | Max. | Units | Test Condition |
| DC Specifications | | | <u>. </u> | | • | |
| Control voltage: | . , | _ | | | ., | |
| Low High | Vctl_L | 0 1.0 | 0 1.8 | 0.3 3.0 | V | |
| Supply voltage | V _{CTL_H} V _{DD} | 2.5 | 2.8 | 3.3 | V | |
| Supply current | I _{DD} | 2.0 | 75 | 110 | uA | V _{DD} = 2.8 V |
| Control current | Ictl | | 1 | 5 | uA | V _{CTL} = 1.8 V |
| RF Specifications | | | <u> </u> | | L | |
| | | | 0.35 | 0.45 | dB | 0.8 to 1.0 GHz |
| Insertion loss | IL | | 0.45 | 0.55 | dB | 1.0 to 2.2 GHz |
| | | 00 | 0.50 | 0.70 | dB | 2.2 to 3.0 GHz |
| Isolation | ISO | 26 22 | 28 24 | | dB dB | 0.8 to 1.0 GHz 1.0 to 2.2 GHz |
| isolation | 130 | 19 | 22 | | dB | 2.2 to 3.0 GHz |
| Return loss | S ₁₁ | 10 | 20 | | dB | 0.8 to 3.0 GHz |
| Voltage Standing Wave Ratio | VSWR | | 1.20 | | | 0.8 to 3.0 GHz |
| On Resistance (RF1/2/3/4 to ANT) | Ron | | 1.05 | 1.15 | Ω | Switch on Path |
| OFF Capacitance (RF1/2/3/4 to ANT) | Coff | | 130 | 150 | fF | Switch off Path |
| Input 0.1 dB compression point | P _{0.1dB} | +43 | +43.3 | | dBm | 0.8 to 3.0 GHz, ANT to RF1/2/3/4 |
| Peak RF operating voltage | V_{peak} | | 45 | | V | f0 = 700 to 2700 MHz, 25% duty cycle |
| LTE TX harmonic | 2f0 | | -90 | -80 | dBm | f0 = 700 to 2700 MHz, PIN = +26 |
| (RF1/2/3/4 to ANT) | 3f0 | | -80 | -70 | dBm | dBm |
| GSM LB harmonic | 2f0 | | -60 | -50 | dBm | f0 = 824 to 915 MHz, PIN = +35 |
| (RF1/2/3/4 to ANT) | 3f0 | | -60 | -50 | dBm | dBm |
| GSM HB harmonic | 2f0 | | -60 | -50 | dBm | f0 = 1710 to 2690 MHz, PIN = +33 |
| (RF1/2/3/4 to ANT) | 3f0 | | -60 | -50 | dBm | dBm |
| Second order intermodulation | IMD2 | | -112 | -105 | dBm | CW Carrier on RF Port, +20 dBm CW Interferer on ANT port, -15 dBm |
| Third order intermodulation | IMD3 | | -112 | -105 | dBm | CW Carrier on RF Port, +20 dBm CW Interferer on ANT port, -15 dBm |
| Switching on time | | | 3.0 | 5.0 | μs | 50% VCTL to 90% RF |
| Switching off time | | | 3.0 | 5.0 | μs | 50% VCTL to 10% RF |
| Startup time | | | 10 | 20 | μs | Power off state to any RF switch state |



Table 5. IMD2 Test Conditions

| Band | In-band freq | CW Carrier | | CW Interferer | |
|--------|--------------|------------|-----|---------------|-----|
| Dallu | MHz | MHz | dBm | MHz | dBm |
| 1 Low | 2140 | 1950 | +20 | 190 | -15 |
| 1 High | 2140 | 1950 | +20 | 4090 | -15 |
| 5 Low | 881.5 | 836.5 | +20 | 45 | -15 |
| 5 High | 881.5 | 836.5 | +20 | 1718 | -15 |

Table 6. IMD3 Test Conditions

| Band | In-band freq | CW C | CW Carrier | | CW Interferer | |
|-------|--------------|-------|------------|-------|---------------|--|
| Ballu | MHz | MHz | dBm | MHz | dBm | |
| 1 | 2140 | 1950 | +20 | 1760 | -15 | |
| 5 | 881.5 | 836.5 | +20 | 791.5 | -15 | |

Absolute Maximum Ratings

Table 7. Maximum ratings

| Parameters | Symbol | Minimum | Maximum | Units |
|---|------------------|---------|---------|-------|
| Supply voltage | V_{DD} | +2.5 | +3.6 | V |
| Digital control voltage | V_{CTL} | 0 | +3.6 | V |
| RF input power | P _{IN} | | +43.8 | dBm |
| Operating temperature | Top | -30 | +85 | °C |
| Storage temperature | T _{STG} | -55 | +150 | °C |
| Electrostatic Discharge Human body model (HBM), Class 2 | ESD_HBM | | 2000 | |
| Machine Model (MM), | ESD_MM | | 200 | V |
| Class B Charged device model (CDM), Class III | ESD_CDM | | 500 | |

Note: Exposure to maximum rating conditions for extended periods may reduce device reliability. There is no damage to device with only one parameter set at the limit and all other parameters set at or below their nominal value. Exceeding any of the limits listed here may result in permanent damage to the device.



Package Outline Dimension




Figure 4. Package outline dimension



Reflow Chart




Figure 5. Recommended Lead-Free Reflow Profile

Table 8.

| Profile Parameter | Lead-Free Assembly, Convection, IR/Convection |
|---|---|
| Ramp-up rate (TS _{max} to T _p) | 3℃/second max. |
| Preheat temperature (TS _{min} to TS _{max}) | 150℃ to 200℃ |
| Preheat time (t _s) | 60 - 180 seconds |
| Time above TL , 217℃ (t _L) | 60 - 150 seconds |
| Peak temperature (T _p) | 260℃ |
| Time within 5°C of peak temperature(t _p) | 20 - 40 seconds |
| Ramp-down rate | 6°C/second max. |
| Time 25°C to peak temperature | 8 minutes max. |

ESD Sensitivity

Integrated circuits are ESD sensitive and can be damaged by static electric charge. Proper ESD protection techniques should be used when handling these devices.

RoHS Compliant

This product does not contain lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls (PBB) and polybrominated diphenyl ethers (PBDE), and are considered RoHS compliant.