Note: This datasheet may be out of date Please download the latest datasheet of BLM15BD102SH1# from the official website of Murata Manufacturing

https://www.murata.com/en-us/products/productdetail?partno=BLM15BD102SH1%23

### BLM15BD102SH1#

"#" indicates a package specification code.









< List of part numbers with package codes >

BLM15BD102SH1B BLM15BD102SH1D BLM15BD102SH1J



### Appearance & Shape











# **Features**

The chip ferrite beads BLM series is designed to function nearly as a resistor at noise frequencies, which greatly reduces the possibility of resonance and leaves signal wave forms undistorted. BLM series is effective in circuits without stable

ground lines because BLM series does not need a connection to ground.

The nickel barrier structure of the external electrodes provides excellent solder heat resistance. BLM B series can minimize attenuation of the signal waveform due to its sharp impedance characteristics. Various impedances are available to match signal frequency.



### **Applications**

Automotive Usage	Powertrain/Safety
---------------------	-------------------



# **Packaging Information**

Packaging	Specifications	Minimum Order Quantity
В	Bulk(Bag)	1000
D	180mm Paper Tape	10000
J	330mm Paper Tape	50000

1 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated : 2018/03/09

Note: This datasheet may be out of date

 $\underline{ Please \ download \ the \ latest \ data sheet \ of \ BLM15BD102SH1\# \ from \ the \ official \ website \ of \ Murata \ Manufacturing} }$ 

Co., Ltd. https://www.murata.com/en-us/products/productdetail?partno=BLM15BD102SH1%23

# BLM15BD102SH1#

"#" indicates a package specification code.



Shape	SMD
Size Code (in mm)	1005
Size Code (in inch)	0402
Length	1.0mm
Length Tolerance	±0.05mm
Width	0.5mm
Width Tolerance	±0.05mm
Thickness	0.5mm
Thickness Tolerance	±0.05mm
Impedance (at 100MHz)	1000Ω
Impedance (at 100MHz) Tolerance	±25%
Rated Current (at 85°C)	200mA
Rated Current (at 125°C)	200mA
DC Resistance(max.)	0.9Ω
Operating Temperature Range	-55°C to 125°C
Mass(typ.)	0.001g
Number of Circuit	1

2 of 3

#### Attention

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/

Last updated :2018/03/09


<sup>1.</sup> This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.


Co., Ltd. https://www.murata.com/en-us/products/productdetail?partno=BLM15BD102SH1%23

# BLM15BD102SH1#

"#" indicates a package specification code.







Impedance-Frequency Characteristics

**Equivalent Circuit** 

3 of 3

#### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering. 2.This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering



URL: https://www.murata.com/