

# **DATA SHEET**

THIN FILM CHIP RESISTORS
High precision - high stability
RT series
0.01% TO 1%, TCR 5 TO 50
sizes 0201/0402/0603/0805/1206/
1210/2010/2512

**RoHS** compliant



YAGEO Phicomp



#### SCOPE

This specification describes RT series high precision - high stability chip resistors with lead-free terminations made by thin film process.

#### **APPLICATIONS**

- Converters
- Printing equipment
- Server board
- Telecom
- Consumer

#### **FEATURES**

- Halogen Free Epoxy
- RoHS compliant
- Reducing environmentally hazardous wastes
- High component and equipment reliability
- Saving of PCB space
- None forbidden-materials used in products/production

#### ORDERING INFORMATION - GLOBAL PART NUMBER & 12NC

Both part numbers are identified by the series, size, tolerance, packing type, temperature coefficient, taping reel and resistance value.

## YAGEO BRAND ordering code

#### **GLOBAL PART NUMBER (PREFERRED)**

## RT XXXX F X X XX XXXX L

(1) (2) (3) (4) (5) (6) (7)

#### (I) SIZE

0201/0402/0603/0805/1206/1210/2010/2512

#### (2) TOLERANCE

 $L = \pm 0.01\%$ 

 $W = \pm 0.05\%$ 

 $B = \pm 0.1\%$ 

 $C = \pm 0.25\%$ 

 $D = \pm 0.5\%$ 

 $F = \pm 1\%$ 

#### (3) PACKAGING TYPE

R = Paper/PE taping reel

K = Embossed taping reel

#### (4) TEMPERATURE COEFFICIENT OF RESISTANCE

 $A = 5 ppm/^{\circ}C$ 

 $B = 10 \text{ ppm/}^{\circ}\text{C}$ 

 $C = 15 \text{ ppm/}^{\circ}C$ 

 $D = 25 \text{ ppm/}^{\circ}C$ 

 $E = 50 \text{ ppm/}^{\circ}\text{C}$ 

#### (5) TAPING REEL

07 = 7 inch dia. Reel

10 = 10 inch dia, Reel

13 = 13 inch dia, Reel

#### (6) RESISTANCE VALUE

There are  $2\sim4$  digits indicated the resistor value. Letter R/K/M is decimal point. Detailed resistance rules show in table of "Resistance rule of global part number".

#### (7) DEFAULT CODE

(1 to 9.76 M $\Omega$ )

Letter L is system default code for order only  $^{(Note)}$ 

 $9M76 = 9,760,000 \Omega$ 

number Resistance code rule	Example
XRXX (I to 9.76 Ω)	IR = I Ω IR5 = I.5 Ω 9R76 = 9.76 Ω
XXRX (10 to 97.6 $\Omega$ )	$10R = 10 \Omega$ $97R6 = 97.6 \Omega$
XXXR (100 to 976 Ω)	100R = 100 Ω
XKXX (1 to 9.76 KΩ)	IK = 1,000 Ω 9K76 = 9760 Ω
XMXX	IM = 1,000,000 Ω

Resistance rule of global part

#### **ORDERING EXAMPLE**

The ordering code of a RT0603 chip resistor, TC 50 value 56  $\Omega$  with  $\pm 0.5\%$  tolerance, supplied in 7-inch tape reel is: RT0603DRE0756RL.

#### NOTE

- All our RSMD products meet RoHS compliant and Halogen Free. "LFP" of the internal 2D reel label mentions "Lead Free Process"
- 2. On customized label, "LFP" or specific symbol can be printed



#### **PHYCOMP BRAND** ordering codes

Phicomp

Both GLOBAL PART NUMBER (preferred) and I2NC (traditional) codes are acceptable to order Phycomp brand products. For matching traditional types with size codes, please refer to "Comparison table of traditional types and sizes".

#### **GLOBAL PART NUMBER (PREFERRED)**

For detailed information of GLOBAL PART NUMBER and ordering example, please refer to page 2.

#### 12NC CODE

<b>2390</b> (I)	<b>X</b> (2)	<b>XX</b> (3)	<b>X</b> (4)	<b>XXXX</b> (5)	<b>L</b> (6)
START WITH (I)	TCR <sup>(2)</sup> (ppm/°C)	PACKING CODE BY SIZE (inch) (3)	TOL. <sup>(4)</sup> (%)	RESISTANCE RANGE	DEFAULT CODE (NOTE)
2390	8 = ±10	0402: 07 = 7" reel	7 = ±1	The remaining 4 digits	Letter L is
	$7 = \pm 15$	47 = 13" reel	$6 = \pm 0.5$	represent the resistance	,
	$6 = \pm 25$	0603: 04 = 7" reel	$5 = \pm 0.25$	value with the last digit indicating the multiplier	
	$4 = \pm 50$	24 = 10" reel	$4 = \pm 0.1$	as shown in the table o	
		44 = 13" reel	$3 = \pm 0.05$	"Last digit of 12NC".	(Note)
		0805: 01 = 7" reel		$0402:4.7\Omega \le R \le 240K\Omega$	!
		41 = 13" reel		0603: I $\Omega \le R \le IM\Omega$	
		1206: II = 7" reel		0805: $I\Omega \le R \le I.5 M\Omega$	
		51 = 13" reel		1206: $1\Omega \le R \le 1.5 M\Omega$	
		1210: 12 = 7" reel		$1210:4.7\Omega \le R \le 1 M\Omega$	
		52 = 13" reel		$2010:4.7\Omega \le R \le 1 M\Omega$	
		2010: 15 = 7" reel		$25 \mid 2: 4.7\Omega \le R \le   M\Omega$	
		2512: 18 = 7" reel			

Comparison table of traditional types and sizes										
<b>TF</b> (l)	<b>X</b> (2)	<b>X</b> (3)	<b>X</b> (4)							
START WITH	SIZE CODE	TCR (ppm/°C)	TOL. (%)							
TF	3 = 0402	$4 = \pm 10$	$0 = \pm 1$							
	2 = 0603	$3 = \pm 15$	$I = \pm 0.5$							
	I = 0805	$1 = \pm 25$	$2 = \pm 0.25$							
	0 = 1206	$2 = \pm 50$	$3 = \pm 0.1$							
	5 = 1210		$4 = \pm 0.05$							
	7 = 2010									
	6 = 2512									
<b>€</b> Example:										
TF321 =	TF321 = RT0402, TC50, $\pm$ 0.5% tolerance									

#### Exceptions to above packing code definitions:

0805 TC50 with 1%, supplied in 13" reel, the packing code is 02. 0603 TC50 with 1%, supplied in 13" reel, the packing code is 03. 2512 TC15, in 7" reel, the packing code is 35. 2010 TC15, in 7" reel, the packing code is 31.

The ordering code of a TF221 resistor, TC50, value 56  $\Omega$  , with  $\pm 0.5\%$ tolerance, supplied in tape of 5,000 units per reel is: 239040465609L or RT0603DRE0756RL.

#### **ORDERING EXAMPLE**

- 1. All our RSMD products meet RoHS compliant and Halogen Free. "LFP" of the internal 2D reel label mentions "Lead Free Process"
- 2. On customized label, "LFP" or specific symbol can be printed

10 to 97.6 kΩ $3$									
$100 \text{ to } 976 \text{ k}\Omega$ 4									
I to 9.76 N	I to 9.76 $M\Omega$								
10 to 97.6	ΜΩ		6						
Example:	ΙΩ	=	1008 or 108						
	33 kΩ	=	3303 or 333						
	10 MΩ	=	1006 or 106						

Resistance decade (3)

I to 9.76 Ω

10 to 97.6  $\Omega$ 

100 to 976 O I to 9.76 kΩ



Last digit

8

9

9

#### **MARKING**

#### RT0201 / RT0402 / RESISTANCE VALUE IS NOT IN E-24 / E96 SERIES



No marking

#### RT0603



E-24 series: exception values 10/11/13/15/20/75 of E-24 series, one short bar under marking letter



E-96 series: including values 10/11/13/15/20/75 of E-24 series, 3 digits

#### RT0805 / RT1206 / RT1210 / RT2010 / RT2512



Either resistance in E-24 or E-96: 4 digits

First three digits for significant figure and 4th digit for number of zeros

For further marking information, please see special data sheet "Chip resistors marking".

#### CONSTRUCTION


The resistors are constructed out of a high-grade ceramic body. Internal metal electrodes are added at each end and connected by a resistive layer. The resistive layer is adjusted to give the approximate required resistance and laser cutting of this resistive layer that achieves tolerance trims the value. The resistive layer is covered with a protective coat and printed with the resistance value. Finally, the two external terminations (matte tin) are added. See fig. 5.

#### **DIMENSION**

Table I	For outlines see fig. 5	
T\/DE	1 ( ) 14//	

TYPE	L (mm)	W (mm)	H (mm)	I <sub>I</sub> (mm)	I <sub>2</sub> (mm)
RT0201	0.60 ±0.03	0.30 ±0.03	0.23 ±0.03	0.10 ±0.05	0.15 ±0.05
RT0402	1.00 ±0.10	0.50 ±0.05	0.30 ±0.05	0.20 ±0.10	0.25 ±0.10
RT0603	1.60 ±0.10	0.80 ±0.10	0.45 ±0.10	0.25 ±0.15	0.25 ±0.15
RT0805	2.00 ±0.10	1.25 ±0.10	0.50 ±0.10	0.35 ±0.20	0.35 ±0.20
RT1206	3.10 ±0.10	1.60 ±0.10	0.55 ±0.10	0.45 ±0.20	0.40 ±0.20
RT1210	3.10 ±0.10	2.60 ±0.15	0.55 ±0.10	0.50 ±0.20	0.50 ±0.20
RT2010	5.00 ±0.10	2.50 ±0.15	0.55 ±0.10	0.60 ±0.20	0.50 ±0.20
RT2512	6.35 ±0.10	3.20 ±0.15	0.55 ±0.10	0.60 ±0.20	0.50 ±0.20

#### **OUTLINES**



# 5

## **ELECTRICAL CHARACTERISTICS**

#### Table 2

Tabl	e 2											
TYPE	Operating Temperature	Power Rating	Max. Work		Dielectric Withstand					nge (E-24/E-96	, , ,	
	Range		Vol. (I)	Vol.	Vol.		±0.01%	±0.05%	±0.1%	±0.25%	±0.5%	±1.0%
						±50			22 ~75K	22 ~75K	22 ~75K	22 ~75K
	LL 0C+-					±25			22~75K	22~75K	22~75K	22~75K
RT0201	–55 °C to +125 °C	1/20W	25V	50V	50V	±15						
	+125 C					±10						
						±5						
						±50	50.1~12K	20~12K	4.7~240K	4.7~240K	4.7~240K	4.7~240K
						±25	50.1~12K	20~12K	4.7~240K	4.7~240K	4.7~240K	4.7~240K
RT0402		1/16W	50V	100V	75V	±15	20~12K	20~12K	20~70K	20~70K		
						±10	20~12K	20~12K	20~70K	20~70K		
	-					±5	20~10K	20~10K	20~10K	20~10K		
						±50	50.1~30K	4.7~100K	I~IM	I~IM	I~IM	1~1M
						±25	50.1~30K	4.7~100K	~ M	~ M	I~IM	I~IM
RT0603		1/10W	75V	150V	100V	±15	50.1~100K	4.7~100K	4.7~332K	4.7~332K		
	−55 °C to					±10 ±5	50.1~100K 20~30K	4.7~100K 20~30K	4.7~332K 20~30K	4.7~332K 20~30K		
	-55 °C to +155 °C					±50	50.1~30K	4.7~200K	1~1.5M	1~1.5M	I~I.5M	I~I.5M
	+133 C					±25	50.1~30K	4.7~200K	I~1.5M	I~1.5M	1~1.5M	I~1.5M
RT0805		1/8W	150V	300V	200V	±15	50.1~200K	4.7~200K	4.7~800K	4.7~800K		
111 0005		170 V V	130 V	300 V	200 v	±10	50.1~200K	4.7~200K	4.7~800K	4.7~800K		
						±5	20~50K	20~50K	20~50K	20~50K		
	-	-				±50	50.1~30K	5.6~500K	1~1.5M	I~1.5M	I~I.5M	I~I.5M
						±25	50.1~30K	5.6~500K	1~1.5M	I~1.5M	1~1.5M	I~1.5M
RT1206		1/4W	200V	400V	300V	±15	50.1~500K	5.6~500K	5.6~1M	5.6~IM		
						±10	50.1~500K	5.6~500K	5.6~IM	5.6~IM		
						±5	20~100K	20~100K	20~100K	20~100K		
						±50		4.7~IM	4.7~IM	4.7~IM	4.7~IM	4.7~IM
						±25		4.7~IM	4.7~IM	4.7~IM	4.7~IM	4.7~IM
RT1210		1/4W	200V	400V	400V	±15		100~100k	4.7~100k	4.7~100k		
						±10		100~100k	4.7~100k	4.7~100k		
						±5						
	-	-				±50		4.7~IM	4.7~IM	4.7~IM	4.7~IM	4.7~IM
						±25		4.7~IM	4.7~IM	4.7~IM	4.7~IM	4.7~IM
DTOLLO	−55 °C to	1 (2) 4 (	2001/	400) /	400) /							7,/ - 1111
RT2010	+125 °C	1/2W	200V	400V	400V	±15		100~100k	4.7~100k	4.7~100k		
						±10		100~100k	4.7~100k	4.7~100k		
	<b>=</b>	-				±5						
						±50		4.7~IM	4.7~IM	4.7~IM	4.7~IM	4.7~IM
						±25		4.7~IM	4.7~IM	4.7~IM	4.7~IM	4.7~IM
RT2512		3/4W	200V	400V	400V	±15		100~100k	4.7~100k	4.7~100k		
						±10		100~100k	4.7~100k	4.7~100k		
						±5						
						<u>.</u>						

#### NOTE

- 1. The maximum working voltage that may be continuously applied to the resistor element, see "IEC publication 60115-8"
- 2. Value of E-192 series is on request



6 9

#### FOOTPRINT AND SOLDERING PROFILES

For recommended footprint and soldering profiles, please see the special data sheet "Chip resistors mounting".

#### PACKING STYLE AND PACKAGING QUANTITY

Table 3 Packing style and packaging quantity

PACKING STYLE	REEL DIMENSION	RT0201	RT0402	RT0603	RT0805	RT1206	RT1210	RT2010	RT2512
Paper/PE taping reel (R)	7" (178 mm)	10,000	10,000	5,000	5,000	5,000	5,000		
	10" (254 mm)	20,000	20,000	10,000	10,000	10,000	10,000		
	13" (330 mm)	50,000	50,000	20,000	20,000	20,000	20,000		
Embossed taping reel (K)	7" (178 mm)							4,000	4,000

#### NOTE

1. For Paper/Embossed tape and reel specification/dimensions, please see the special data sheet "Chip resistors packing"

#### **FUNCTIONAL DESCRIPTION**

#### **POWER RATING**

Each type rated power at 70°C: RT0201=1/20W, RT0402=1/16W, RT0603=1/10W, RT0805=1/8W, RT1206=1/4W, RT1210=1/4W, RT2010=1/2W, RT2512=3/4W.

#### **RATED VOLTAGE**

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{(P \times R)}$$


or max. working voltage whichever is less

Where

V=Continuous rated DC or AC (rms) working voltage (V)

P=Rated power (W)

R=Resistance value ( $\Omega$ )



## TESTS AND REQUIREMENTS

Table 4 Test condition, procedure and requirements

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS		
Temperature Coefficient of	MIL-STD-202 Method 304	At +25/–55 °C and +25/+125 °C	Refer to table 2		
		Formula:			
,		T.C.R= $\frac{R_2-R_1}{R_1(t_2-t_1)} \times 10^6 \text{ (ppm/°C)}$			
		Where $t_1$ =+25 °C or specified room temperature			
		$t_2$ =-55 °C or +125 °C test temperature			
		R <sub>I</sub> =resistance at reference temperature in ohms			
		R <sub>2</sub> =resistance at test temperature in ohms			
Temperature MIL-STD-202 Method 304		At 70±5 °C for 1,000 hours, RCWV applied for 1.5 hours on, 0.5 hour off, still air required	±(0.5%+0.05 Ω)		
Temperature	IEC 60068-2-2	1000 hours at maximum operating temperature depending on specification, unpowered	±(0.5%+0.05 Ω)		
	MIL-STD-202 Method 106G	Each temperature / humidity cycle is defined at 8 hours, 3 cycles / 24 hours for IOd. with 25 °C / 65 °C 95% R.H, without steps 7a & 7b, unpowered	±(0.5%+0.05 Ω)		
		Parts mounted on test-boards, without condensation on parts			
		Measurement at 24±2 hours after test conclusion			
Thermal Shock	MIL-STD-202 Method 107G	-55/+125 °C Number of cycles required is 300.	$\pm (0.5\% + 0.05~\Omega)$ for 10 K $\Omega$ to 10 M $\Omega$		
		Devices mounted	$\pm (0.5\% + 0.05 \ \Omega)$ for others		
		Maximum transfer time is 20 seconds. Dwell time is 15 minutes. Air – Air			
Humidity	IEC 60115-1 4.24.2	Steady state for 1000 hours at 40 °C / 95% R.H.	±(0.5%+0.05 Ω)		
(steady state)		RCWV applied for 1.5 hours on and			
		0.5 hour off			

# Chip Resistor Surface Mount RT SERIES 0201 to 2512 (RoHS Compliant)

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Short Time Overload	IEC60115-1 4.13	2.5 times of rated voltage or maximum	±(0.5%+0.05 Ω)
		overload voltage whichever is less for 5 sec at room temperature	No visible damage
Board Flex/	IEC 60115-1 4.33	Chips mounted on a 90mm glass epoxy resin	±(0.25%+0.05 Ω)
Bending	PCB (FR4)		No visible damage
		Bending: see table 6 for each size Bending time: 60±5 seconds	
Insulation Resistance	IEC 60115-1 4.6	Rated continuous overload voltage (RCOV) for I minute	≥10 GΩ
		Details see below table 5	
Dielectric Withstand Voltage	IEC 60115-1 4.7	Maximum voltage (V <sub>rms</sub> ) applied for 1 minute	No breakdown or flashover
Solderability		Electrical Test not required	Well tinned (≥95%
- Wetting	J-STD-002 test B	Magnification 50X	covered)
		SMD conditions:	No visible damage
		I <sup>st</sup> step: method B, aging 4 hours at 155°C dry heat	
		2 <sup>nd</sup> step: leadfree solder bath at 245±3°C Dipping time: 3±0.5 seconds	
- Leaching	J-STD-002 test D	Leadfree solder, 260 °C, 30 seconds immersion time	No visible damage
- Resistance to	IEC 60115-1 4.18	Condition B, no pre-heat of samples.	±(0.5%+0.05 Ω)
Soldering Heat		Leadfree solder, 260 °C, 10 seconds	No visible damage
		immersion time Procedure 2 for SMD: devices fluxed and cleaned with isopropanol	The residence callinage

Table 5	Criteria	of rated	continued	working	voltage	and	overload '	voltage
---------	----------	----------	-----------	---------	---------	-----	------------	---------

TYPE	RT0201	RT0402	RT0603	RT0805	RT1206	RT1210	RT2010	RT2512
Voltage (DC/unit: V); (AC/ unit: $V_{rms}$ )	50	100	100	300	500	500	500	500

7	Table	6	Ranc	ling	for	sizes	020	٦١ -	to ?	51	7
	labie	n	Den	11119	IOT:	51765	いノ	"	1() /	′. ⊃ I	/

TYPE	RT0201	RT0402	RT0603	RT0805	RT1206	RT1210	RT2010	RT2512
Specification (mm)	5	5	3	3	2	2	2	2

## Chip Resistor Surface Mount RT SERIES 0201 to 2512 (RoHS Compliant)

#### REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 8	May 31, 2017	-	-Add 10" packing
Version 7	Jan. 17, 2017	-	- Add ±0.01% tol. for 0402 to 1206
Version 6	May. 11, 2015	-	-Extend resistor value
Version 5	Aug. 22, 2014	-	-Add RT0201
			- RT0402/0603/0805/1206: resistance range and operating temperature range updated
			- Fig. 6 updated
Version 4	Oct 21, 2009	-	- Test Items and methods updated
			- Test requirements upgraded
Version 3	Jul 11, 2008	-	- Change to dual brand datasheet that describe RT0402 to RT2512 with RoHS compliant
			- Description of "Halogen Free Epoxy" added
			- Define global part number
			- Modify electrical characteristic
Version 2	Dec 26, 2005	-	- New datasheet for thin film high precision - high stability chip resistors sizes of 0201/0402/0603/0805/1206/1210/2010/2512, 1%, 0.5%, 0.25%, 0.1%, 0.05%, TC25/50 with lead-free terminations
			- Replace the 0402 to 1210 parts of pdf files: TFx10_1_1, TFx115_2, TFx1225_2, TFx131_3, TFx1405_1, TFx20_1_2, TFx215_2, TFx2225_2, TFx231_2, TFx2405_1, and combine into a document.
			- Test method and procedure updated
			- PE tape added (paper tape will be replaced by PE tape)

<sup>&</sup>quot;Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products itself are unchanged. Any product change will be announced by PCN."

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

# Yageo:

RT0603BRD0710KL RT0603BRD0712K4L RT0603BRD072K67L RT0603BRD0749R9L RT0603FRE0710K2L RT0603FRE071K78L RT0603FRE072K7L RT0603FRE0733KL RT0603FRE07348RL RT0603FRE075K49L RT0603FRE076K2L RT0805BRD0722K6L RT0805BRD0724K9L RT0805BRD072K67L RT1206BRD07100KL RT1206BRD07100RL RT1206BRD0710K5L RT1206BRD0710KL RT1206BRD0712KL RT1206BRD0715KL RT1206BRD07187KL RT1206BRD0719K1L RT1206BRD0720KL RT1206BRD0723K2L RT1206BRD0726K1L RT1206BRD072KL RT1206BRD07301RL RT1206BRD0730K1L RT1206BRD0731K6L RT1206BRD07357KL RT1206BRD073K01L RT1206BRD073K74L RT1206BRD07402RL RT1206BRD07442RL RT1206BRD0744K2L RT1206BRD07475KL RT1206BRD0749K9L RT1206BRD0749R9L RT1206BRD074K99L RT1206BRD0756K2L RT1206BRD076K65L RT1206BRD0775KL RT1206BRD0784K5L RT1210BRD07120RL RT0402BRD07100KL RT0402FRE0712K1L RT0603FRE0711KL RT0603FRE07150KL RT0603FRE0719K1L RT0603FRE072K21L RT0603FRE0768KL RT0603FRE078R25L RT0805BRD071K4L RT0805BRD072K74L RT0805BRD072K8L RT0805BRD0720KL RT0805BRD0722K1L RT0805BRD07402RL RT0805BRD0793R1L RT0402DRE078K87L RT0603BRD0710K5L RT0603FRE073K92L RT0603FRE0717K4L RT0603DRE071KL RT0603DRE07100KL RT0603DRE07121RL RT0603BRD07267KL RT0603BRD07118KL RT0603BRD07196KL RT0603BRD0764K9L RT0805BRD071K1L RT0805BRD0712K1L RT0805BRD07121KL RT0805BRD0713KL RT0805BRD07154KL RT0805BRD07178KL RT0805BRD0727KL RT0805BRD07287KL RT0805BRD0747KL RT0805BRD0788K7L RT0805BRD079K09L RT0805BRD076K34L RT0805BRD0795K3L RT0603BRD0724KL RT0603FRE0712KL RT0805BRD07681KL RT0603BRD071K07L RT0603BRD071K65L RT0603BRD071K87L RT0603BRD075K49L RT0603BRD071K4L RT0603BRD071K37L RT0603FRE076K49L RT0805BRD071ML RT0402BRD071KL RT0402BRD071K5L RT0603BRD0712K7L RT0603BRD0714K7L RT1206BRD0717K4L RT0402BRD0747K5L