

Features

- Fluorescence Type
- High Luminous Intensity
- High Efficiency
- Pb-free
- The product itself will remain within RoHS compliant version.

Descriptions



• The 57-21 series is available in soft orange, green, blue and yellow. Due to the package design, the LED has wide viewing angle and optimized light coupling by inter reflector. This feature makes ideal for light pipe application. The low current requirement makes this device ideal for portable equipment or any other application where power is at a premium.

Applications

- OA equipment
- Backlighting of full color LCD
- Automotive equipment
- Replacement of conventional light bulbs and Fluorescent Lamps


Device Selection Guide

Chip		Resin Color	
Material	Emitted Color	Kesiii Color	
InGaN	Brilliant Green	Water Clear	



Technical Data Sheet Side View LED

Package Outline Dimensions



Note: Tolerances unless mentioned are ± 0.1 mm, unit = mm.



Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit
Reverse Voltage	V _R	5	V
Forward Current	I _F	25	mA
Peak Forward Current (Duty 1/10 @1KHz)	I _{FP}	100	mA
Power Dissipation	Pd	95	mW
Electrostatic Discharge(HBM)	ESD	1000	V
Operating Temperature	Topr	-40 ~ +85	°C
Storage Temperature	Tstg	-40 ~ +90	°C
Soldering Temperature	Tsol	Reflow Soldering : 260° C for 10 sec. Hand Soldering : 350° C for 3 sec.	

Electro-Optical Characteristics (Ta=25°C)

I		· · · · · · · · · · · · · · · · · · ·				
Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	Iv	285		715	mcd	
Viewing Angle	201/2		120		deg	
Peak Wavelength	λp		518		nm	
Dominant Wavelength	λd	517.5		535.5	nm	I _F =20mA
Spectrum Radiation Bandwidth	Δλ		35		nm	
Forward Voltage	V_{F}	2.75		3.95	V	Ĭ
Reverse Current	I _R			50	μΑ	V _R =5V

Notes:

- 1. Tolerance of Luminous Intensity: $\pm 11\%$
- 2. Tolerance of Dominant Wavelength: ±1nm
- 3. Tolerance of Forward Voltage: ±0.05V

http://www.everlight.com

Prepared date: 05-Jun.-2012



Bin Range of Luminous Intensity

Bin Code	Min.	Max.	Unit	Conduction	
T1	285	360			
T2	360	450	mad	L = 20m A	
U1	450	565	mcd	I _F =20mA	
U2	565	715			

Bin Range of Dominant Wavelength

Groups	Bin	Min	Max	Unit	Condition	
	B10	517.5	519.5			
	B11	519.5	521.5			
	B12	521.5	523.5			
	B13	523.5	525.5			
А	B14	525.5	527.5	nm	I _F =20mA	
	B15	527.5	529.5			
	B16	529.5	531.5			
	B17	531.5	533.5			
	B18	533.5	535.5			

http://www.everlight.com

Prepared date: 05-Jun.-2012



Bin Range of Forward Voltage

Groups	Bin	Min	Max	Unit	Condition	
М	5	2.75	3.05			
	6	3.05	3.35		L -20 A	
	7	3.35	3.65	volt	I _F =20mA	
	8	3.65	3.95			

Notes:

1. Tolerance of Luminous Intensity: ±11%

2. Tolerance of Dominant Wavelength: ±1nm

3. Tolerance of Forward Voltage: $\pm 0.1V$



Ta=25°

3.8

Ta=25°

2 10

10°

I_F (mA)

20°

0.4 0.6

Ta=25°

30°

40°

50°


60°

70°

80°

90°

4.2



Typical Electro-Optical Characteristics Curves

Everlight Electronics Co., Ltd. Device No.: DSE-0001455

http://www.everlight.com Prepared date: 05-Jun.-2012 Rev.1 Page: 6 of 11 Prepared by: Rita Shen



Technical Data Sheet Side View LED


Label Explanation

CAT: Luminous Intensity Rank HUE: Dom. Wavelength Rank REF: Forward Voltage Rank

57-21/GHC-AT1U2M/BF



Reel Dimensions




Note: Tolerance unless mentioned is ± 0.1 mm, unit = mm.

Everlight Electronics Co., Ltd. Device No.: DSE-0001455




Carrier Tape Dimensions: Loaded Quantity 500 pcs. Per Reel



Note: Tolerance unless mentioned is ± 0.1 mm, unit = mm.

Moisture Resistant Packaging





Reliability Test Items and Conditions

The reliability of products shall be satisfied with items listed below. Confidence level : 90% LTPD : 10%

No.	Items	Test Condition	Test Hours/Cycles	Sample Size	Ac/Re
1	Reflow Soldering	Temp. : 260°C±5°C Min. 5sec.	6 Min.	22 pcs.	0/1
2	Temperature Cycle	H : +100°C 15min ∫ 5 min L : -40°C 15min	300 Cycles	22 pcs.	0/1
3	Thermal Shock	H : +100°C 5min ∫ 10 sec L : -10°C 5min	300 Cycles	22 pcs.	0/1
4	High Temperature Storage	Temp. : 100°C	1000 Hrs.	22 pcs.	0/1
5	Low Temperature Storage	Temp. : -40°C	1000 Hrs.	22 pcs.	0/1
6	DC Operating Life	$I_F = 20 \text{ mA}$	1000 Hrs.	22 pcs.	0/1
7	High Temperature / High Humidity	85°C/85%RH	1000 Hrs.	22 pcs.	0/1




Precautions for Use

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
 - 2.1 Do not open moisture proof bag before the products are ready to use.
- 2.2 Before opening the package: The LEDs should be kept at 30° C or less and 90%RH or less.
- 2.3 After opening the package: The LED's floor life is 72 hours under 30℃ or less and 60% RH or less. If unused LEDs remain, it should be stored in moisture proof packages.
- 2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.
 Baking treatment : 60±5°C for 24 hours.
- 3. Soldering Condition
 - 3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.



4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350° C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5. Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.

