





CONSTANT VOLTAGE AND CONSTANT CURRENT CONTROLLER

Description

The AP4313 is a highly integrated solution for a voltage/constant current mode SMPS application.

The AP4313 contains one 1.21V voltage reference with ±1% accuracy, one current sensing circuit and two operational amplifiers. Combining the voltage reference with one operational amplifier makes AP4313 an ideal voltage controller for use in adapters and battery chargers. The other low voltage reference combined with the other operational amplifier makes it an ideal current limiter for output low side current sensing.


The AP4313 is available in SOT26 package.

Features

- Constant Voltage and Constant Current Control
- Precision Internal Voltage Reference
- Few External Components
- **Easy Compensation**
- Low Supply Current: 0.5mA
- Operating Temperature Range: -40 to +105°C
- Totally Lead-free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)

Pin Assignments

(Top View) Pin 1 Mark



SOT26


Applications

- Adapters
- **Battery Chargers**

Notes:

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
- 2. See http://www.diodes.com/quality/lead_free.html for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green"
- 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.

Typical Applications Circuit




$$V_{\scriptscriptstyle OUT} = V_{\scriptscriptstyle REF} imes rac{R1 + R2}{R1}$$
 (V)

$$CurrentLimit = \frac{V_{SENSE}}{R_{SS}}$$
 (A)

Typical Application 1




Typical Applications Circuit (Cont.)



$$V_{OUT} = [V_{REF} + (I_L \times R_{SS})] \times \frac{R1 + R2}{R1} - (I_L \times R_{SS}) \text{ (V)}$$

 $CurrentLimit = \frac{V_{SENSE}}{R_{SS}}$ (A)

Typical Application 2




Typical Application 3



Pin Descriptions

Pin Number	Pin Name	Function		
1	V_{CTRL}	Input pin of the voltage control loop		
2	GND	Ground		
3	V_{OUT}	Output pin. Sinking current only		
4	I _{CTRL}	Input pin of the current control loop		
5	$V_{\sf SENSE}$	Input pin of the current control loop		
6	V _{cc}	Power supply		

Functional Block Diagram





Absolute Maximum Ratings (Note 4)

Symbol	Parameter	Rating	Unit
V _{cc}	Power Supply Voltage	20	V
V _{IN}	Input Voltage	-0.3 to V _{CC}	V
T _J	Junction Temperature	+150	°C
T _{STG}	Storage Temperature	-65 to +150	°C
T _{LEAD}	T _{LEAD} Lead Temperature (Soldering, 5 sec)		°C
θ _{JC}	θ _{JC} Package Thermal Resistance (Junction to Case)		°C/W

Note 4: Stresses greater than those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "Recommended Operating Conditions" is not implied. Exposure to "Absolute Maximum Ratings" for extended periods may affect device reliability.

Recommended Operating Conditions

Symbol	Parameter	Min	Max	Unit
V _{cc}	Power Supply Voltage	2.5	18	V
T _A	Operating Temperature Range	-40	+105	°C


$\textbf{Electrical Characteristics} \ \, (V_{\text{CC}}\!\!=\!\!5V,\,T_{\underline{A}}\!\!=\!\!+25^{\circ}\!C,\,\text{unless otherwise specified.})$

Symbol	Parameter	Conditions	Min	Тур	Max	Unit		
TOTAL CURRE	TOTAL CURRENT CONSUMPTION							
Icc	Total Supply Current Not Including the Output Sinking Current	-	-	0.6	1.2	mA		
VOLTAGE CON	VOLTAGE CONTROL LOOP							
Gmv	Transconduction Gain (V _{CTRL}). Sink Current Only	-	1	3.5	-	mA/mV		
V_{REF}	Voltage Control Loop Reference	_	1.198	1.21	1.222	V		
I _{IBV}	Input Bias Current (V _{CTRL})	_	-	50	_	nA		
CURRENT CON	CURRENT CONTROL LOOP							
Gmi	Transconduction Gain (I _{CTRL})	_	1.5	7	_	mA/mV		
V _{SENSE}	Current Control Loop Reference	I _{OUT} =2.5mA	196	200	204	mV		
I _{IBI}	Current Out of Pin I _{CTRL} at -200mV	_	_	25	_	μА		
OUTPUT STAGE								
V _{OL}	Low Output Voltage at 10mA Sinking Current	-	-	200	-	mV		
I _{os}	Output Short Circuit Current. Output to V _{CC} . Sink Current Only	-	-	27	50	mA		




Performance Characteristics


V_{REF} vs. Ambient Temperature




V_{SENSE} vs. Ambient Temperature




VCTRL Pin Input Bias Current vs. Ambient Temperature




I_{CTRL} Pin Input Bias Current vs. Ambient Temperature



Output Short Circuit Current vs. Ambient Temperature




Supply Current vs. Ambient Temperature






Ordering Information



Package	Temperature Range	Part Number	Marking ID	Packing
SOT26	-40 to +105°C	AP4313KTR-G1	G6G	3000/Tape & Reel


Marking Information

(Top View)




: Logo XXX: Marking ID





Package Outline Dimensions (All dimensions in mm(inch).)


(1) Package Type: SOT26





Suggested Pad Layout

(1) Package Type: SOT26



Dimensions	Z	G	X	Υ	Е
	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)	(mm)/(inch)
Value	3.600/0.142	1.600/0.063	0.700/0.028	1.000/0.039	0.950/0.037



IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
 - 1. are intended to implant into the body, or
 - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2014, Diodes Incorporated

www.diodes.com